

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563091

Luminaire Tested: **SQ4-PC3-150U-050D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563091
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12111.5 lumens
Efficiency: N/A
Efficacy: 144.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563091
CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563091

CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25				
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21				
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17				
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15				
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13				
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11				
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10				
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8				
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7				
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6720	6720	6720
5°	6770	6727	6702
10°	6754	6722	6703
15°	6719	6719	6712
20°	6674	6694	6694
25°	6611	6659	6639
30°	6531	6610	6581
35°	6433	6533	6487
40°	6327	6416	6352
45°	6213	6256	6159
50°	6049	6049	5953
55°	5858	5782	5695
60°	5575	5463	5376
65°	5154	5050	5005
70°	4512	4548	4530
75°	3629	4014	4038
80°	2579	3404	3439
85°	1574	2858	2858



TEST NUMBER: P563091

CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.4	0.9
10°-20°	296.7	2.4
20°-30°	449.3	3.7
30°-40°	538.7	4.4
40°-50°	549.3	4.5
50°-60°	479.5	4.0
60°-70°	343.3	2.8
70°-80°	176.8	1.5
80°-90°	47.7	0.4
90°-100°	657.9	5.4
100°-110°	1778.8	14.7
110°-120°	1870.1	15.4
120°-130°	1519.0	12.5
130°-140°	1191.6	9.8
140°-150°	914.5	7.6
150°-160°	657.7	5.4
160°-170°	401.8	3.3
170°-180°	135.5	1.1
0°-30°	849.4	7.0
0°-40°	1388.1	11.5
0°-60°	2416.9	20.0
0°-90°	2984.6	24.6
90°-120°	4306.8	35.6
90°-150°	7931.9	65.5
90°-180°	9127.0	75.4
0°-180°	12111.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1092	1092	1092	1092	1092	
5°	1096	1086	1090	1086	1085	104
15°	1055	1046	1055	1055	1054	297
25°	974	967	981	978	978	448
35°	857	855	870	864	864	536
45°	714	712	719	710	708	550
55°	546	539	539	531	531	487
65°	354	346	347	344	344	350
75°	153	160	169	170	170	165
85°	22	34	40	42	40	30
90°	3	9	20	21	20	8
95°	102	358	1094	566	337	107
105°	331	511	1973	2911	2792	348
115°	582	712	1636	3168	3576	575
125°	797	913	1475	2489	2924	710
135°	955	1069	1435	2010	2275	738
145°	1111	1194	1416	1720	1851	695
155°	1254	1303	1403	1543	1594	578
165°	1365	1379	1410	1464	1472	385
175°	1417	1416	1411	1429	1426	135
180°	1416	1416	1416	1416	1416	

TEST NUMBER: P563091

CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1092.5	1092.5	1092.5	1092.5	1092.5
2.5°	1099.0	1089.5	1092.5	1090.0	1086.0
5°	1096.5	1085.7	1089.5	1086.4	1085.4
7.5°	1088.7	1077.8	1082.8	1080.7	1079.8
10°	1081.4	1070.5	1076.3	1074.3	1073.3
12.5°	1071.7	1061.6	1068.2	1066.2	1066.0
15°	1055.1	1046.2	1055.1	1055.1	1054.1
17.5°	1034.2	1026.1	1035.7	1036.2	1035.7
20°	1019.7	1010.8	1022.7	1021.7	1022.7
22.5°	1001.9	994.5	1007.3	1004.7	1005.7
25°	974.1	967.2	981.2	978.2	978.2
27.5°	941.4	936.4	951.7	948.5	948.5
30°	919.5	914.6	930.7	926.6	926.6
32.5°	895.2	891.9	907.2	902.3	902.3
35°	856.8	854.8	870.0	863.9	863.9
37.5°	817.2	815.4	829.1	821.8	819.4
40°	788.0	787.0	799.1	791.1	791.1
42.5°	758.9	757.9	768.4	758.7	758.7
45°	714.2	712.2	719.2	710.1	708.1
47.5°	665.4	663.4	667.8	657.9	656.9
50°	632.2	630.3	632.2	623.1	622.1
52.5°	598.2	594.7	595.0	585.9	585.7
55°	546.3	539.3	539.2	531.1	531.1
57.5°	491.2	482.1	482.9	476.0	475.0
60°	453.2	443.3	444.1	438.0	437.0
62.5°	416.0	404.5	406.9	400.0	399.8
65°	354.1	346.1	347.0	343.9	343.9
67.5°	294.6	287.3	292.5	290.1	289.9
70°	250.9	245.9	252.9	252.9	251.9
72.5°	210.4	210.2	218.9	218.9	219.5
75°	152.7	159.7	168.9	169.9	169.9
77.5°	102.0	114.2	124.4	124.8	124.6
80°	72.8	86.7	96.1	98.1	97.1
82.5°	49.4	64.0	71.8	73.8	72.8
85°	22.3	34.1	40.5	41.5	40.5
87.5°	7.1	15.4	20.1	20.4	18.5
90°	3.0	9.0	19.8	21.3	19.8
92.5°	43.3	157.7	311.2	135.1	97.8
95°	102.1	358.4	1094.1	566.2	336.8
97.5°	164.0	411.0	1705.4	1411.3	1036.5
100°	210.3	432.3	1895.6	1976.9	1598.4
102.5°	252.9	461.8	1962.6	2405.7	2122.6
105°	330.7	510.9	1973.3	2910.8	2791.6
107.5°	402.6	567.1	1887.1	3225.8	3265.5
110°	458.7	607.7	1810.3	3310.4	3478.8



TEST NUMBER: P563091

CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	508.6	648.1	1739.5	3293.5	3576.3
115°	582.1	711.7	1636.5	3168.1	3576.3
117.5°	654.0	775.6	1568.6	2976.4	3439.2
120°	697.9	817.1	1528.4	2838.9	3311.2
122.5°	739.3	856.1	1504.0	2691.5	3167.3
125°	796.9	913.2	1475.0	2489.1	2924.1
127.5°	850.0	964.1	1458.0	2323.9	2706.5
130°	879.2	996.9	1450.6	2221.9	2567.6
132.5°	909.7	1026.2	1443.3	2129.9	2448.1
135°	955.4	1068.6	1435.4	2009.8	2275.0
137.5°	1001.4	1108.4	1428.7	1912.4	2128.4
140°	1033.1	1132.9	1426.3	1849.7	2041.9
142.5°	1063.6	1157.5	1421.4	1793.1	1961.4
145°	1110.8	1194.3	1415.6	1720.3	1851.4
147.5°	1153.8	1227.7	1408.9	1654.4	1755.1
150°	1185.5	1251.1	1406.5	1618.6	1699.0
152.5°	1214.8	1272.0	1405.2	1585.3	1651.5
155°	1254.1	1303.2	1403.4	1543.2	1593.9
157.5°	1294.9	1329.2	1403.7	1513.9	1547.2
160°	1318.1	1346.4	1404.9	1495.4	1519.2
162.5°	1336.4	1359.9	1406.1	1480.6	1498.5
165°	1365.3	1378.7	1409.5	1464.5	1472.0
167.5°	1385.1	1394.4	1409.8	1450.7	1454.3
170°	1397.3	1401.8	1411.0	1444.5	1444.5
172.5°	1407.1	1408.0	1411.0	1437.2	1436.0
175°	1417.1	1415.6	1411.0	1429.2	1426.3
177.5°	1420.5	1416.9	1410.7	1422.8	1419.3
180°	1415.6	1415.6	1415.6	1415.6	1415.6

(END OF REPORT)