

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563163

Luminaire Tested: **SQ4-PC3-150U-125D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563163  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-150U-125D-840-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 16581.3 lumens  
Efficiency: N/A  
Efficacy: 130.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 127.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563163  
CATALOG NUMBER: SQ4-PC3-150U-125D-840-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563163

CATALOG NUMBER: SQ4-PC3-150U-125D-840-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	89	85	88	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	80	74	69	65	62	58	55	51	48	46	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16794	16794	16794
5°	16920	16811	16748
10°	16879	16800	16753
15°	16791	16791	16774
20°	16680	16730	16730
25°	16522	16642	16591
30°	16321	16519	16447
35°	16078	16325	16211
40°	15813	16036	15873
45°	15525	15635	15393
50°	15119	15119	14878
55°	14639	14450	14232
60°	13933	13652	13435
65°	12877	12620	12509
70°	11276	11366	11321
75°	9071	10034	10093
80°	6447	8508	8597
85°	3924	7135	7135



TEST NUMBER: P563163

CATALOG NUMBER: SQ4-PC3-150U-125D-840-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	258.4	1.6
10°-20°	741.5	4.5
20°-30°	1122.9	6.8
30°-40°	1346.2	8.1
40°-50°	1372.7	8.3
50°-60°	1198.3	7.2
60°-70°	857.9	5.2
70°-80°	441.9	2.7
80°-90°	114.7	0.7
90°-100°	657.9	4.0
100°-110°	1778.8	10.7
110°-120°	1870.1	11.3
120°-130°	1519.0	9.2
130°-140°	1191.6	7.2
140°-150°	914.5	5.5
150°-160°	657.7	4.0
160°-170°	401.8	2.4
170°-180°	135.5	0.8
0°-30°	2122.8	12.8
0°-40°	3469.1	20.9
0°-60°	6040.0	36.4
0°-90°	7454.4	45.0
90°-120°	4306.8	26.0
90°-150°	7931.9	47.8
90°-180°	9127.0	55.0
0°-180°	16581.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2730	2730	2730	2730	2730	
5°	2740	2713	2723	2715	2713	260
15°	2637	2614	2637	2637	2634	743
25°	2434	2417	2452	2445	2445	1120
35°	2141	2136	2174	2159	2159	1339
45°	1785	1780	1797	1775	1770	1374
55°	1365	1348	1348	1327	1327	1217
65°	885	865	867	860	860	875
75°	382	399	422	425	425	413
85°	56	85	101	104	101	76
90°	3	9	20	21	20	9
95°	102	358	1094	566	337	107
105°	331	511	1973	2911	2792	348
115°	582	712	1636	3168	3576	575
125°	797	913	1475	2489	2924	710
135°	955	1069	1435	2010	2275	738
145°	1111	1194	1416	1720	1851	695
155°	1254	1303	1403	1543	1594	578
165°	1365	1379	1410	1464	1472	385
175°	1417	1416	1411	1429	1426	135
180°	1416	1416	1416	1416	1416	



TEST NUMBER: P563163

CATALOG NUMBER: SQ4-PC3-150U-125D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2730.3	2730.3	2730.3	2730.3	2730.3
2.5°	2746.5	2722.7	2730.3	2724.0	2714.1
5°	2740.4	2713.2	2722.7	2715.1	2712.6
7.5°	2720.7	2693.5	2706.0	2700.9	2698.4
10°	2702.5	2675.3	2689.8	2684.7	2682.3
12.5°	2678.2	2653.0	2669.6	2664.6	2664.1
15°	2636.8	2614.5	2636.8	2636.7	2634.2
17.5°	2584.7	2564.4	2588.2	2589.7	2588.2
20°	2548.3	2526.0	2555.9	2553.4	2555.9
22.5°	2503.8	2485.5	2517.4	2510.9	2513.4
25°	2434.5	2417.2	2452.2	2444.6	2444.6
27.5°	2352.6	2340.2	2378.4	2370.3	2370.3
30°	2298.0	2285.6	2325.8	2315.7	2315.7
32.5°	2237.3	2228.9	2267.2	2255.0	2255.0
35°	2141.3	2136.3	2174.1	2159.0	2159.0
37.5°	2042.2	2037.7	2072.0	2053.7	2047.7
40°	1969.4	1966.9	1997.2	1976.9	1976.9
42.5°	1896.5	1894.1	1920.3	1896.0	1896.0
45°	1784.8	1779.9	1797.4	1774.6	1769.6
47.5°	1663.0	1658.0	1669.0	1644.2	1641.7
50°	1580.0	1575.1	1580.0	1557.2	1554.8
52.5°	1495.1	1486.2	1487.0	1464.2	1463.7
55°	1365.1	1347.8	1347.5	1327.2	1327.2
57.5°	1227.6	1204.9	1206.9	1189.6	1187.2
60°	1132.6	1107.8	1109.8	1094.6	1092.1
62.5°	1039.5	1010.9	1016.8	999.6	999.1
65°	884.8	865.0	867.1	859.5	859.5
67.5°	736.2	717.9	731.1	725.0	724.5
70°	627.0	614.6	632.0	632.0	629.5
72.5°	525.8	525.3	547.1	547.1	548.6
75°	381.7	399.0	422.2	424.7	424.7
77.5°	254.8	285.5	311.0	312.0	311.5
80°	182.0	216.6	240.2	245.2	242.7
82.5°	123.4	160.0	179.5	184.5	182.0
85°	55.6	85.3	101.1	103.6	101.1
87.5°	16.8	35.8	44.4	44.6	40.4
90°	3.0	9.0	19.8	21.3	19.8
92.5°	43.3	157.7	311.2	135.1	97.8
95°	102.1	358.4	1094.1	566.2	336.8
97.5°	164.0	411.0	1705.4	1411.3	1036.5
100°	210.3	432.3	1895.6	1976.9	1598.4
102.5°	252.9	461.8	1962.6	2405.7	2122.6
105°	330.7	510.9	1973.3	2910.8	2791.6
107.5°	402.6	567.1	1887.1	3225.8	3265.5
110°	458.7	607.7	1810.3	3310.4	3478.8



TEST NUMBER: P563163

CATALOG NUMBER: SQ4-PC3-150U-125D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	508.6	648.1	1739.5	3293.5	3576.3
115°	582.1	711.7	1636.5	3168.1	3576.3
117.5°	654.0	775.6	1568.6	2976.4	3439.2
120°	697.9	817.1	1528.4	2838.9	3311.2
122.5°	739.3	856.1	1504.0	2691.5	3167.3
125°	796.9	913.2	1475.0	2489.1	2924.1
127.5°	850.0	964.1	1458.0	2323.9	2706.5
130°	879.2	996.9	1450.6	2221.9	2567.6
132.5°	909.7	1026.2	1443.3	2129.9	2448.1
135°	955.4	1068.6	1435.4	2009.8	2275.0
137.5°	1001.4	1108.4	1428.7	1912.4	2128.4
140°	1033.1	1132.9	1426.3	1849.7	2041.9
142.5°	1063.6	1157.5	1421.4	1793.1	1961.4
145°	1110.8	1194.3	1415.6	1720.3	1851.4
147.5°	1153.8	1227.7	1408.9	1654.4	1755.1
150°	1185.5	1251.1	1406.5	1618.6	1699.0
152.5°	1214.8	1272.0	1405.2	1585.3	1651.5
155°	1254.1	1303.2	1403.4	1543.2	1593.9
157.5°	1294.9	1329.2	1403.7	1513.9	1547.2
160°	1318.1	1346.4	1404.9	1495.4	1519.2
162.5°	1336.4	1359.9	1406.1	1480.6	1498.5
165°	1365.3	1378.7	1409.5	1464.5	1472.0
167.5°	1385.1	1394.4	1409.8	1450.7	1454.3
170°	1397.3	1401.8	1411.0	1444.5	1444.5
172.5°	1407.1	1408.0	1411.0	1437.2	1436.0
175°	1417.1	1415.6	1411.0	1429.2	1426.3
177.5°	1420.5	1416.9	1410.7	1422.8	1419.3
180°	1415.6	1415.6	1415.6	1415.6	1415.6

(END OF REPORT)