

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563427

Luminaire Tested: **SQ4-PP3-075U-100D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563427  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-100D-840-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10321.5 lumens  
Efficiency: N/A  
Efficacy: 124.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563427  
CATALOG NUMBER: SQ4-PP3-075U-100D-840-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563427

CATALOG NUMBER: SQ4-PP3-075U-100D-840-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	46	45	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33	30
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	27	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13900	13900	13900
5°	14001	13916	13867
10°	13978	13879	13817
15°	13886	13810	13734
20°	13793	13716	13612
25°	13630	13535	13401
30°	13377	13307	13138
35°	13028	12938	12775
40°	12611	12531	12388
45°	12267	12181	12060
50°	11826	11750	11637
55°	11214	11066	10980
60°	10209	9916	9867
65°	8993	8619	8590
70°	7765	7443	7443
75°	6683	6590	6495
80°	5894	5961	5823
85°	4615	5032	5032



TEST NUMBER: P563427

CATALOG NUMBER: SQ4-PP3-075U-100D-840-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	213.7	2.1
10°-20°	610.1	5.9
20°-30°	913.9	8.9
30°-40°	1072.0	10.4
40°-50°	1075.3	10.4
50°-60°	917.4	8.9
60°-70°	598.3	5.8
70°-80°	300.1	2.9
80°-90°	84.8	0.8
90°-100°	328.4	3.2
100°-110°	903.5	8.8
110°-120°	932.6	9.0
120°-130°	747.2	7.2
130°-140°	586.8	5.7
140°-150°	449.7	4.4
150°-160°	323.3	3.1
160°-170°	197.7	1.9
170°-180°	66.6	0.6
0°-30°	1737.7	16.8
0°-40°	2809.7	27.2
0°-60°	4802.4	46.5
0°-90°	5785.7	56.1
90°-120°	2164.4	21.0
90°-150°	3948.2	38.3
90°-180°	4536.0	43.9
0°-180°	10321.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2260	2260	2260	2260	2260	
5°	2268	2246	2254	2246	2246	215
15°	2181	2159	2169	2161	2157	615
25°	2008	1985	1994	1977	1975	923
35°	1735	1718	1723	1703	1701	1084
45°	1410	1400	1400	1386	1386	1086
55°	1046	1042	1032	1026	1024	929
65°	618	606	592	588	590	617
75°	281	281	277	275	273	305
85°	65	71	71	71	71	77
90°	2	6	10	13	13	6
95°	49	179	581	248	158	52
105°	162	248	996	1516	1415	170
115°	286	348	798	1590	1804	282
125°	394	449	724	1226	1436	352
135°	476	528	704	991	1121	367
145°	550	587	693	844	910	345
155°	622	642	689	759	781	286
165°	673	681	692	720	724	190
175°	696	698	693	702	701	66
180°	696	696	696	696	696	

TEST NUMBER: P563427

CATALOG NUMBER: SQ4-PP3-075U-100D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2259.8	2259.8	2259.8	2259.8	2259.8
2.5°	2274.1	2255.5	2259.8	2256.4	2247.1
5°	2267.7	2246.4	2253.9	2246.0	2246.0
7.5°	2252.3	2229.0	2236.4	2228.5	2228.1
10°	2238.0	2214.8	2222.2	2214.2	2212.3
12.5°	2217.4	2194.2	2203.2	2193.7	2193.3
15°	2180.6	2159.3	2168.7	2160.7	2156.8
17.5°	2139.0	2115.8	2127.1	2116.0	2114.4
20°	2107.3	2084.1	2095.4	2079.6	2079.6
22.5°	2069.3	2046.0	2059.0	2038.4	2038.4
25°	2008.3	1985.0	1994.4	1976.6	1974.6
27.5°	1935.8	1912.9	1922.7	1902.5	1902.1
30°	1883.5	1862.2	1873.6	1851.8	1849.8
32.5°	1826.5	1806.7	1815.0	1793.2	1791.2
35°	1735.0	1717.5	1723.1	1703.2	1701.3
37.5°	1638.7	1620.9	1627.2	1610.2	1609.4
40°	1570.6	1559.0	1560.7	1546.7	1542.9
42.5°	1507.2	1494.0	1495.7	1481.8	1481.1
45°	1410.2	1400.5	1400.3	1386.4	1386.4
47.5°	1307.2	1299.8	1297.7	1286.2	1285.8
50°	1235.9	1230.1	1227.9	1218.0	1216.1
52.5°	1161.4	1158.7	1151.9	1143.6	1143.2
55°	1045.7	1041.9	1031.9	1025.9	1023.9
57.5°	920.2	912.4	901.2	892.5	894.0
60°	829.9	822.1	806.1	802.1	802.1
62.5°	742.7	733.4	717.4	711.9	715.0
65°	617.9	606.3	592.2	588.3	590.2
67.5°	504.6	494.2	478.9	478.9	477.3
70°	431.8	426.0	413.9	413.9	413.9
72.5°	366.8	364.1	355.3	355.3	353.7
75°	281.2	281.2	277.3	275.3	273.3
77.5°	210.7	211.5	209.5	207.5	204.0
80°	166.4	170.2	168.3	166.3	164.4
82.5°	125.2	129.0	128.7	125.2	124.8
85°	65.4	71.2	71.3	71.3	71.3
87.5°	17.7	24.8	27.4	28.1	29.6
90°	1.5	5.8	10.4	13.3	13.3
92.5°	20.4	87.4	151.4	58.1	47.7
95°	48.9	179.3	580.7	248.3	158.5
97.5°	79.7	198.8	886.2	682.8	481.8
100°	102.2	210.9	982.2	991.4	808.8
102.5°	123.5	225.2	1007.1	1229.9	1062.5
105°	161.5	248.4	995.5	1516.1	1414.7
107.5°	197.6	277.0	938.9	1656.3	1686.4
110°	223.7	296.1	896.3	1691.2	1795.5



TEST NUMBER: P563427

CATALOG NUMBER: SQ4-PP3-075U-100D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	247.4	317.5	853.6	1668.7	1827.5
115°	285.9	348.2	798.5	1590.0	1804.4
117.5°	322.7	380.0	763.5	1479.5	1722.0
120°	345.2	400.2	748.1	1396.7	1647.3
122.5°	365.3	420.4	737.4	1324.2	1562.0
125°	394.1	449.1	724.4	1225.5	1435.5
127.5°	421.3	473.7	715.8	1143.1	1327.3
130°	435.5	489.1	711.1	1094.1	1262.2
132.5°	452.1	505.7	707.5	1051.1	1202.9
135°	475.5	527.7	703.7	991.1	1121.4
137.5°	497.5	545.8	700.4	942.5	1050.0
140°	514.0	559.0	699.2	910.3	1007.4
142.5°	528.3	569.7	696.9	881.5	964.7
145°	549.6	587.3	693.3	844.4	909.6
147.5°	572.4	604.9	691.5	811.5	863.7
150°	586.6	615.6	690.3	793.5	834.0
152.5°	599.7	626.3	689.2	777.9	811.5
155°	622.2	642.5	688.9	759.0	780.7
157.5°	638.5	655.0	688.9	743.4	758.5
160°	650.3	663.4	688.9	735.0	746.6
162.5°	659.8	670.5	690.0	727.9	737.1
165°	672.6	681.2	691.8	720.1	724.4
167.5°	681.4	688.1	693.3	713.5	714.6
170°	687.4	691.7	693.3	711.1	711.1
172.5°	692.1	694.1	693.3	707.5	706.3
175°	696.3	697.7	693.3	702.2	700.7
177.5°	697.4	697.4	692.7	699.8	697.4
180°	696.3	696.3	696.3	696.3	696.3

(END OF REPORT)