

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562825

Luminaire Tested: **SQ4-PC3-0U-075D-840-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562825
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8789.2 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct

Input Watts (W): 79.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562825
CATALOG NUMBER: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562825

CATALOG NUMBER: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85																												
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71																												
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60																												
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51																												
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44																												
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39																												
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34																												
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31																												
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28																												
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9904	9904	9904
5°	9979	9914	9878
10°	9954	9908	9880
15°	9902	9902	9893
20°	9837	9866	9866
25°	9744	9815	9785
30°	9625	9742	9700
35°	9482	9628	9561
40°	9326	9457	9361
45°	9156	9221	9078
50°	8917	8917	8774
55°	8634	8522	8394
60°	8217	8052	7923
65°	7595	7443	7377
70°	6649	6703	6676
75°	5351	5917	5953
80°	3802	5017	5071
85°	2315	4210	4210



TEST NUMBER: P562825

CATALOG NUMBER: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.8	3.5
10°-20°	874.6	10.0
20°-30°	1324.5	15.1
30°-40°	1587.9	18.1
40°-50°	1619.1	18.4
50°-60°	1413.4	16.1
60°-70°	1011.9	11.5
70°-80°	521.2	5.9
80°-90°	131.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2503.9	28.5
0°-40°	4091.8	46.6
0°-60°	7124.4	81.1
0°-90°	8789.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8789.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3220	3220	3220	3220	3220	
5°	3232	3200	3212	3202	3200	307
15°	3110	3084	3110	3110	3107	877
25°	2872	2851	2892	2884	2884	1322
35°	2526	2520	2564	2546	2546	1580
45°	2105	2099	2120	2093	2087	1621
55°	1610	1590	1589	1566	1566	1435
65°	1044	1020	1023	1014	1014	1032
75°	450	471	498	501	501	487
85°	66	101	119	122	119	92
90°	0	0	0	0	0	



TEST NUMBER: P562825

CATALOG NUMBER: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3220.4	3220.4	3220.4	3220.4	3220.4
2.5°	3239.5	3211.5	3220.4	3213.0	3201.4
5°	3232.4	3200.3	3211.5	3202.5	3199.6
7.5°	3209.1	3177.0	3191.8	3185.8	3182.9
10°	3187.6	3155.6	3172.7	3166.7	3163.8
12.5°	3159.0	3129.3	3148.9	3142.9	3142.3
15°	3110.1	3083.9	3110.1	3110.0	3107.1
17.5°	3048.7	3024.8	3052.9	3054.6	3052.9
20°	3005.7	2979.5	3014.7	3011.8	3014.7
22.5°	2953.3	2931.7	2969.4	2961.7	2964.6
25°	2871.6	2851.2	2892.4	2883.5	2883.5
27.5°	2774.9	2760.4	2805.4	2795.8	2795.8
30°	2710.5	2696.0	2743.3	2731.4	2731.4
32.5°	2639.0	2629.1	2674.2	2659.8	2659.8
35°	2525.7	2519.8	2564.4	2546.5	2546.5
37.5°	2408.8	2403.5	2444.0	2422.3	2415.3
40°	2322.9	2320.0	2355.7	2331.8	2331.8
42.5°	2237.0	2234.1	2265.0	2236.4	2236.4
45°	2105.2	2099.4	2120.1	2093.2	2087.3
47.5°	1961.5	1955.7	1968.6	1939.4	1936.4
50°	1863.7	1857.9	1863.7	1836.8	1833.9
52.5°	1763.5	1753.0	1753.9	1727.1	1726.5
55°	1610.2	1589.8	1589.3	1565.5	1565.5
57.5°	1448.0	1421.2	1423.6	1403.2	1400.3
60°	1335.9	1306.7	1309.1	1291.1	1288.2
62.5°	1226.2	1192.3	1199.3	1179.0	1178.4
65°	1043.7	1020.3	1022.8	1013.8	1013.8
67.5°	868.3	846.8	862.4	855.2	854.6
70°	739.5	724.9	745.5	745.4	742.5
72.5°	620.2	619.7	645.3	645.3	647.1
75°	450.3	470.7	498.0	501.0	501.0
77.5°	300.6	336.7	366.8	368.0	367.4
80°	214.7	255.5	283.3	289.2	286.3
82.5°	145.5	188.7	211.7	217.6	214.7
85°	65.6	100.6	119.3	122.2	119.3
87.5°	19.1	40.1	47.7	47.6	42.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)