

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563547

Luminaire Tested: **SQ4-PP3-0U-125D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563547
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-125D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7381.0 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563547
CATALOG NUMBER: SQ4-PP3-0U-125D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563547

CATALOG NUMBER: SQ4-PP3-OU-125D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17738	17738	17738
5°	17868	17759	17696
10°	17838	17712	17633
15°	17720	17623	17527
20°	17602	17503	17371
25°	17393	17273	17102
30°	17071	16982	16766
35°	16624	16511	16302
40°	16093	15991	15809
45°	15653	15543	15389
50°	15091	14995	14850
55°	14311	14121	14013
60°	13027	12655	12592
65°	11477	10998	10962
70°	9909	9499	9499
75°	8529	8408	8289
80°	7520	7608	7431
85°	5886	6422	6422



TEST NUMBER: P563547

CATALOG NUMBER: SQ4-PP3-0U-125D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.7	3.7
10°-20°	778.6	10.5
20°-30°	1166.3	15.8
30°-40°	1368.0	18.5
40°-50°	1372.3	18.6
50°-60°	1170.7	15.9
60°-70°	763.5	10.3
70°-80°	383.0	5.2
80°-90°	106.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2217.6	30.0
0°-40°	3585.6	48.6
0°-60°	6128.5	83.0
0°-90°	7381.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7381.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2884	2884	2884	2884	2884	
5°	2894	2867	2876	2866	2866	275
15°	2783	2756	2768	2757	2752	785
25°	2563	2533	2545	2522	2520	1178
35°	2214	2192	2199	2174	2171	1383
45°	1800	1787	1787	1769	1769	1386
55°	1334	1330	1317	1309	1307	1186
65°	789	774	756	751	753	787
75°	359	359	354	351	349	389
85°	83	91	91	91	91	101
90°	0	0	0	0	0	



TEST NUMBER: P563547

CATALOG NUMBER: SQ4-PP3-0U-125D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2883.8	2883.8	2883.8	2883.8	2883.8
2.5°	2902.0	2878.3	2883.8	2879.5	2867.6
5°	2893.9	2866.8	2876.2	2866.1	2866.1
7.5°	2874.2	2844.6	2854.0	2843.9	2843.4
10°	2856.0	2826.4	2835.8	2825.6	2823.2
12.5°	2829.7	2800.1	2811.5	2799.4	2798.9
15°	2782.7	2755.5	2767.6	2757.3	2752.4
17.5°	2729.7	2700.0	2714.5	2700.3	2698.3
20°	2689.2	2659.6	2674.0	2653.8	2653.8
22.5°	2640.7	2611.0	2627.5	2601.3	2601.3
25°	2562.8	2533.2	2545.1	2522.3	2519.9
27.5°	2470.3	2441.2	2453.7	2427.9	2427.4
30°	2403.6	2376.4	2391.0	2363.1	2360.6
32.5°	2330.8	2305.6	2316.2	2288.3	2285.8
35°	2214.0	2191.8	2198.9	2173.6	2171.1
37.5°	2091.2	2068.5	2076.6	2054.8	2053.8
40°	2004.3	1989.4	1991.6	1973.8	1968.9
42.5°	1923.4	1906.6	1908.7	1891.0	1890.0
45°	1799.5	1787.2	1786.9	1769.2	1769.2
47.5°	1668.1	1658.7	1656.0	1641.3	1640.8
50°	1577.1	1569.7	1567.0	1554.3	1551.9
52.5°	1482.1	1478.6	1470.0	1459.3	1458.8
55°	1334.5	1329.6	1316.8	1309.2	1306.7
57.5°	1174.3	1164.4	1150.0	1138.9	1140.9
60°	1059.0	1049.1	1028.7	1023.6	1023.6
62.5°	947.8	935.9	915.4	908.5	912.4
65°	788.6	773.7	755.7	750.7	753.2
67.5°	644.0	630.7	611.1	611.1	609.1
70°	551.0	543.6	528.2	528.2	528.2
72.5°	468.1	464.6	453.4	453.4	451.4
75°	358.9	358.9	353.8	351.3	348.8
77.5°	268.9	269.9	267.4	264.8	260.3
80°	212.3	217.2	214.8	212.2	209.8
82.5°	159.7	164.7	164.3	159.7	159.2
85°	83.4	90.8	91.0	91.0	91.0
87.5°	22.2	30.1	32.4	32.4	34.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)