

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562873

Luminaire Tested: **SQ4-PC3-0U-125D-840-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562873
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14903.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct

Input Watts (W): 140.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562873
CATALOG NUMBER: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562873

CATALOG NUMBER: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16794	16794	16794
5°	16920	16811	16748
10°	16879	16800	16752
15°	16790	16790	16774
20°	16680	16729	16729
25°	16522	16642	16591
30°	16321	16519	16447
35°	16078	16325	16211
40°	15813	16036	15874
45°	15525	15635	15393
50°	15119	15119	14877
55°	14639	14450	14233
60°	13932	13652	13435
65°	12877	12620	12510
70°	11275	11366	11321
75°	9072	10034	10093
80°	6447	8506	8597
85°	3924	7135	7135



TEST NUMBER: P562873

CATALOG NUMBER: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	516.8	3.5
10°-20°	1483.0	10.0
20°-30°	2245.9	15.1
30°-40°	2692.5	18.1
40°-50°	2745.4	18.4
50°-60°	2396.6	16.1
60°-70°	1715.7	11.5
70°-80°	883.7	5.9
80°-90°	223.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4245.7	28.5
0°-40°	6938.1	46.6
0°-60°	12080.1	81.1
0°-90°	14903.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14903.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5461	5461	5461	5461	5461	
5°	5481	5426	5445	5430	5425	520
15°	5274	5229	5274	5273	5268	1487
25°	4869	4834	4904	4889	4889	2241
35°	4282	4273	4348	4318	4318	2678
45°	3570	3560	3595	3549	3539	2748
55°	2730	2696	2695	2654	2654	2434
65°	1770	1730	1734	1719	1719	1750
75°	764	798	844	849	849	825
85°	111	171	202	207	202	156
90°	0	0	0	0	0	



TEST NUMBER: P562873

CATALOG NUMBER: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5460.6	5460.6	5460.6	5460.6	5460.6
2.5°	5493.0	5445.5	5460.6	5448.0	5428.2
5°	5480.8	5426.4	5445.4	5430.1	5425.2
7.5°	5441.4	5387.0	5412.1	5401.8	5396.9
10°	5405.0	5350.6	5379.7	5369.5	5364.5
12.5°	5356.4	5306.0	5339.2	5329.1	5328.1
15°	5273.5	5229.0	5273.5	5273.4	5268.5
17.5°	5169.4	5128.8	5176.4	5179.4	5176.4
20°	5096.6	5052.1	5111.7	5106.8	5111.7
22.5°	5007.6	4971.0	5034.9	5021.8	5026.8
25°	4869.0	4834.4	4904.4	4889.3	4889.3
27.5°	4705.2	4680.5	4756.8	4740.6	4740.6
30°	4596.0	4571.3	4651.6	4631.4	4631.4
32.5°	4474.7	4457.8	4534.3	4510.0	4510.0
35°	4282.5	4272.6	4348.3	4317.9	4317.9
37.5°	4084.3	4075.4	4144.0	4107.3	4095.4
40°	3938.7	3933.8	3994.3	3953.9	3953.9
42.5°	3793.1	3788.1	3840.6	3792.1	3792.1
45°	3569.6	3559.7	3594.9	3549.2	3539.3
47.5°	3325.9	3316.0	3338.0	3288.4	3283.4
50°	3160.1	3150.2	3160.1	3114.4	3109.5
52.5°	2990.2	2972.4	2974.0	2928.5	2927.5
55°	2730.3	2695.7	2694.9	2654.5	2654.5
57.5°	2455.2	2409.8	2413.8	2379.3	2374.3
60°	2265.1	2215.7	2219.6	2189.2	2184.2
62.5°	2079.1	2021.7	2033.6	1999.2	1998.2
65°	1769.6	1730.1	1734.2	1719.1	1719.1
67.5°	1472.3	1435.8	1462.2	1450.1	1449.1
70°	1253.9	1229.2	1264.0	1263.9	1259.0
72.5°	1051.7	1050.7	1094.1	1094.2	1097.2
75°	763.5	798.1	844.4	849.4	849.4
77.5°	509.7	571.0	621.9	623.9	622.9
80°	364.0	433.3	480.3	490.3	485.4
82.5°	246.7	319.9	359.0	369.0	364.0
85°	111.2	170.6	202.2	207.2	202.2
87.5°	32.4	68.0	80.9	80.7	72.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)