

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563979

Luminaire Tested: **SQ4-PR1-050U-075D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563979
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-075D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7347.0 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 58.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563979
CATALOG NUMBER: SQ4-PR1-050U-075D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563979

CATALOG NUMBER: SQ4-PR1-050U-075D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	86	83	78	76	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40	37
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	25	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10647	10647	10647
5°	10743	10660	10605
10°	10709	10635	10578
15°	10662	10595	10538
20°	10608	10540	10462
25°	10534	10462	10341
30°	10420	10346	10198
35°	10266	10177	10031
40°	10032	9924	9744
45°	9623	9454	9260
50°	8902	8689	8517
55°	7770	7594	7435
60°	6548	6493	6365
65°	5663	5685	5641
70°	5201	5228	5228
75°	4995	4995	5031
80°	4700	4754	4700
85°	3790	4206	4206



TEST NUMBER: P563979

CATALOG NUMBER: SQ4-PR1-050U-075D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.7	2.2
10°-20°	468.3	6.4
20°-30°	706.4	9.6
30°-40°	841.7	11.5
40°-50°	829.8	11.3
50°-60°	634.2	8.6
60°-70°	392.4	5.3
70°-80°	222.9	3.0
80°-90°	69.6	0.9
90°-100°	221.9	3.0
100°-110°	602.8	8.2
110°-120°	619.7	8.4
120°-130°	495.5	6.7
130°-140°	389.3	5.3
140°-150°	298.5	4.1
150°-160°	214.7	2.9
160°-170°	131.3	1.8
170°-180°	44.2	0.6
0°-30°	1338.4	18.2
0°-40°	2180.1	29.7
0°-60°	3644.1	49.6
0°-90°	4329.0	58.9
90°-120°	1444.4	19.7
90°-150°	2627.7	35.8
90°-180°	3018.0	41.1
0°-180°	7347.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1731	1731	1731	1731	1731	
5°	1740	1721	1726	1720	1718	165
15°	1674	1657	1664	1658	1655	472
25°	1552	1533	1542	1525	1524	714
35°	1367	1351	1355	1337	1336	853
45°	1106	1092	1087	1067	1064	848
55°	725	713	708	696	693	649
65°	389	386	391	388	388	394
75°	210	210	210	212	212	222
85°	54	57	60	60	60	62
90°	2	6	10	13	13	4
95°	33	121	386	168	113	35
105°	107	167	663	1009	950	114
115°	190	231	531	1056	1202	188
125°	262	298	480	809	954	233
135°	315	350	467	659	743	244
145°	364	390	461	560	602	229
155°	412	426	458	503	517	190
165°	446	452	459	479	480	126
175°	462	464	461	467	465	44
180°	462	462	462	462	462	

TEST NUMBER: P563979

CATALOG NUMBER: SQ4-PR1-050U-075D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1731.0	1731.0	1731.0	1731.0	1731.0
2.5°	1741.7	1726.6	1731.0	1727.2	1719.1
5°	1739.9	1721.0	1726.5	1720.5	1717.6
7.5°	1726.5	1707.9	1713.4	1707.4	1705.6
10°	1714.6	1697.1	1702.7	1696.6	1693.7
12.5°	1701.5	1682.8	1689.5	1682.3	1679.4
15°	1674.3	1656.8	1663.9	1657.9	1654.9
17.5°	1644.5	1625.9	1632.9	1625.9	1622.1
20°	1620.7	1603.2	1610.2	1599.7	1598.3
22.5°	1594.4	1576.9	1584.0	1570.0	1569.7
25°	1552.1	1533.1	1541.6	1525.2	1523.7
27.5°	1501.7	1484.2	1491.2	1474.5	1472.8
30°	1467.1	1449.6	1456.7	1438.7	1435.8
32.5°	1427.7	1411.4	1417.3	1399.4	1397.6
35°	1367.2	1351.2	1355.3	1337.3	1335.9
37.5°	1298.3	1283.7	1286.1	1266.4	1264.9
40°	1249.4	1234.8	1236.0	1215.1	1213.6
42.5°	1195.7	1181.2	1179.9	1159.0	1157.6
45°	1106.3	1091.7	1086.9	1067.4	1064.5
47.5°	1004.3	989.7	980.7	964.9	962.9
50°	930.3	915.8	908.0	894.5	890.1
52.5°	850.4	835.9	829.3	816.9	812.6
55°	724.6	712.9	708.2	696.2	693.3
57.5°	605.0	597.2	595.8	584.1	583.0
60°	532.3	527.9	527.8	517.4	517.4
62.5°	470.2	467.0	469.3	462.5	461.3
65°	389.1	386.2	390.6	387.6	387.6
67.5°	325.0	325.0	327.7	326.5	326.5
70°	289.2	289.2	290.7	290.7	290.7
72.5°	257.0	255.9	259.7	259.7	258.5
75°	210.2	210.2	210.2	211.7	211.7
77.5°	163.7	164.0	165.2	164.9	163.7
80°	132.7	134.2	134.2	132.7	132.7
82.5°	101.7	103.1	103.2	102.8	101.7
85°	53.7	56.6	59.6	59.6	59.6
87.5°	15.8	21.3	25.9	26.5	25.3
90°	1.5	5.8	10.4	13.4	13.4
92.5°	13.4	60.8	105.5	45.3	38.3
95°	32.7	121.3	386.4	168.2	113.0
97.5°	54.1	134.0	592.4	460.9	323.7
100°	68.4	142.5	655.4	664.4	536.5
102.5°	82.6	150.9	672.1	821.7	708.9
105°	107.0	166.6	662.9	1009.3	949.7
107.5°	132.3	184.9	624.5	1106.1	1122.7
110°	150.1	198.1	596.0	1125.2	1196.4



TEST NUMBER: P563979

CATALOG NUMBER: SQ4-PR1-050U-075D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.6	211.2	567.4	1109.4	1216.6
115°	190.2	230.9	530.6	1055.6	1202.4
117.5°	213.4	252.4	507.1	979.3	1144.7
120°	228.9	266.7	496.4	928.2	1092.4
122.5°	242.0	279.7	489.3	876.9	1035.3
125°	261.6	297.9	480.1	808.8	954.2
127.5°	279.1	315.2	475.0	757.2	881.9
130°	289.8	324.7	472.6	724.8	836.7
132.5°	300.5	335.4	470.2	697.2	796.3
135°	315.1	350.0	466.7	658.8	743.1
137.5°	330.8	362.5	464.9	624.9	695.9
140°	340.3	370.9	463.7	603.4	667.3
142.5°	349.9	378.0	462.5	586.5	640.0
145°	364.1	390.3	460.7	559.8	601.9
147.5°	380.2	402.6	459.2	538.8	571.9
150°	390.9	409.8	459.2	526.7	552.9
152.5°	399.2	415.8	458.1	515.9	537.4
155°	411.7	426.2	457.8	502.7	517.2
157.5°	423.9	435.2	457.8	493.7	504.7
160°	431.0	441.2	457.8	487.7	496.4
162.5°	438.1	446.0	458.9	482.9	489.3
165°	445.9	451.7	459.2	478.6	480.1
167.5°	453.9	456.8	460.7	473.5	474.7
170°	456.3	459.2	460.7	471.1	471.1
172.5°	458.6	460.4	460.7	468.8	468.8
175°	462.2	463.7	460.7	466.6	465.2
177.5°	463.4	463.4	459.8	464.5	462.2
180°	462.2	462.2	462.2	462.2	462.2

(END OF REPORT)