

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564315

Luminaire Tested: **SQ4-PR1-100U-125D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564315
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-100U-125D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13424.4 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 107.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564315
CATALOG NUMBER: SQ4-PR1-100U-125D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564315

CATALOG NUMBER: SQ4-PR1-100U-125D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18053	18053	18053
5°	18215	18075	17981
10°	18158	18031	17937
15°	18078	17965	17869
20°	17987	17871	17739
25°	17860	17740	17535
30°	17668	17542	17291
35°	17407	17255	17008
40°	17010	16828	16523
45°	16317	16031	15701
50°	15095	14732	14441
55°	13175	12877	12606
60°	11102	11009	10791
65°	9603	9639	9566
70°	8819	8866	8866
75°	8472	8472	8532
80°	7970	8058	7970
85°	6422	7135	7135



TEST NUMBER: P564315

CATALOG NUMBER: SQ4-PR1-100U-125D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.6	2.1
10°-20°	794.1	5.9
20°-30°	1197.8	8.9
30°-40°	1427.1	10.6
40°-50°	1407.0	10.5
50°-60°	1075.3	8.0
60°-70°	665.4	5.0
70°-80°	378.0	2.8
80°-90°	116.9	0.9
90°-100°	438.6	3.3
100°-110°	1210.8	9.0
110°-120°	1248.7	9.3
120°-130°	1003.5	7.5
130°-140°	788.6	5.9
140°-150°	604.8	4.5
150°-160°	434.7	3.2
160°-170°	265.8	2.0
170°-180°	89.6	0.7
0°-30°	2269.4	16.9
0°-40°	3696.6	27.5
0°-60°	6178.9	46.0
0°-90°	7339.3	54.7
90°-120°	2898.1	21.6
90°-150°	5295.0	39.4
90°-180°	6085.0	45.3
0°-180°	13424.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2935	2935	2935	2935	2935	
5°	2950	2918	2928	2917	2912	280
15°	2839	2809	2821	2811	2806	801
25°	2632	2600	2614	2586	2584	1211
35°	2318	2291	2298	2268	2265	1447
45°	1876	1851	1843	1810	1805	1437
55°	1229	1209	1201	1180	1176	1101
65°	660	655	662	657	657	668
75°	356	356	356	359	359	376
85°	91	96	101	101	101	106
90°	3	6	12	14	15	8
95°	64	237	796	327	213	69
105°	216	333	1332	2034	1915	230
115°	387	467	1073	2124	2416	380
125°	530	604	972	1646	1932	472
135°	638	707	946	1333	1503	494
145°	740	792	934	1135	1221	463
155°	835	862	926	1018	1050	385
165°	904	915	930	967	974	255
175°	936	938	932	946	942	89
180°	936	936	936	936	936	

TEST NUMBER: P564315

CATALOG NUMBER: SQ4-PR1-100U-125D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2935.1	2935.1	2935.1	2935.1	2935.1
2.5°	2953.3	2927.6	2935.1	2928.7	2914.8
5°	2950.2	2918.1	2927.5	2917.3	2912.3
7.5°	2927.5	2895.8	2905.2	2895.1	2892.1
10°	2907.3	2877.6	2887.0	2876.8	2871.9
12.5°	2885.0	2853.4	2864.8	2852.5	2847.6
15°	2839.0	2809.3	2821.3	2811.1	2806.1
17.5°	2788.4	2756.8	2768.7	2756.9	2750.5
20°	2748.0	2718.3	2730.3	2712.5	2710.1
22.5°	2703.5	2673.8	2685.8	2662.0	2661.5
25°	2631.7	2599.6	2614.0	2586.1	2583.7
27.5°	2546.2	2516.6	2528.6	2500.2	2497.2
30°	2487.6	2457.9	2469.9	2439.5	2434.5
32.5°	2420.9	2393.2	2403.2	2372.8	2369.8
35°	2318.2	2291.0	2298.0	2267.6	2265.1
37.5°	2201.4	2176.7	2180.7	2147.3	2144.8
40°	2118.5	2093.8	2095.8	2060.3	2057.8
42.5°	2027.5	2002.8	2000.7	1965.2	1962.8
45°	1875.8	1851.1	1842.9	1810.0	1805.0
47.5°	1702.9	1678.2	1662.9	1636.1	1632.6
50°	1577.5	1552.8	1539.6	1516.7	1509.2
52.5°	1442.0	1417.3	1406.1	1385.2	1377.8
55°	1228.6	1208.9	1200.8	1180.5	1175.5
57.5°	1025.9	1012.5	1010.2	990.4	988.5
60°	902.5	895.1	894.9	877.2	877.2
62.5°	797.3	791.9	795.8	784.2	782.2
65°	659.8	654.9	662.3	657.3	657.3
67.5°	551.1	551.1	555.7	553.6	553.6
70°	490.4	490.4	493.0	493.0	493.0
72.5°	435.8	433.9	440.4	440.3	438.4
75°	356.5	356.5	356.5	359.0	359.0
77.5°	277.6	278.1	280.1	279.6	277.6
80°	225.0	227.5	227.5	225.0	225.0
82.5°	172.4	174.9	174.9	174.4	172.4
85°	91.0	96.0	101.1	101.1	101.1
87.5°	26.9	35.4	42.8	43.1	41.4
90°	3.0	5.9	12.0	13.5	15.0
92.5°	27.0	112.0	200.2	73.1	56.9
95°	64.4	237.3	795.7	327.1	212.8
97.5°	106.7	265.8	1178.7	907.5	657.2
100°	137.9	282.9	1320.1	1329.5	1080.4
102.5°	167.8	302.3	1347.7	1642.6	1406.4
105°	215.8	333.0	1332.1	2033.7	1915.0
107.5°	266.7	371.0	1257.8	2222.3	2265.7
110°	302.7	396.5	1200.3	2262.9	2403.5



TEST NUMBER: P564315

CATALOG NUMBER: SQ4-PR1-100U-125D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	335.1	425.3	1146.3	2230.8	2438.3
115°	386.6	467.2	1072.9	2123.9	2415.5
117.5°	431.6	511.8	1024.6	1973.5	2305.2
120°	461.5	540.6	1005.5	1871.7	2205.7
122.5°	490.3	565.9	989.9	1776.6	2093.0
125°	530.5	603.7	972.5	1645.8	1931.5
127.5°	564.6	637.9	962.3	1535.2	1781.7
130°	587.4	660.7	957.5	1467.6	1691.8
132.5°	609.0	678.7	952.7	1410.8	1613.8
135°	638.3	707.2	945.5	1333.0	1502.9
137.5°	671.3	734.0	941.9	1267.7	1412.7
140°	689.3	750.8	939.5	1224.1	1351.6
142.5°	709.7	766.5	937.1	1185.4	1297.7
145°	740.2	791.5	933.5	1134.8	1221.2
147.5°	769.6	814.4	930.2	1092.1	1159.2
150°	791.2	827.8	929.0	1066.6	1120.8
152.5°	808.0	842.2	927.8	1044.8	1089.7
155°	834.6	862.5	926.0	1018.2	1050.4
157.5°	859.2	880.6	926.3	998.8	1020.7
160°	873.6	892.6	927.5	987.8	1004.0
162.5°	885.6	902.3	928.7	978.2	990.8
165°	903.6	915.3	930.5	966.7	974.0
167.5°	917.4	924.4	932.0	959.7	962.0
170°	924.5	930.4	932.0	956.0	956.0
172.5°	930.5	934.1	932.0	951.2	950.0
175°	936.5	938.0	932.0	945.5	942.5
177.5°	938.9	937.8	931.7	940.1	937.7
180°	936.5	936.5	936.5	936.5	936.5

(END OF REPORT)