

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563353

Luminaire Tested: **SQ4-PP3-050U-125D-840-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563353
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-125D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20801.5 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 167
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563353

CATALOG NUMBER: SQ4-PP3-050U-125D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563353

CATALOG NUMBER: SQ4-PP3-050U-125D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60
2	94	86	80	75	89	82	76	72	74	69	66	66	63	60	59	57	55	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	43
4	79	68	59	53	74	64	57	51	58	52	48	53	48	44	47	44	40	37
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	29
7	62	49	41	35	58	47	39	34	43	37	32	39	34	30	35	31	28	25
8	57	45	37	31	54	43	35	30	39	33	29	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	25	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17738	17738	17738
5°	17868	17759	17696
10°	17838	17712	17633
15°	17720	17623	17527
20°	17602	17503	17371
25°	17393	17273	17101
30°	17071	16981	16766
35°	16625	16511	16302
40°	16093	15992	15809
45°	15653	15543	15389
50°	15092	14995	14850
55°	14311	14121	14013
60°	13027	12654	12592
65°	11477	10998	10962
70°	9909	9500	9500
75°	8529	8409	8289
80°	7520	7610	7431
85°	5886	6422	6422



TEST NUMBER: P563353

CATALOG NUMBER: SQ4-PP3-050U-125D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	545.4	2.6
10°-20°	1557.3	7.5
20°-30°	2332.6	11.2
30°-40°	2736.0	13.2
40°-50°	2744.5	13.2
50°-60°	2341.3	11.3
60°-70°	1526.9	7.3
70°-80°	766.1	3.7
80°-90°	215.6	1.0
90°-100°	443.8	2.1
100°-110°	1205.5	5.8
110°-120°	1239.5	6.0
120°-130°	991.0	4.8
130°-140°	778.7	3.7
140°-150°	597.1	2.9
150°-160°	429.4	2.1
160°-170°	262.6	1.3
170°-180°	88.5	0.4
0°-30°	4435.2	21.3
0°-40°	7171.2	34.5
0°-60°	12257.0	58.9
0°-90°	14765.6	71.0
90°-120°	2888.8	13.9
90°-150°	5255.5	25.3
90°-180°	6036.0	29.0
0°-180°	20801.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5768	5768	5768	5768	5768	
5°	5788	5734	5752	5732	5732	550
15°	5566	5511	5535	5515	5505	1570
25°	5126	5066	5090	5045	5040	2357
35°	4428	4384	4398	4347	4342	2766
45°	3599	3574	3574	3538	3538	2771
55°	2669	2659	2634	2618	2613	2372
65°	1577	1548	1511	1501	1506	1574
75°	718	718	708	702	698	779
85°	167	182	182	182	182	196
90°	3	12	21	27	27	11
95°	65	243	773	336	226	69
105°	214	333	1326	2019	1899	227
115°	380	462	1061	2111	2405	375
125°	523	596	960	1618	1908	466
135°	630	700	933	1318	1486	487
145°	728	781	922	1120	1204	457
155°	823	852	916	1005	1034	380
165°	892	903	918	957	960	252
175°	924	927	922	933	930	88
180°	924	924	924	924	924	

TEST NUMBER: P563353

CATALOG NUMBER: SQ4-PP3-050U-125D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5767.7	5767.7	5767.7	5767.7	5767.7
2.5°	5804.0	5756.6	5767.7	5759.0	5735.3
5°	5787.9	5733.5	5752.5	5732.3	5732.3
7.5°	5748.4	5689.1	5708.0	5687.8	5686.8
10°	5712.0	5652.7	5671.6	5651.3	5646.3
12.5°	5659.5	5600.2	5623.1	5598.8	5597.8
15°	5565.5	5511.1	5535.1	5514.7	5504.8
17.5°	5459.3	5400.0	5429.0	5400.6	5396.6
20°	5378.4	5319.1	5348.1	5307.7	5307.7
22.5°	5281.4	5222.1	5255.1	5202.5	5202.5
25°	5125.7	5066.4	5090.3	5044.7	5039.7
27.5°	4940.7	4882.3	4907.3	4855.7	4854.7
30°	4807.2	4752.8	4781.9	4726.2	4721.3
32.5°	4661.6	4611.2	4632.3	4576.6	4571.7
35°	4428.1	4383.6	4397.8	4347.1	4342.2
37.5°	4182.4	4137.0	4153.1	4109.6	4107.6
40°	4008.5	3978.9	3983.3	3947.7	3937.8
42.5°	3846.8	3813.2	3817.5	3782.0	3780.1
45°	3599.1	3574.4	3573.8	3538.4	3538.4
47.5°	3336.2	3317.5	3312.0	3282.6	3281.6
50°	3154.3	3139.4	3134.0	3108.7	3103.7
52.5°	2964.2	2957.3	2939.9	2918.7	2917.7
55°	2669.0	2659.1	2633.6	2618.3	2613.4
57.5°	2348.5	2328.7	2300.0	2277.8	2281.8
60°	2118.0	2098.2	2057.3	2047.2	2047.2
62.5°	1895.6	1871.9	1830.9	1816.9	1824.8
65°	1577.1	1547.5	1511.4	1501.4	1506.4
67.5°	1288.0	1261.3	1222.3	1222.2	1218.2
70°	1102.0	1087.1	1056.5	1056.5	1056.5
72.5°	936.2	929.2	906.9	906.8	902.8
75°	717.8	717.8	707.7	702.5	697.6
77.5°	537.8	539.8	534.8	529.6	520.7
80°	424.6	434.5	429.7	424.5	419.6
82.5°	319.5	329.4	328.6	319.4	318.5
85°	166.8	181.6	182.0	182.0	182.0
87.5°	45.1	62.6	68.9	70.1	74.1
90°	3.0	11.7	20.8	26.8	26.8
92.5°	26.8	121.5	211.0	90.6	76.7
95°	65.4	242.7	772.8	336.3	225.9
97.5°	108.2	268.0	1184.8	921.8	647.4
100°	136.7	285.0	1310.9	1328.8	1073.1
102.5°	165.3	301.9	1344.1	1643.4	1417.9
105°	214.0	333.2	1325.7	2018.6	1899.4
107.5°	264.5	369.8	1249.0	2212.3	2245.4
110°	300.2	396.1	1192.0	2250.4	2392.8

TEST NUMBER: P563353

CATALOG NUMBER: SQ4-PP3-050U-125D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.1	422.4	1134.9	2218.8	2433.2
115°	380.5	461.9	1061.2	2111.2	2404.7
117.5°	426.8	504.7	1014.2	1958.6	2289.4
120°	457.8	533.3	992.8	1856.3	2184.8
122.5°	483.9	559.5	978.5	1753.8	2070.6
125°	523.2	595.8	960.1	1617.7	1908.3
127.5°	558.2	630.3	950.0	1514.5	1763.9
130°	579.6	649.4	945.2	1449.7	1673.5
132.5°	601.0	670.8	940.5	1394.4	1592.6
135°	630.2	699.9	933.4	1317.7	1486.2
137.5°	661.7	725.0	929.8	1249.9	1391.7
140°	680.7	741.7	927.4	1206.7	1334.6
142.5°	699.7	756.1	925.0	1173.0	1279.9
145°	728.3	780.6	921.5	1119.6	1203.8
147.5°	760.4	805.1	918.5	1077.5	1143.8
150°	781.8	819.5	918.5	1053.4	1105.8
152.5°	798.4	831.5	916.1	1031.8	1074.8
155°	823.4	852.4	915.5	1005.3	1034.4
157.5°	847.7	870.4	915.5	987.4	1009.4
160°	862.0	882.4	915.5	975.4	992.8
162.5°	876.3	892.0	917.9	965.7	978.5
165°	891.7	903.4	918.5	957.2	960.1
167.5°	907.8	913.6	921.5	947.1	949.4
170°	912.5	918.4	921.5	942.3	942.3
172.5°	917.3	920.8	921.5	937.5	937.5
175°	924.4	927.3	921.5	933.3	930.4
177.5°	926.8	926.8	919.7	929.1	924.4
180°	924.4	924.4	924.4	924.4	924.4

(END OF REPORT)