

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564747

Luminaire Tested: **SQ4-PW1-075U-075D-840-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564747
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-075U-075D-840-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8843.1 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564747
CATALOG NUMBER: SQ4-PW1-075U-075D-840-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564747

CATALOG NUMBER: SQ4-PW1-075U-075D-840-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41				41
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	39	35				35
3	81	72	64	59	74	66	60	55	56	51	48	47	43	40	38	36	34	29				29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25				25
5	68	57	49	43	63	52	45	40	45	39	35	37	33	30	31	28	25	22				22
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19				19
7	58	46	38	32	53	43	36	30	37	31	27	31	26	23	25	22	20	17				17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15				15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14				14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10408	10408	10408
5°	10476	10393	10347
10°	10392	10309	10252
15°	10282	10168	10130
20°	10159	10003	9983
25°	10017	9835	9805
30°	9805	9657	9594
35°	9527	9393	9337
40°	9230	9086	9051
45°	8871	8754	8715
50°	8503	8432	8375
55°	8106	8106	7978
60°	7611	7759	7483
65°	6966	7312	6792
70°	6140	6730	5980
75°	5245	6024	5102
80°	4066	5069	4119
85°	2632	3896	3472



TEST NUMBER: P564747

CATALOG NUMBER: SQ4-PW1-075U-075D-840-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.3	1.8
10°-20°	449.9	5.1
20°-30°	667.3	7.5
30°-40°	780.8	8.8
40°-50°	777.4	8.8
50°-60°	671.3	7.6
60°-70°	483.2	5.5
70°-80°	253.4	2.9
80°-90°	64.6	0.7
90°-100°	328.4	3.7
100°-110°	903.5	10.2
110°-120°	932.6	10.5
120°-130°	747.2	8.4
130°-140°	586.8	6.6
140°-150°	449.7	5.1
150°-160°	323.3	3.7
160°-170°	197.7	2.2
170°-180°	66.6	0.8
0°-30°	1276.6	14.4
0°-40°	2057.4	23.3
0°-60°	3506.1	39.6
0°-90°	4307.3	48.7
90°-120°	2164.4	24.5
90°-150°	3948.2	44.6
90°-180°	4536.0	51.3
0°-180°	8843.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1692	1692	1692	1692	1692	
5°	1697	1678	1683	1679	1676	161
15°	1615	1594	1597	1594	1591	455
25°	1476	1451	1449	1440	1445	679
35°	1269	1251	1251	1239	1244	793
45°	1020	1011	1006	1003	1002	787
55°	756	754	756	745	744	674
65°	479	493	502	483	467	474
75°	221	241	254	237	215	236
85°	37	49	55	52	49	49
90°	2	6	10	13	13	5
95°	49	179	581	248	158	52
105°	162	248	996	1516	1415	170
115°	286	348	798	1590	1804	282
125°	394	449	724	1226	1436	352
135°	476	528	704	991	1121	367
145°	550	587	693	844	910	345
155°	622	642	689	759	781	286
165°	673	681	692	720	724	190
175°	696	698	693	702	701	66
180°	696	696	696	696	696	

TEST NUMBER: P564747

CATALOG NUMBER: SQ4-PW1-075U-075D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1692.2	1692.2	1692.2	1692.2	1692.2
2.5°	1701.8	1687.8	1692.2	1688.5	1680.3
5°	1696.7	1677.7	1683.3	1678.7	1675.8
7.5°	1679.4	1661.9	1666.0	1661.2	1659.4
10°	1663.9	1646.4	1650.5	1644.4	1641.5
12.5°	1646.0	1627.3	1631.4	1625.4	1623.6
15°	1614.7	1594.3	1596.8	1593.8	1590.8
17.5°	1578.3	1557.6	1558.0	1553.3	1552.7
20°	1552.1	1530.2	1528.2	1522.3	1525.2
22.5°	1523.5	1500.4	1498.4	1490.1	1494.2
25°	1476.0	1451.3	1449.2	1440.4	1444.7
27.5°	1421.2	1396.7	1396.7	1384.3	1389.0
30°	1380.6	1357.3	1359.7	1345.0	1350.8
32.5°	1337.7	1316.7	1318.0	1303.2	1309.1
35°	1268.8	1251.3	1250.9	1239.1	1243.5
37.5°	1198.4	1183.0	1180.5	1173.7	1174.9
40°	1149.5	1136.4	1131.6	1127.2	1127.2
42.5°	1098.2	1086.3	1081.5	1078.2	1077.1
45°	1019.8	1011.1	1006.4	1003.4	1001.9
47.5°	942.3	934.1	930.1	927.9	926.5
50°	888.6	882.8	881.2	876.6	875.2
52.5°	834.9	831.4	829.9	824.2	822.7
55°	755.9	754.5	755.9	745.4	744.0
57.5°	673.6	675.9	680.8	666.7	663.2
60°	618.7	624.6	630.7	614.1	608.3
62.5°	562.7	572.0	580.6	561.6	553.4
65°	478.6	493.2	502.4	482.7	466.7
67.5°	397.5	415.6	426.7	405.4	387.3
70°	341.4	361.8	374.2	352.9	332.5
72.5°	292.5	315.3	325.3	305.2	284.8
75°	220.7	241.1	253.5	236.6	214.7
77.5°	156.5	175.8	186.1	171.3	153.3
80°	114.8	135.2	143.1	130.9	116.3
82.5°	81.4	98.3	103.8	96.4	86.5
85°	37.3	48.9	55.2	52.1	49.2
87.5°	9.8	18.9	24.7	25.4	26.5
90°	1.5	5.8	10.4	13.3	13.3
92.5°	20.4	87.4	151.4	58.1	47.7
95°	48.9	179.3	580.7	248.3	158.5
97.5°	79.7	198.8	886.2	682.8	481.8
100°	102.2	210.9	982.2	991.4	808.8
102.5°	123.5	225.2	1007.1	1229.9	1062.5
105°	161.5	248.4	995.5	1516.1	1414.7
107.5°	197.6	277.0	938.9	1656.3	1686.4
110°	223.7	296.1	896.3	1691.2	1795.5



TEST NUMBER: P564747

CATALOG NUMBER: SQ4-PW1-075U-075D-840-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	247.4	317.5	853.6	1668.7	1827.5
115°	285.9	348.2	798.5	1590.0	1804.4
117.5°	322.7	380.0	763.5	1479.5	1722.0
120°	345.2	400.2	748.1	1396.7	1647.3
122.5°	365.3	420.4	737.4	1324.2	1562.0
125°	394.1	449.1	724.4	1225.5	1435.5
127.5°	421.3	473.7	715.8	1143.1	1327.3
130°	435.5	489.1	711.1	1094.1	1262.2
132.5°	452.1	505.7	707.5	1051.1	1202.9
135°	475.5	527.7	703.7	991.1	1121.4
137.5°	497.5	545.8	700.4	942.5	1050.0
140°	514.0	559.0	699.2	910.3	1007.4
142.5°	528.3	569.7	696.9	881.5	964.7
145°	549.6	587.3	693.3	844.4	909.6
147.5°	572.4	604.9	691.5	811.5	863.7
150°	586.6	615.6	690.3	793.5	834.0
152.5°	599.7	626.3	689.2	777.9	811.5
155°	622.2	642.5	688.9	759.0	780.7
157.5°	638.5	655.0	688.9	743.4	758.5
160°	650.3	663.4	688.9	735.0	746.6
162.5°	659.8	670.5	690.0	727.9	737.1
165°	672.6	681.2	691.8	720.1	724.4
167.5°	681.4	688.1	693.3	713.5	714.6
170°	687.4	691.7	693.3	711.1	711.1
172.5°	692.1	694.1	693.3	707.5	706.3
175°	696.3	697.7	693.3	702.2	700.7
177.5°	697.4	697.4	692.7	699.8	697.4
180°	696.3	696.3	696.3	696.3	696.3

(END OF REPORT)