

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563761

Luminaire Tested: **SQ4-PP3-150U-050D-840-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563761
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-050D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24166.5 lumens
Efficiency: N/A
Efficacy: 143.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 168.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563761
CATALOG NUMBER: SQ4-PP3-150U-050D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563761

CATALOG NUMBER: SQ4-PP3-150U-050D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	26	24	23	18
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	29	25	25	21	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	32	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7098	7098	7098
5°	7150	7106	7081
10°	7138	7087	7055
15°	7091	7052	7013
20°	7043	7004	6951
25°	6960	6912	6843
30°	6831	6795	6709
35°	6652	6607	6523
40°	6439	6399	6326
45°	6263	6219	6158
50°	6038	6000	5942
55°	5726	5650	5607
60°	5213	5063	5039
65°	4593	4401	4387
70°	3965	3801	3801
75°	3413	3365	3316
80°	3009	3044	2974
85°	2354	2569	2569



TEST NUMBER: P563761

CATALOG NUMBER: SQ4-PP3-150U-050D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.2	0.9
10°-20°	623.1	2.6
20°-30°	933.4	3.9
30°-40°	1094.8	4.5
40°-50°	1098.2	4.5
50°-60°	936.8	3.9
60°-70°	611.0	2.5
70°-80°	306.5	1.3
80°-90°	90.7	0.4
90°-100°	1315.8	5.4
100°-110°	3557.5	14.7
110°-120°	3740.2	15.5
120°-130°	3038.1	12.6
130°-140°	2383.1	9.9
140°-150°	1829.1	7.6
150°-160°	1315.4	5.4
160°-170°	803.6	3.3
170°-180°	270.9	1.1
0°-30°	1774.7	7.3
0°-40°	2869.5	11.9
0°-60°	4904.5	20.3
0°-90°	5912.8	24.5
90°-120°	8613.5	35.6
90°-150°	15863.8	65.6
90°-180°	18254.0	75.5
0°-180°	24166.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2308	2308	2308	2308	2308	
5°	2316	2294	2302	2294	2294	220
15°	2227	2205	2215	2207	2203	628
25°	2051	2027	2037	2019	2017	943
35°	1772	1754	1760	1740	1738	1107
45°	1440	1430	1430	1416	1416	1109
55°	1068	1064	1054	1048	1046	949
65°	631	619	605	601	603	630
75°	287	287	283	281	279	312
85°	67	73	73	73	73	79
90°	6	18	40	43	40	16
95°	204	717	2188	1132	674	214
105°	661	1022	3947	5822	5583	696
115°	1164	1423	3273	6336	7153	1150
125°	1594	1826	2950	4978	5848	1421
135°	1911	2137	2871	4020	4550	1477
145°	2222	2388	2831	3441	3703	1390
155°	2508	2606	2807	3086	3188	1157
165°	2731	2757	2819	2929	2944	769
175°	2834	2831	2822	2858	2852	269
180°	2831	2831	2831	2831	2831	

TEST NUMBER: P563761

CATALOG NUMBER: SQ4-PP3-150U-050D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2307.9	2307.9	2307.9	2307.9	2307.9
2.5°	2322.4	2303.4	2307.9	2304.4	2294.9
5°	2316.0	2294.2	2301.8	2293.7	2293.7
7.5°	2300.2	2276.5	2284.0	2275.9	2275.5
10°	2285.6	2261.9	2269.4	2261.3	2259.3
12.5°	2264.6	2240.9	2250.0	2240.3	2239.9
15°	2227.0	2205.2	2214.8	2206.6	2202.7
17.5°	2184.5	2160.8	2172.4	2161.0	2159.4
20°	2152.1	2128.4	2140.0	2123.8	2123.8
22.5°	2113.3	2089.6	2102.8	2081.7	2081.7
25°	2051.0	2027.3	2036.8	2018.6	2016.6
27.5°	1977.0	1953.6	1963.6	1943.0	1942.6
30°	1923.6	1901.8	1913.4	1891.2	1889.2
32.5°	1865.3	1845.1	1853.6	1831.3	1829.3
35°	1771.9	1754.1	1759.7	1739.5	1737.5
37.5°	1673.6	1655.4	1661.8	1644.4	1643.6
40°	1604.0	1592.1	1593.9	1579.6	1575.7
42.5°	1539.3	1525.8	1527.5	1513.3	1512.6
45°	1440.1	1430.3	1430.0	1415.9	1415.9
47.5°	1335.0	1327.4	1325.3	1313.5	1313.1
50°	1262.1	1256.2	1254.1	1243.9	1241.9
52.5°	1186.1	1183.3	1176.4	1167.9	1167.5
55°	1068.0	1064.0	1053.8	1047.7	1045.7
57.5°	939.7	931.8	920.3	911.5	913.0
60°	847.5	839.6	823.2	819.2	819.2
62.5°	758.5	749.0	732.6	727.0	730.2
65°	631.1	619.2	604.8	600.8	602.8
67.5°	515.4	504.7	489.1	489.0	487.5
70°	440.9	435.0	422.7	422.7	422.7
72.5°	374.6	371.8	362.9	362.8	361.2
75°	287.2	287.2	283.2	281.1	279.1
77.5°	215.2	216.0	214.0	211.9	208.3
80°	169.9	173.9	171.9	169.9	167.9
82.5°	127.8	131.8	131.5	127.8	127.4
85°	66.7	72.7	72.8	72.8	72.8
87.5°	19.0	27.7	33.8	34.4	35.4
90°	6.1	18.0	39.6	42.6	39.6
92.5°	86.6	315.4	622.3	270.1	195.7
95°	204.2	716.7	2188.2	1132.4	673.5
97.5°	327.9	822.0	3410.8	2822.7	2073.0
100°	420.6	864.6	3791.2	3953.8	3196.9
102.5°	505.9	923.7	3925.3	4811.4	4245.3
105°	661.3	1021.9	3946.6	5821.5	5583.1
107.5°	805.2	1134.1	3774.1	6451.7	6530.9
110°	917.3	1215.3	3620.5	6620.9	6957.6

TEST NUMBER: P563761

CATALOG NUMBER: SQ4-PP3-150U-050D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1017.3	1296.2	3479.1	6587.1	7152.6
115°	1164.2	1423.4	3273.1	6336.2	7152.6
117.5°	1308.0	1551.2	3137.2	5952.8	6878.3
120°	1395.8	1634.2	3056.7	5677.7	6622.4
122.5°	1478.7	1712.3	3007.9	5382.9	6334.7
125°	1593.9	1826.3	2950.0	4978.2	5848.3
127.5°	1699.9	1928.2	2915.9	4647.9	5413.1
130°	1758.4	1993.9	2901.3	4443.8	5135.1
132.5°	1819.4	2052.4	2886.7	4259.7	4896.2
135°	1910.8	2137.3	2870.8	4019.6	4550.0
137.5°	2002.9	2216.8	2857.4	3824.8	4256.8
140°	2066.2	2265.9	2852.5	3699.3	4083.7
142.5°	2127.2	2314.9	2842.8	3586.1	3922.8
145°	2221.7	2388.5	2831.2	3440.6	3702.8
147.5°	2307.6	2455.4	2817.8	3308.7	3510.2
150°	2371.0	2502.1	2812.9	3237.1	3398.0
152.5°	2429.5	2543.9	2810.5	3170.6	3302.9
155°	2508.1	2606.5	2806.8	3086.4	3187.8
157.5°	2589.8	2658.4	2807.4	3027.7	3094.5
160°	2636.1	2692.8	2809.9	2990.7	3038.4
162.5°	2672.7	2719.8	2812.3	2961.2	2997.0
165°	2730.6	2757.4	2819.0	2929.0	2943.9
167.5°	2770.2	2788.7	2819.6	2901.4	2908.6
170°	2794.6	2803.6	2822.0	2889.1	2889.1
172.5°	2814.1	2815.9	2822.0	2874.4	2872.0
175°	2834.2	2831.3	2822.0	2858.5	2852.5
177.5°	2840.9	2833.8	2821.4	2845.7	2838.5
180°	2831.2	2831.2	2831.2	2831.2	2831.2

(END OF REPORT)