

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519485

Luminaire Tested: **SQ4-WB-125U-075D-840-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519485  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-125U-075D-840-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11354.9 lumens  
Efficiency: N/A  
Efficacy: 129.2 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 87.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519485  
CATALOG NUMBER: SQ4-WB-125U-075D-840-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P519485

CATALOG NUMBER: SQ4-WB-125U-075D-840-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				
1	95	91	87	84	85	82	79	77	66	64	62	51	50	49	37	36	36	30				
2	87	80	75	70	78	73	68	64	59	55	53	46	44	42	34	32	31	26				
3	80	71	65	59	72	65	59	54	52	48	45	41	38	36	31	29	28	23				
4	73	63	56	51	66	58	52	47	47	43	39	37	34	32	28	26	25	21				
5	68	57	49	44	61	52	45	41	42	38	34	34	31	28	26	24	22	18				
6	62	51	44	38	56	47	40	36	39	34	30	31	27	25	23	21	20	17				
7	58	46	39	34	52	43	36	32	35	30	27	28	25	22	22	19	18	15				
8	54	42	35	30	49	39	33	28	32	27	24	26	23	20	20	18	16	14				
9	50	39	32	27	45	36	29	25	30	25	22	24	21	18	19	16	15	13				
10	47	36	29	24	43	33	27	23	27	23	20	22	19	17	17	15	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15946	15946	15946
5°	15747	15691	15782
10°	14878	15013	15361
15°	13734	14053	14683
20°	12472	12941	13797
25°	11186	11797	12854
30°	10002	10656	11877
35°	8747	9378	10719
40°	7362	7947	9280
45°	6076	6600	7748
50°	5072	5530	6455
55°	4307	4745	5331
60°	3681	4114	4254
65°	2930	3461	2748
70°	2599	2701	1678
75°	2405	2189	1027
80°	2217	2015	886
85°	2004	1849	720



TEST NUMBER: P519485

CATALOG NUMBER: SQ4-WB-125U-075D-840-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	237.8	2.1
10°-20°	618.5	5.4
20°-30°	801.2	7.1
30°-40°	784.5	6.9
40°-50°	600.5	5.3
50°-60°	400.1	3.5
60°-70°	218.4	1.9
70°-80°	91.0	0.8
80°-90°	28.5	0.3
90°-100°	548.9	4.8
100°-110°	1478.5	13.0
110°-120°	1551.7	13.7
120°-130°	1259.2	11.1
130°-140°	987.5	8.7
140°-150°	758.2	6.7
150°-160°	545.1	4.8
160°-170°	333.0	2.9
170°-180°	112.3	1.0
0°-30°	1657.5	14.6
0°-40°	2442.0	21.5
0°-60°	3442.6	30.3
0°-90°	3780.5	33.3
90°-120°	3579.1	31.5
90°-150°	6584.0	58.0
90°-180°	7574.0	66.7
0°-180°	11354.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2592	2592	2592	2592	2592	
5°	2550	2525	2541	2547	2556	237
15°	2157	2149	2207	2267	2306	602
25°	1648	1653	1738	1814	1894	758
35°	1165	1170	1249	1333	1428	724
45°	698	712	759	816	891	545
55°	402	418	442	459	497	364
65°	201	218	238	208	189	209
75°	101	101	92	63	43	108
85°	28	28	26	17	10	31
90°	3	9	18	19	19	7
95°	84	298	900	460	318	87
105°	274	426	1635	2446	2296	288
115°	483	591	1362	2631	2976	475
125°	659	757	1223	2066	2432	589
135°	794	886	1188	1667	1888	613
145°	918	989	1173	1425	1530	576
155°	1042	1080	1163	1279	1320	480
165°	1130	1143	1167	1214	1220	319
175°	1175	1173	1169	1185	1182	112
180°	1173	1173	1173	1173	1173	

TEST NUMBER: P519485

CATALOG NUMBER: SQ4-WB-125U-075D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2592.5	2592.5	2592.5	2592.5	2592.5
2.5°	2598.9	2575.7	2581.6	2581.4	2574.3
5°	2550.4	2524.8	2541.3	2547.2	2556.1
7.5°	2455.8	2436.4	2466.5	2488.7	2506.7
10°	2382.1	2365.4	2403.7	2436.0	2459.4
12.5°	2296.5	2282.5	2330.0	2373.4	2403.9
15°	2156.8	2149.0	2206.9	2266.9	2305.8
17.5°	2007.3	2003.6	2069.9	2140.0	2189.8
20°	1905.4	1904.3	1977.1	2050.1	2107.9
22.5°	1802.6	1805.0	1881.5	1957.4	2023.3
25°	1648.3	1652.8	1738.2	1814.0	1894.0
27.5°	1505.7	1507.7	1596.0	1676.0	1761.4
30°	1408.3	1413.9	1500.4	1583.2	1672.2
32.5°	1310.9	1317.4	1402.2	1487.7	1578.5
35°	1164.9	1170.4	1249.0	1333.1	1427.6
37.5°	1014.2	1021.8	1091.6	1171.1	1264.1
40°	916.9	928.0	989.7	1064.6	1155.8
42.5°	823.1	836.9	894.1	965.2	1047.5
45°	698.5	711.8	758.8	816.2	890.7
47.5°	591.1	606.4	642.5	691.9	755.6
50°	530.1	544.6	577.9	614.5	674.6
52.5°	476.4	490.9	520.5	548.8	599.9
55°	401.6	418.2	442.5	459.3	497.1
57.5°	340.1	356.1	375.4	383.0	405.9
60°	299.2	317.0	334.4	333.6	345.8
62.5°	261.9	277.0	294.4	282.4	283.0
65°	201.3	218.0	237.8	207.7	188.8
67.5°	162.7	166.2	186.6	144.9	122.4
70°	144.5	144.5	150.2	112.2	93.3
72.5°	127.2	127.2	121.9	91.2	71.4
75°	101.2	101.2	92.1	63.2	43.2
77.5°	78.0	77.1	70.5	47.2	31.4
80°	62.6	62.6	56.9	37.3	25.0
82.5°	48.9	48.9	44.1	29.1	18.7
85°	28.4	28.4	26.2	16.9	10.2
87.5°	10.6	11.8	12.7	9.3	8.4
90°	3.0	8.8	17.9	19.4	19.4
92.5°	36.5	128.8	254.7	122.6	85.2
95°	83.7	298.5	899.8	460.1	318.4
97.5°	133.6	341.7	1411.3	1179.0	889.0
100°	171.9	359.0	1573.9	1646.7	1366.1
102.5°	209.0	383.2	1627.7	1997.0	1766.7
105°	273.5	425.5	1635.2	2446.3	2295.8
107.5°	334.5	470.1	1565.5	2677.2	2716.1
110°	375.2	503.8	1502.1	2748.9	2890.7



TEST NUMBER: P519485

CATALOG NUMBER: SQ4-WB-125U-075D-840-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	418.2	537.5	1441.2	2733.1	2966.0
115°	482.8	590.9	1361.6	2631.0	2975.9
117.5°	541.7	643.1	1300.1	2468.1	2852.1
120°	579.9	677.8	1269.0	2351.1	2745.7
122.5°	613.4	710.2	1246.3	2231.5	2624.9
125°	659.1	757.1	1222.6	2066.5	2431.8
127.5°	703.1	799.5	1207.7	1920.9	2247.1
130°	729.4	825.9	1201.7	1837.5	2123.9
132.5°	755.7	851.0	1195.7	1764.0	2027.1
135°	793.7	885.7	1188.3	1667.1	1887.8
137.5°	829.8	918.1	1184.4	1584.9	1766.1
140°	855.0	939.7	1180.8	1534.3	1697.9
142.5°	881.3	960.2	1178.4	1487.0	1625.0
145°	917.7	989.3	1173.3	1425.3	1530.5
147.5°	957.2	1019.4	1168.2	1373.4	1456.1
150°	983.5	1037.6	1165.8	1340.8	1409.5
152.5°	1007.4	1054.5	1164.6	1314.2	1370.0
155°	1041.8	1079.8	1162.9	1278.9	1319.8
157.5°	1072.0	1101.5	1163.2	1254.1	1281.5
160°	1091.1	1116.0	1164.3	1239.5	1260.0
162.5°	1107.8	1128.0	1165.5	1227.5	1242.1
165°	1130.0	1143.1	1167.3	1213.8	1219.7
167.5°	1147.9	1155.5	1168.8	1203.3	1205.6
170°	1159.9	1162.8	1168.8	1197.2	1197.2
172.5°	1167.0	1167.6	1170.0	1191.3	1191.3
175°	1174.8	1173.3	1168.8	1185.2	1182.3
177.5°	1178.1	1175.8	1169.7	1179.2	1176.9
180°	1173.3	1173.3	1173.3	1173.3	1173.3

(END OF REPORT)