

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519750

Luminaire Tested: **SQ4-125U-0D-840-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519750
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10099.3 lumens
Efficiency: N/A
Efficacy: 163.9 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Indirect

Input Watts (W): 61.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519750
CATALOG NUMBER: SQ4-125U-0D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519750

CATALOG NUMBER: SQ4-125U-0D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5907	63499	22469
100°	6089	55748	48390
105°	6500	38859	54560
110°	6747	27015	51986
115°	7026	19817	43312
120°	7134	15611	33776
125°	7069	13111	26078
130°	6979	11499	20324
135°	6904	10336	16421
140°	6864	9481	13633
145°	6891	8810	11492
150°	6985	8280	10011
155°	7070	7892	8957
160°	7142	7621	8247
165°	7195	7434	7766
170°	7244	7300	7477
175°	7254	7217	7300



TEST NUMBER: P519750

CATALOG NUMBER: SQ4-125U-0D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	731.8	7.2
100°-110°	1971.4	19.5
110°-120°	2068.9	20.5
120°-130°	1678.9	16.6
130°-140°	1316.7	13.0
140°-150°	1010.9	10.0
150°-160°	726.8	7.2
160°-170°	444.1	4.4
170°-180°	149.7	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	4772.2	47.3
90°-150°	8778.6	86.9
90°-180°	10099.0	100.0
0°-180°	10099.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	4	12	24	26	26	
95°	112	398	1200	614	424	124
105°	365	567	2180	3262	3061	383
115°	644	788	1816	3508	3968	633
125°	879	1009	1630	2755	3242	785
135°	1058	1181	1584	2223	2517	817
145°	1224	1319	1564	1900	2041	767
155°	1389	1440	1550	1705	1760	639
165°	1507	1524	1556	1618	1626	425
175°	1566	1564	1558	1580	1576	149
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P519750

CATALOG NUMBER: SQ4-125U-0D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	4.0	11.8	23.9	25.9	25.9
92.5°	48.6	171.8	339.6	163.5	113.6
95°	111.6	398.0	1199.7	613.5	424.5
97.5°	178.2	455.6	1881.7	1572.0	1185.4
100°	229.2	478.6	2098.5	2195.6	1821.5
102.5°	278.6	510.9	2170.3	2662.7	2355.6
105°	364.7	567.4	2180.2	3261.8	3061.1
107.5°	446.0	626.8	2087.4	3569.7	3621.5
110°	500.2	671.7	2002.9	3665.2	3854.3
112.5°	557.6	716.6	1921.5	3644.1	3954.7
115°	643.7	787.9	1815.5	3508.0	3967.9
117.5°	722.2	857.5	1733.4	3290.7	3802.8
120°	773.2	903.8	1692.0	3134.8	3660.9
122.5°	817.9	946.9	1661.7	2975.4	3499.9
125°	878.9	1009.4	1630.2	2755.3	3242.4
127.5°	937.5	1066.1	1610.3	2561.2	2996.1
130°	972.5	1101.1	1602.3	2450.0	2831.9
132.5°	1007.6	1134.7	1594.3	2352.0	2702.8
135°	1058.2	1181.0	1584.4	2222.8	2517.0
137.5°	1106.5	1224.2	1579.2	2113.2	2354.8
140°	1139.9	1253.0	1574.4	2045.7	2263.9
142.5°	1175.0	1280.2	1571.2	1982.7	2166.7
145°	1223.6	1319.1	1564.4	1900.4	2040.7
147.5°	1276.2	1359.3	1557.6	1831.2	1941.5
150°	1311.3	1383.4	1554.5	1787.7	1879.3
152.5°	1343.2	1406.0	1552.9	1752.3	1826.7
155°	1389.0	1439.7	1550.5	1705.2	1759.7
157.5°	1429.3	1468.7	1550.9	1672.1	1708.7
160°	1454.8	1487.9	1552.5	1652.7	1680.0
162.5°	1477.1	1504.0	1554.1	1636.6	1656.1
165°	1506.6	1524.2	1556.5	1618.4	1626.2
167.5°	1530.5	1540.7	1558.4	1604.4	1607.5
170°	1546.5	1550.4	1558.4	1596.3	1596.3
172.5°	1556.1	1556.8	1560.0	1588.3	1588.3
175°	1566.4	1564.5	1558.4	1580.3	1576.4
177.5°	1570.8	1567.7	1559.6	1572.3	1569.2
180°	1564.4	1564.4	1564.4	1564.4	1564.4

(END OF REPORT)