

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518502

Luminaire Tested: **SQ4-BB-075U-050D-840-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P518502  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-BB-075U-050D-840-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8582.3 lumens  
Efficiency: N/A  
Efficacy: 119.5 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 71.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P518502  
CATALOG NUMBER: SQ4-BB-075U-050D-840-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P518502

CATALOG NUMBER: SQ4-BB-075U-050D-840-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30
1	94	90	87	84	84	81	79	76	64	63	61	49	48	47	35	34	33	27
2	87	80	75	70	78	72	68	64	58	55	52	44	42	41	32	31	30	24
3	80	71	65	60	72	65	59	55	52	48	45	40	38	36	29	28	27	22
4	73	64	57	52	66	58	52	47	47	43	39	36	34	32	27	25	24	20
5	68	57	50	45	61	52	46	41	42	38	35	33	30	28	25	23	22	18
6	63	52	45	39	56	47	41	36	39	34	31	30	27	25	23	21	20	16
7	58	47	40	35	52	43	37	32	35	31	27	28	25	23	21	19	18	15
8	54	43	36	31	49	39	33	29	32	28	25	26	23	21	20	18	16	14
9	51	39	33	28	46	36	30	26	30	25	22	24	21	19	18	16	15	13
10	47	36	30	25	43	33	27	24	28	23	20	22	19	17	17	15	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9792	9792	9792
5°	9634	9611	9682
10°	9014	9135	9390
15°	8195	8455	8926
20°	7274	7652	8323
25°	6335	6837	7647
30°	5426	6022	7007
35°	4499	5112	6234
40°	3457	4088	5312
45°	2499	3095	4274
50°	1702	2307	3390
55°	1107	1668	2635
60°	635	1174	1904
65°	168	717	964
70°	84	221	277
75°	37	18	0
80°	27	0	0
85°	0	0	0



TEST NUMBER: P518502

CATALOG NUMBER: SQ4-BB-075U-050D-840-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	193.7	2.3
10°-20°	495.4	5.8
20°-30°	620.2	7.2
30°-40°	572.8	6.7
40°-50°	384.9	4.5
50°-60°	198.8	2.3
60°-70°	62.3	0.7
70°-80°	3.9	0.0
80°-90°	2.4	0.0
90°-100°	437.9	5.1
100°-110°	1204.6	14.0
110°-120°	1243.4	14.5
120°-130°	996.2	11.6
130°-140°	782.5	9.1
140°-150°	599.6	7.0
150°-160°	431.1	5.0
160°-170°	263.6	3.1
170°-180°	88.9	1.0
0°-30°	1309.3	15.3
0°-40°	1882.1	21.9
0°-60°	2465.8	28.7
0°-90°	2534.5	29.5
90°-120°	2885.9	33.6
90°-150°	5264.2	61.3
90°-180°	6048.0	70.5
0°-180°	8582.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2123	2123	2123	2123	2123	
5°	2080	2059	2075	2083	2091	193
15°	1716	1710	1770	1830	1869	478
25°	1245	1255	1343	1435	1502	571
35°	799	819	908	1015	1107	495
45°	383	406	474	567	655	301
55°	138	161	207	266	328	128
65°	15	30	66	79	88	26
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	2	8	14	18	18	4
95°	65	239	774	331	211	69
105°	215	331	1327	2022	1886	227
115°	381	464	1065	2120	2406	376
125°	525	599	966	1634	1914	469
135°	634	704	938	1321	1495	489
145°	733	783	924	1126	1213	460
155°	830	857	918	1012	1041	381
165°	897	908	922	960	966	253
175°	928	930	924	936	934	88
180°	928	928	928	928	928	

TEST NUMBER: P518502

CATALOG NUMBER: SQ4-BB-075U-050D-840-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2122.6	2122.6	2122.6	2122.6	2122.6
2.5°	2127.5	2107.5	2112.8	2112.6	2107.0
5°	2080.5	2059.4	2075.4	2082.8	2090.8
7.5°	1992.6	1976.1	2006.8	2029.8	2046.4
10°	1924.4	1910.4	1950.1	1981.4	2004.5
12.5°	1845.6	1834.7	1882.7	1925.7	1955.2
15°	1716.0	1709.9	1770.4	1829.8	1869.0
17.5°	1577.1	1576.9	1645.9	1719.7	1766.9
20°	1481.8	1484.8	1558.8	1640.2	1695.4
22.5°	1386.5	1393.6	1472.6	1557.4	1620.7
25°	1244.6	1254.7	1343.2	1435.1	1502.4
27.5°	1108.2	1122.9	1216.1	1311.6	1393.5
30°	1018.7	1035.8	1130.6	1231.1	1315.5
32.5°	930.8	951.1	1043.5	1149.8	1235.8
35°	798.9	819.0	907.8	1014.6	1107.0
37.5°	662.8	682.4	769.2	874.3	974.1
40°	574.0	596.1	678.8	780.7	882.1
42.5°	493.5	515.6	593.3	693.5	789.3
45°	383.0	406.1	474.4	566.8	655.2
47.5°	291.4	316.5	376.5	460.0	540.6
50°	237.2	262.3	321.4	395.1	472.4
52.5°	193.7	218.0	271.3	340.7	411.6
55°	137.6	160.7	207.4	266.3	327.6
57.5°	95.1	115.0	156.9	206.1	254.1
60°	68.8	87.9	127.3	167.2	206.4
62.5°	45.8	63.3	101.9	132.5	158.8
65°	15.4	29.5	65.7	79.3	88.3
67.5°	7.8	9.4	34.5	36.4	39.4
70°	6.2	6.2	16.4	17.5	20.5
72.5°	4.5	4.5	6.6	8.4	9.0
75°	2.1	2.1	1.0	0.0	0.0
77.5°	1.0	1.0	0.8	0.0	0.0
80°	1.0	1.0	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.4	1.6	2.8	3.6	3.6
90°	2.0	7.8	13.8	17.8	17.8
92.5°	27.3	116.5	201.9	77.5	63.6
95°	65.2	239.0	774.3	331.1	211.3
97.5°	106.3	265.0	1181.6	910.4	642.3
100°	136.3	281.1	1309.6	1321.8	1078.5
102.5°	164.7	300.3	1342.7	1639.9	1416.6
105°	215.3	331.2	1327.3	2021.5	1886.3
107.5°	263.5	369.3	1251.9	2208.4	2248.6
110°	298.3	394.8	1195.0	2254.9	2394.0



TEST NUMBER: P518502

CATALOG NUMBER: SQ4-BB-075U-050D-840-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	329.9	423.3	1138.1	2224.9	2436.6
115°	381.2	464.3	1064.6	2120.0	2405.8
117.5°	430.2	506.7	1018.0	1972.7	2296.0
120°	460.2	533.6	997.5	1862.3	2196.4
122.5°	487.1	560.5	983.3	1765.5	2082.7
125°	525.4	598.8	965.9	1633.9	1914.0
127.5°	561.7	631.7	954.4	1524.1	1769.8
130°	580.7	652.2	948.1	1458.8	1682.9
132.5°	602.8	674.3	943.4	1401.5	1603.9
135°	634.0	703.6	938.2	1321.4	1495.2
137.5°	663.3	727.8	933.9	1256.7	1400.0
140°	685.4	745.3	932.3	1213.7	1343.1
142.5°	704.4	759.6	929.1	1175.4	1286.3
145°	732.8	783.0	924.4	1125.9	1212.8
147.5°	763.2	806.5	922.0	1082.0	1151.5
150°	782.2	820.8	920.4	1058.0	1112.0
152.5°	799.6	835.1	918.9	1037.2	1082.0
155°	829.6	856.6	918.5	1012.0	1040.9
157.5°	851.3	873.3	918.5	991.2	1011.3
160°	867.1	884.5	918.5	980.1	995.5
162.5°	879.8	894.0	920.1	970.5	982.9
165°	896.7	908.3	922.4	960.1	965.9
167.5°	908.6	917.5	924.4	951.3	952.8
170°	916.5	922.3	924.4	948.1	948.1
172.5°	922.8	925.5	924.4	943.3	941.8
175°	928.3	930.3	924.4	936.2	934.3
177.5°	929.9	929.9	923.6	933.0	929.9
180°	928.3	928.3	928.3	928.3	928.3

(END OF REPORT)