

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562804

Luminaire Tested: **SQ4-PC3-0U-050D-840-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562804  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3975.5 lumens  
Efficiency: N/A  
Efficacy: 112.9 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562804  
CATALOG NUMBER: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P562804

CATALOG NUMBER: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6720	6720	6720
5°	6771	6727	6702
10°	6754	6722	6703
15°	6719	6719	6712
20°	6674	6694	6694
25°	6611	6659	6639
30°	6531	6610	6581
35°	6433	6532	6486
40°	6327	6416	6351
45°	6212	6256	6159
50°	6050	6050	5953
55°	5857	5782	5695
60°	5574	5463	5376
65°	5153	5050	5006
70°	4512	4548	4529
75°	3631	4014	4039
80°	2580	3403	3440
85°	1572	2858	2858



TEST NUMBER: P562804

CATALOG NUMBER: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.9	3.5
10°-20°	395.6	10.0
20°-30°	599.1	15.1
30°-40°	718.3	18.1
40°-50°	732.4	18.4
50°-60°	639.3	16.1
60°-70°	457.7	11.5
70°-80°	235.7	5.9
80°-90°	59.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1132.6	28.5
0°-40°	1850.8	46.6
0°-60°	3222.5	81.1
0°-90°	3975.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3975.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1457	1457	1457	1457	1457	
5°	1462	1448	1453	1448	1447	139
15°	1407	1395	1407	1407	1405	397
25°	1299	1290	1308	1304	1304	598
35°	1142	1140	1160	1152	1152	714
45°	952	950	959	947	944	733
55°	728	719	719	708	708	649
65°	472	462	463	459	459	467
75°	204	213	225	227	227	220
85°	30	46	54	55	54	41
90°	0	0	0	0	0	



TEST NUMBER: P562804

CATALOG NUMBER: SQ4-PC3-0U-050D-840-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1456.7	1456.7	1456.7	1456.7	1456.7
2.5°	1465.3	1452.6	1456.7	1453.3	1448.0
5°	1462.1	1447.6	1452.6	1448.5	1447.2
7.5°	1451.5	1437.0	1443.7	1441.0	1439.7
10°	1441.8	1427.3	1435.1	1432.4	1431.0
12.5°	1428.9	1415.4	1424.3	1421.6	1421.3
15°	1406.8	1394.9	1406.8	1406.7	1405.4
17.5°	1379.0	1368.2	1380.9	1381.7	1380.9
20°	1359.6	1347.7	1363.6	1362.3	1363.6
22.5°	1335.8	1326.1	1343.1	1339.6	1340.9
25°	1298.9	1289.6	1308.3	1304.3	1304.3
27.5°	1255.2	1248.6	1268.9	1264.6	1264.6
30°	1226.0	1219.4	1240.9	1235.5	1235.5
32.5°	1193.7	1189.2	1209.6	1203.1	1203.1
35°	1142.4	1139.8	1159.9	1151.8	1151.8
37.5°	1089.5	1087.2	1105.5	1095.7	1092.5
40°	1050.7	1049.4	1065.5	1054.7	1054.7
42.5°	1011.8	1010.5	1024.5	1011.6	1011.6
45°	952.2	949.6	959.0	946.8	944.1
47.5°	887.2	884.6	890.5	877.2	875.9
50°	843.0	840.3	843.0	830.8	829.5
52.5°	797.7	792.9	793.3	781.2	780.9
55°	728.3	719.1	718.9	708.1	708.1
57.5°	655.0	642.8	643.9	634.7	633.4
60°	604.2	591.1	592.1	584.0	582.7
62.5°	554.6	539.3	542.5	533.3	533.0
65°	472.1	461.5	462.6	458.6	458.6
67.5°	392.8	383.0	390.1	386.8	386.6
70°	334.5	327.9	337.2	337.2	335.8
72.5°	280.5	280.3	291.9	291.9	292.7
75°	203.7	212.9	225.2	226.6	226.6
77.5°	136.0	152.3	165.9	166.4	166.2
80°	97.1	115.6	128.1	130.8	129.5
82.5°	65.8	85.3	95.8	98.4	97.1
85°	29.7	45.5	54.0	55.3	54.0
87.5°	8.6	18.1	21.6	21.5	19.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)