

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562828

Luminaire Tested: **SQ4-PC3-0U-075D-840-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562828
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5859.5 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562828
CATALOG NUMBER: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562828

CATALOG NUMBER: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9904	9904	9904
5°	9979	9914	9877
10°	9955	9908	9880
15°	9902	9902	9893
20°	9837	9866	9866
25°	9744	9815	9784
30°	9625	9742	9699
35°	9482	9628	9561
40°	9326	9458	9362
45°	9156	9221	9079
50°	8917	8917	8774
55°	8634	8522	8394
60°	8217	8052	7923
65°	7595	7443	7378
70°	6649	6703	6676
75°	5351	5917	5953
80°	3802	5018	5069
85°	2313	4208	4208



TEST NUMBER: P562828

CATALOG NUMBER: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.2	3.5
10°-20°	583.1	10.0
20°-30°	883.0	15.1
30°-40°	1058.6	18.1
40°-50°	1079.4	18.4
50°-60°	942.3	16.1
60°-70°	674.6	11.5
70°-80°	347.5	5.9
80°-90°	87.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1669.3	28.5
0°-40°	2727.9	46.6
0°-60°	4749.6	81.1
0°-90°	5859.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5859.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2147	2147	2147	2147	2147	
5°	2155	2134	2141	2135	2133	205
15°	2073	2056	2073	2073	2071	585
25°	1914	1901	1928	1922	1922	881
35°	1684	1680	1710	1698	1698	1053
45°	1404	1400	1413	1395	1392	1080
55°	1074	1060	1060	1044	1044	957
65°	696	680	682	676	676	688
75°	300	314	332	334	334	324
85°	44	67	80	82	80	61
90°	0	0	0	0	0	



TEST NUMBER: P562828

CATALOG NUMBER: SQ4-PC3-0U-075D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2147.0	2147.0	2147.0	2147.0	2147.0
2.5°	2159.7	2141.0	2147.0	2142.0	2134.2
5°	2154.9	2133.5	2141.0	2135.0	2133.0
7.5°	2139.4	2118.0	2127.9	2123.9	2121.9
10°	2125.1	2103.7	2115.2	2111.1	2109.2
12.5°	2106.0	2086.2	2099.3	2095.3	2094.9
15°	2073.4	2055.9	2073.4	2073.4	2071.4
17.5°	2032.5	2016.5	2035.2	2036.4	2035.2
20°	2003.8	1986.3	2009.8	2007.9	2009.8
22.5°	1968.8	1954.5	1979.6	1974.5	1976.4
25°	1914.4	1900.8	1928.3	1922.3	1922.3
27.5°	1850.0	1840.2	1870.2	1863.9	1863.9
30°	1807.0	1797.3	1828.9	1820.9	1820.9
32.5°	1759.3	1752.7	1782.8	1773.2	1773.2
35°	1683.8	1679.9	1709.6	1697.7	1697.7
37.5°	1605.8	1602.4	1629.3	1614.9	1610.2
40°	1548.6	1546.7	1570.5	1554.6	1554.6
42.5°	1491.3	1489.4	1510.0	1490.9	1490.9
45°	1403.5	1399.6	1413.4	1395.4	1391.6
47.5°	1307.7	1303.8	1312.4	1292.9	1291.0
50°	1242.5	1238.6	1242.5	1224.5	1222.6
52.5°	1175.7	1168.7	1169.3	1151.4	1151.0
55°	1073.5	1059.9	1059.6	1043.7	1043.7
57.5°	965.3	947.5	949.0	935.5	933.5
60°	890.6	871.2	872.7	860.7	858.8
62.5°	817.4	794.9	799.5	786.0	785.6
65°	695.8	680.2	681.9	675.9	675.9
67.5°	578.9	564.5	574.9	570.1	569.7
70°	493.0	483.3	497.0	496.9	495.0
72.5°	413.5	413.1	430.2	430.2	431.4
75°	300.2	313.8	332.0	334.0	334.0
77.5°	200.4	224.5	244.5	245.3	244.9
80°	143.1	170.3	188.9	192.8	190.8
82.5°	97.0	125.8	141.1	145.1	143.1
85°	43.7	67.1	79.5	81.5	79.5
87.5°	12.7	26.7	31.8	31.7	28.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)