

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562526

Luminaire Tested: **SQ4-PC3-025U-050D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562526  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-025U-050D-940-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2545.4 lumens  
Efficiency: N/A  
Efficacy: 115.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 22.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562526  
CATALOG NUMBER: SQ4-PC3-025U-050D-940-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P562526

CATALOG NUMBER: SQ4-PC3-025U-050D-940-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	90	96	92	88	85	82	79	76	72	70	68	63	62	61	56
2	93	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	40	37	34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23
8	56	44	36	30	53	41	34	29	37	31	27	34	29	25	30	26	23	21
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5752	5752	5752
5°	5795	5757	5736
10°	5780	5753	5737
15°	5750	5750	5744
20°	5712	5729	5729
25°	5658	5700	5681
30°	5590	5657	5633
35°	5507	5591	5552
40°	5415	5492	5437
45°	5317	5355	5271
50°	5177	5177	5095
55°	5014	4948	4874
60°	4772	4676	4600
65°	4410	4323	4283
70°	3860	3893	3876
75°	3108	3436	3458
80°	2210	2912	2943
85°	1344	2445	2445



TEST NUMBER: P562526

CATALOG NUMBER: SQ4-PC3-025U-050D-940-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.0	2.3
10°-20°	169.3	6.7
20°-30°	256.4	10.1
30°-40°	307.4	12.1
40°-50°	313.4	12.3
50°-60°	273.6	10.7
60°-70°	195.8	7.7
70°-80°	100.9	4.0
80°-90°	26.2	1.0
90°-100°	63.4	2.5
100°-110°	166.7	6.5
110°-120°	172.9	6.8
120°-130°	138.7	5.4
130°-140°	108.8	4.3
140°-150°	83.5	3.3
150°-160°	60.2	2.4
160°-170°	36.8	1.4
170°-180°	12.4	0.5
0°-30°	484.7	19.0
0°-40°	792.0	31.1
0°-60°	1379.0	54.2
0°-90°	1702.0	66.9
90°-120°	403.0	15.8
90°-150°	734.0	28.8
90°-180°	843.0	33.1
0°-180°	2545.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	623	623	623	623	623	
5°	626	620	622	620	619	59
15°	602	597	602	602	601	170
25°	556	552	560	558	558	256
35°	489	488	496	493	493	306
45°	408	406	410	405	404	314
55°	312	308	308	303	303	278
65°	202	198	198	196	196	200
75°	87	91	96	97	97	94
85°	13	20	23	24	23	17
90°	1	2	7	3	3	1
95°	8	33	109	56	38	9
105°	30	46	184	280	261	32
115°	53	65	148	295	336	53
125°	74	83	134	227	268	66
135°	88	97	130	183	208	68
145°	103	109	128	156	168	64
155°	116	119	128	141	145	53
165°	125	127	128	134	135	35
175°	130	130	129	131	131	12
180°	130	130	130	130	130	

TEST NUMBER: P562526

CATALOG NUMBER: SQ4-PC3-025U-050D-940-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	623.4	623.4	623.4	623.4	623.4
2.5°	627.1	621.6	623.4	621.9	619.7
5°	625.7	619.5	621.6	619.9	619.3
7.5°	621.2	615.0	617.8	616.7	616.1
10°	617.0	610.8	614.1	613.0	612.4
12.5°	611.5	605.7	609.5	608.3	608.2
15°	602.0	596.9	602.0	602.0	601.4
17.5°	590.1	585.5	590.9	591.3	590.9
20°	581.8	576.7	583.5	583.0	583.5
22.5°	571.6	567.5	574.8	573.3	573.8
25°	555.8	551.9	559.9	558.1	558.1
27.5°	537.1	534.3	543.0	541.2	541.2
30°	524.7	521.8	531.0	528.7	528.7
32.5°	510.8	508.9	517.6	514.8	514.8
35°	488.9	487.7	496.4	492.9	492.9
37.5°	466.2	465.2	473.1	468.9	467.5
40°	449.6	449.1	456.0	451.4	451.4
42.5°	433.0	432.4	438.4	432.9	432.9
45°	407.5	406.4	410.4	405.2	404.0
47.5°	379.7	378.5	381.1	375.4	374.8
50°	360.7	359.6	360.7	355.5	355.0
52.5°	341.3	339.3	339.5	334.3	334.2
55°	311.7	307.7	307.6	303.0	303.0
57.5°	280.3	275.1	275.5	271.6	271.0
60°	258.6	252.9	253.4	249.9	249.3
62.5°	237.3	230.8	232.1	228.2	228.1
65°	202.0	197.5	198.0	196.2	196.2
67.5°	168.1	163.9	166.9	165.5	165.4
70°	143.1	140.3	144.3	144.3	143.7
72.5°	120.1	119.9	124.9	124.9	125.2
75°	87.2	91.1	96.4	97.0	97.0
77.5°	58.2	65.2	71.0	71.2	71.1
80°	41.6	49.5	54.8	56.0	55.4
82.5°	28.2	36.5	41.0	42.1	41.6
85°	12.7	19.5	23.1	23.7	23.1
87.5°	3.9	8.3	10.6	9.9	9.0
90°	0.8	2.5	6.7	3.3	3.3
92.5°	3.5	16.9	37.4	16.5	10.7
95°	8.3	32.8	109.3	56.3	38.4
97.5°	14.5	36.0	163.5	130.0	95.8
100°	19.2	38.8	180.2	182.6	141.8
102.5°	23.2	41.5	184.8	227.4	192.5
105°	30.0	45.5	184.3	279.8	261.1
107.5°	37.0	51.4	173.8	307.1	311.6
110°	41.7	54.8	165.2	314.1	333.7

TEST NUMBER: P562526

CATALOG NUMBER: SQ4-PC3-025U-050D-940-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	46.4	58.8	157.2	309.6	339.7
115°	53.4	64.8	147.6	294.6	336.2
117.5°	60.2	70.7	141.1	273.6	319.8
120°	64.2	74.0	138.5	259.6	304.5
122.5°	68.2	78.0	136.5	245.6	289.8
125°	74.2	83.2	134.3	227.0	267.8
127.5°	79.1	88.2	132.5	212.0	246.4
130°	81.7	91.5	131.8	202.6	234.4
132.5°	84.4	94.2	131.1	194.5	223.0
135°	88.4	97.4	130.1	183.2	207.7
137.5°	92.6	101.4	130.0	174.8	194.9
140°	95.9	104.1	129.3	168.1	186.8
142.5°	98.6	106.1	129.3	163.4	179.5
145°	102.6	109.1	128.5	156.3	168.5
147.5°	106.6	113.0	128.5	150.4	160.5
150°	109.3	115.0	128.5	147.0	155.1
152.5°	111.9	116.3	128.5	144.3	150.5
155°	115.9	119.2	128.5	141.1	145.1
157.5°	118.9	122.0	128.5	138.2	141.1
160°	120.9	123.4	128.5	136.8	138.5
162.5°	123.0	124.7	128.5	135.5	137.1
165°	125.1	126.8	128.5	133.5	135.1
167.5°	127.1	127.9	129.3	132.6	133.3
170°	128.5	129.3	129.3	132.6	132.6
172.5°	129.1	129.3	129.3	131.9	131.3
175°	130.1	130.1	129.3	131.0	131.0
177.5°	130.1	130.1	129.5	130.8	130.1
180°	130.1	130.1	130.1	130.1	130.1

(END OF REPORT)