

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562910

Luminaire Tested: **SQ4-PC3-100U-050D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562910
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5174.4 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 41.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562910
CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562910

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	39	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	35	30	27	28	24	21	20	18	16	13
7	55	43	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5752	5752	5752
5°	5795	5757	5736
10°	5780	5753	5737
15°	5750	5750	5744
20°	5712	5729	5729
25°	5658	5700	5681
30°	5590	5657	5633
35°	5507	5591	5552
40°	5415	5492	5437
45°	5317	5355	5271
50°	5177	5177	5095
55°	5014	4948	4874
60°	4772	4676	4600
65°	4410	4323	4283
70°	3860	3893	3876
75°	3108	3436	3458
80°	2210	2912	2943
85°	1344	2445	2445



TEST NUMBER: P562910

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.0	1.1
10°-20°	169.3	3.3
20°-30°	256.4	5.0
30°-40°	307.4	5.9
40°-50°	313.4	6.1
50°-60°	273.6	5.3
60°-70°	195.8	3.8
70°-80°	100.9	1.9
80°-90°	26.6	0.5
90°-100°	250.2	4.8
100°-110°	690.9	13.4
110°-120°	712.5	13.8
120°-130°	572.6	11.1
130°-140°	450.0	8.7
140°-150°	345.1	6.7
150°-160°	248.0	4.8
160°-170°	151.7	2.9
170°-180°	51.1	1.0
0°-30°	484.7	9.4
0°-40°	792.0	15.3
0°-60°	1379.0	26.7
0°-90°	1702.4	32.9
90°-120°	1653.6	32.0
90°-150°	3021.2	58.4
90°-180°	3472.0	67.1
0°-180°	5174.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	623	623	623	623	623	
5°	626	620	622	620	619	59
15°	602	597	602	602	601	170
25°	556	552	560	558	558	256
35°	489	488	496	493	493	306
45°	408	406	410	405	404	314
55°	312	308	308	303	303	278
65°	202	198	198	196	196	200
75°	87	91	96	97	97	94
85°	13	20	23	24	23	17
90°	2	3	7	8	8	3
95°	37	135	454	187	121	39
105°	123	190	760	1160	1093	131
115°	221	267	612	1212	1378	217
125°	303	344	555	939	1102	269
135°	364	404	540	761	858	282
145°	422	452	533	648	697	264
155°	476	492	528	581	599	219
165°	516	522	531	552	556	145
175°	534	535	532	540	538	51
180°	534	534	534	534	534	

TEST NUMBER: P562910

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	623.4	623.4	623.4	623.4	623.4
2.5°	627.1	621.6	623.4	621.9	619.7
5°	625.7	619.5	621.6	619.9	619.3
7.5°	621.2	615.0	617.8	616.7	616.1
10°	617.0	610.8	614.1	613.0	612.4
12.5°	611.5	605.7	609.5	608.3	608.2
15°	602.0	596.9	602.0	602.0	601.4
17.5°	590.1	585.5	590.9	591.3	590.9
20°	581.8	576.7	583.5	583.0	583.5
22.5°	571.6	567.5	574.8	573.3	573.8
25°	555.8	551.9	559.9	558.1	558.1
27.5°	537.1	534.3	543.0	541.2	541.2
30°	524.7	521.8	531.0	528.7	528.7
32.5°	510.8	508.9	517.6	514.8	514.8
35°	488.9	487.7	496.4	492.9	492.9
37.5°	466.2	465.2	473.1	468.9	467.5
40°	449.6	449.1	456.0	451.4	451.4
42.5°	433.0	432.4	438.4	432.9	432.9
45°	407.5	406.4	410.4	405.2	404.0
47.5°	379.7	378.5	381.1	375.4	374.8
50°	360.7	359.6	360.7	355.5	355.0
52.5°	341.3	339.3	339.5	334.3	334.2
55°	311.7	307.7	307.6	303.0	303.0
57.5°	280.3	275.1	275.5	271.6	271.0
60°	258.6	252.9	253.4	249.9	249.3
62.5°	237.3	230.8	232.1	228.2	228.1
65°	202.0	197.5	198.0	196.2	196.2
67.5°	168.1	163.9	166.9	165.5	165.4
70°	143.1	140.3	144.3	144.3	143.7
72.5°	120.1	119.9	124.9	124.9	125.2
75°	87.2	91.1	96.4	97.0	97.0
77.5°	58.2	65.2	71.0	71.2	71.1
80°	41.6	49.5	54.8	56.0	55.4
82.5°	28.2	36.5	41.0	42.1	41.6
85°	12.7	19.5	23.1	23.7	23.1
87.5°	4.0	8.4	10.6	10.8	10.0
90°	1.7	3.4	6.8	7.7	8.5
92.5°	15.4	63.9	114.2	41.7	32.5
95°	36.8	135.4	454.0	186.6	121.4
97.5°	60.9	151.7	672.5	517.8	375.0
100°	78.7	161.4	753.2	758.6	616.4
102.5°	95.8	172.5	769.0	937.3	802.5
105°	123.1	190.0	760.1	1160.4	1092.7
107.5°	152.2	211.7	717.7	1268.0	1292.7
110°	172.7	226.2	684.8	1291.1	1371.4



TEST NUMBER: P562910

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	191.2	242.7	654.1	1272.9	1391.2
115°	220.6	266.6	612.2	1211.9	1378.2
117.5°	246.2	292.0	584.6	1126.0	1315.3
120°	263.3	308.5	573.7	1067.9	1258.5
122.5°	279.8	322.9	564.8	1013.7	1194.2
125°	302.7	344.5	554.9	939.1	1102.1
127.5°	322.2	364.0	549.1	876.0	1016.6
130°	335.2	377.0	546.3	837.4	965.3
132.5°	347.5	387.3	543.6	805.0	920.8
135°	364.2	403.5	539.5	760.6	857.6
137.5°	383.0	418.8	537.4	723.3	806.1
140°	393.3	428.4	536.1	698.5	771.2
142.5°	404.9	437.4	534.7	676.4	740.4
145°	422.4	451.6	532.7	647.5	696.8
147.5°	439.1	464.7	530.8	623.1	661.4
150°	451.4	472.3	530.1	608.6	639.5
152.5°	461.0	480.6	529.4	596.2	621.7
155°	476.2	492.1	528.4	581.0	599.3
157.5°	490.2	502.5	528.6	569.9	582.4
160°	498.5	509.3	529.2	563.6	572.8
162.5°	505.3	514.8	529.9	558.1	565.3
165°	515.6	522.2	530.9	551.6	555.7
167.5°	523.4	527.4	531.8	547.6	548.9
170°	527.5	530.9	531.8	545.5	545.5
172.5°	530.9	533.0	531.8	542.7	542.1
175°	534.4	535.2	531.8	539.5	537.8
177.5°	535.7	535.1	531.6	536.4	535.0
180°	534.4	534.4	534.4	534.4	534.4

(END OF REPORT)