

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563668

Luminaire Tested: **SQ4-PP3-125U-050D-840-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563668  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 14040.8 lumens  
Efficiency: N/A  
Efficacy: 145.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 96.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563668  
CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563668

CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20
3	77	68	61	56	69	61	55	51	48	44	41	36	34	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	15	13	12	9
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7098	7098	7098
5°	7150	7106	7081
10°	7137	7087	7055
15°	7090	7052	7013
20°	7044	7004	6951
25°	6960	6912	6843
30°	6831	6795	6709
35°	6652	6607	6523
40°	6439	6399	6325
45°	6264	6220	6158
50°	6038	6000	5942
55°	5726	5650	5607
60°	5213	5063	5038
65°	4592	4401	4386
70°	3965	3801	3801
75°	3413	3365	3317
80°	3010	3044	2973
85°	2355	2567	2567



TEST NUMBER: P563668

CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	145.5	1.0
10°-20°	415.4	3.0
20°-30°	622.2	4.4
30°-40°	729.9	5.2
40°-50°	732.1	5.2
50°-60°	624.6	4.4
60°-70°	407.3	2.9
70°-80°	204.4	1.5
80°-90°	60.2	0.4
90°-100°	731.8	5.2
100°-110°	1971.4	14.0
110°-120°	2068.9	14.7
120°-130°	1678.9	12.0
130°-140°	1316.7	9.4
140°-150°	1010.9	7.2
150°-160°	726.8	5.2
160°-170°	444.1	3.2
170°-180°	149.7	1.1
0°-30°	1183.1	8.4
0°-40°	1913.0	13.6
0°-60°	3269.7	23.3
0°-90°	3941.6	28.1
90°-120°	4772.2	34.0
90°-150°	8778.6	62.5
90°-180°	10099.0	71.9
0°-180°	14040.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1544	1530	1534	1529	1529	147
15°	1485	1470	1477	1471	1468	419
25°	1367	1352	1358	1346	1344	629
35°	1181	1169	1173	1160	1158	738
45°	960	954	953	944	944	739
55°	712	709	702	698	697	633
65°	421	413	403	400	402	420
75°	192	192	189	187	186	208
85°	44	48	48	48	48	52
90°	4	12	24	26	26	9
95°	112	398	1200	614	424	117
105°	365	567	2180	3262	3061	383
115°	644	788	1816	3508	3968	633
125°	879	1009	1630	2755	3242	785
135°	1058	1181	1584	2223	2517	817
145°	1224	1319	1564	1900	2041	767
155°	1389	1440	1550	1705	1760	639
165°	1507	1524	1556	1618	1626	425
175°	1566	1564	1558	1580	1576	149
180°	1564	1564	1564	1564	1564	

TEST NUMBER: P563668

CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1548.3	1535.6	1538.6	1536.3	1530.0
5°	1544.0	1529.5	1534.5	1529.1	1529.1
7.5°	1533.5	1517.6	1522.7	1517.3	1517.0
10°	1523.7	1507.9	1513.0	1507.5	1506.2
12.5°	1509.7	1493.9	1500.0	1493.5	1493.3
15°	1484.6	1470.1	1476.6	1471.1	1468.5
17.5°	1456.3	1440.5	1448.2	1440.7	1439.6
20°	1434.8	1418.9	1426.7	1415.9	1415.9
22.5°	1408.9	1393.0	1401.8	1387.8	1387.8
25°	1367.3	1351.5	1357.9	1345.7	1344.4
27.5°	1318.0	1302.4	1309.1	1295.3	1295.1
30°	1282.4	1267.9	1275.6	1260.8	1259.5
32.5°	1243.5	1230.1	1235.7	1220.9	1219.5
35°	1181.2	1169.4	1173.2	1159.6	1158.3
37.5°	1115.7	1103.6	1107.9	1096.3	1095.7
40°	1069.3	1061.4	1062.6	1053.1	1050.4
42.5°	1026.2	1017.2	1018.3	1008.9	1008.4
45°	960.1	953.5	953.4	943.9	943.9
47.5°	890.0	885.0	883.5	875.7	875.4
50°	841.4	837.5	836.0	829.3	827.9
52.5°	790.7	788.9	784.3	778.6	778.3
55°	712.0	709.3	702.5	698.5	697.1
57.5°	626.5	621.2	613.5	607.6	608.7
60°	565.0	559.7	548.8	546.1	546.1
62.5°	505.7	499.3	488.4	484.7	486.8
65°	420.7	412.8	403.2	400.5	401.8
67.5°	343.6	336.5	326.1	326.0	325.0
70°	294.0	290.0	281.8	281.8	281.8
72.5°	249.7	247.9	241.9	241.9	240.8
75°	191.5	191.5	188.8	187.4	186.1
77.5°	143.5	144.0	142.7	141.3	138.9
80°	113.3	115.9	114.6	113.2	111.9
82.5°	85.2	87.9	87.6	85.2	85.0
85°	44.5	48.5	48.5	48.5	48.5
87.5°	12.7	18.4	22.0	22.5	23.5
90°	4.0	11.8	23.9	25.9	25.9
92.5°	48.6	171.8	339.6	163.5	113.6
95°	111.6	398.0	1199.7	613.5	424.5
97.5°	178.2	455.6	1881.7	1572.0	1185.4
100°	229.2	478.6	2098.5	2195.6	1821.5
102.5°	278.6	510.9	2170.3	2662.7	2355.6
105°	364.7	567.4	2180.2	3261.8	3061.1
107.5°	446.0	626.8	2087.4	3569.7	3621.5
110°	500.2	671.7	2002.9	3665.2	3854.3

TEST NUMBER: P563668

CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	557.6	716.6	1921.5	3644.1	3954.7
115°	643.7	787.9	1815.5	3508.0	3967.9
117.5°	722.2	857.5	1733.4	3290.7	3802.8
120°	773.2	903.8	1692.0	3134.8	3660.9
122.5°	817.9	946.9	1661.7	2975.4	3499.9
125°	878.9	1009.4	1630.2	2755.3	3242.4
127.5°	937.5	1066.1	1610.3	2561.2	2996.1
130°	972.5	1101.1	1602.3	2450.0	2831.9
132.5°	1007.6	1134.7	1594.3	2352.0	2702.8
135°	1058.2	1181.0	1584.4	2222.8	2517.0
137.5°	1106.5	1224.2	1579.2	2113.2	2354.8
140°	1139.9	1253.0	1574.4	2045.7	2263.9
142.5°	1175.0	1280.2	1571.2	1982.7	2166.7
145°	1223.6	1319.1	1564.4	1900.4	2040.7
147.5°	1276.2	1359.3	1557.6	1831.2	1941.5
150°	1311.3	1383.4	1554.5	1787.7	1879.3
152.5°	1343.2	1406.0	1552.9	1752.3	1826.7
155°	1389.0	1439.7	1550.5	1705.2	1759.7
157.5°	1429.3	1468.7	1550.9	1672.1	1708.7
160°	1454.8	1487.9	1552.5	1652.7	1680.0
162.5°	1477.1	1504.0	1554.1	1636.6	1656.1
165°	1506.6	1524.2	1556.5	1618.4	1626.2
167.5°	1530.5	1540.7	1558.4	1604.4	1607.5
170°	1546.5	1550.4	1558.4	1596.3	1596.3
172.5°	1556.1	1556.8	1560.0	1588.3	1588.3
175°	1566.4	1564.5	1558.4	1580.3	1576.4
177.5°	1570.8	1567.7	1559.6	1572.3	1569.2
180°	1564.4	1564.4	1564.4	1564.4	1564.4

(END OF REPORT)