

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563150

Luminaire Tested: **SQ4-PC3-150U-100D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563150
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8541.0 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563150
CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563150

CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	80	74	69	79	73	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	17	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11263	11263	11263
5°	11348	11275	11232
10°	11320	11268	11236
15°	11260	11260	11250
20°	11187	11220	11220
25°	11081	11161	11127
30°	10946	11079	11031
35°	10783	10949	10872
40°	10605	10755	10646
45°	10412	10487	10323
50°	10141	10141	9978
55°	9819	9691	9545
60°	9344	9156	9010
65°	8636	8464	8390
70°	7561	7623	7594
75°	6085	6730	6769
80°	4325	5706	5765
85°	2636	4785	4785



TEST NUMBER: P563150

CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.5	1.4
10°-20°	331.5	3.9
20°-30°	502.1	5.9
30°-40°	601.9	7.0
40°-50°	613.7	7.2
50°-60°	535.8	6.3
60°-70°	383.6	4.5
70°-80°	197.6	2.3
80°-90°	51.6	0.6
90°-100°	375.4	4.4
100°-110°	1014.9	11.9
110°-120°	1067.1	12.5
120°-130°	866.7	10.1
130°-140°	679.9	8.0
140°-150°	521.8	6.1
150°-160°	375.3	4.4
160°-170°	229.3	2.7
170°-180°	77.3	0.9
0°-30°	949.2	11.1
0°-40°	1551.1	18.2
0°-60°	2700.6	31.6
0°-90°	3333.4	39.0
90°-120°	2457.4	28.8
90°-150°	4525.8	53.0
90°-180°	5208.0	61.0
0°-180°	8541.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1221	1221	1221	1221	1221	
5°	1225	1213	1217	1214	1213	116
15°	1179	1169	1179	1179	1178	332
25°	1088	1081	1096	1093	1093	501
35°	957	955	972	965	965	599
45°	798	796	804	793	791	614
55°	610	603	602	593	593	544
65°	396	387	388	384	384	391
75°	171	178	189	190	190	184
85°	25	38	45	46	45	34
90°	2	5	11	12	11	5
95°	58	204	624	323	192	61
105°	189	292	1126	1661	1593	199
115°	332	406	934	1808	2041	328
125°	455	521	842	1420	1668	405
135°	545	610	819	1147	1298	421
145°	634	681	808	982	1056	397
155°	716	744	801	880	909	330
165°	779	787	804	836	840	219
175°	809	808	805	816	814	77
180°	808	808	808	808	808	

TEST NUMBER: P563150

CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1220.8	1220.8	1220.8	1220.8	1220.8
2.5°	1228.0	1217.4	1220.8	1217.9	1213.5
5°	1225.3	1213.1	1217.4	1214.0	1212.8
7.5°	1216.5	1204.3	1209.9	1207.6	1206.5
10°	1208.3	1196.2	1202.7	1200.4	1199.3
12.5°	1197.5	1186.2	1193.6	1191.4	1191.1
15°	1178.9	1169.0	1178.9	1178.9	1177.8
17.5°	1155.7	1146.6	1157.2	1157.9	1157.2
20°	1139.4	1129.4	1142.8	1141.7	1142.8
22.5°	1119.5	1111.3	1125.6	1122.7	1123.8
25°	1088.5	1080.8	1096.4	1093.0	1093.0
27.5°	1051.9	1046.4	1063.4	1059.8	1059.8
30°	1027.5	1021.9	1039.9	1035.4	1035.4
32.5°	1000.3	996.6	1013.7	1008.3	1008.3
35°	957.4	955.2	972.1	965.3	965.3
37.5°	913.1	911.1	926.4	918.2	915.6
40°	880.5	879.4	893.0	883.9	883.9
42.5°	848.0	846.9	858.6	847.7	847.7
45°	798.0	795.8	803.7	793.4	791.2
47.5°	743.5	741.3	746.2	735.1	734.0
50°	706.5	704.2	706.5	696.3	695.2
52.5°	668.5	664.5	664.9	654.7	654.5
55°	610.4	602.6	602.5	593.4	593.4
57.5°	548.9	538.7	539.6	531.9	530.8
60°	506.4	495.3	496.2	489.4	488.3
62.5°	464.8	452.0	454.6	446.9	446.7
65°	395.6	386.8	387.7	384.3	384.3
67.5°	329.2	321.0	326.9	324.2	324.0
70°	280.3	274.8	282.6	282.6	281.5
72.5°	235.1	234.9	244.6	244.6	245.3
75°	170.7	178.4	188.8	189.9	189.9
77.5°	113.9	127.6	139.0	139.5	139.3
80°	81.4	96.9	107.4	109.6	108.5
82.5°	55.2	71.5	80.3	82.5	81.4
85°	24.9	38.1	45.2	46.3	45.2
87.5°	7.6	16.2	20.3	20.5	18.5
90°	1.7	5.1	11.3	12.2	11.3
92.5°	24.7	90.0	177.5	77.1	55.8
95°	58.3	204.5	624.3	323.1	192.1
97.5°	93.6	234.5	973.1	805.3	591.4
100°	120.0	246.6	1081.6	1128.0	912.0
102.5°	144.3	263.5	1119.8	1372.6	1211.1
105°	188.7	291.5	1125.9	1660.8	1592.8
107.5°	229.7	323.6	1076.7	1840.6	1863.2
110°	261.7	346.7	1032.9	1888.9	1984.9



TEST NUMBER: P563150

CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.2	369.8	992.6	1879.2	2040.6
115°	332.1	406.1	933.8	1807.6	2040.6
117.5°	373.2	442.5	895.0	1698.3	1962.3
120°	398.2	466.2	872.0	1619.8	1889.3
122.5°	421.9	488.5	858.1	1535.7	1807.2
125°	454.7	521.0	841.6	1420.2	1668.5
127.5°	485.0	550.1	831.9	1326.0	1544.3
130°	501.7	568.8	827.7	1267.8	1465.0
132.5°	519.1	585.5	823.5	1215.3	1396.8
135°	545.1	609.7	819.0	1146.7	1298.1
137.5°	571.4	632.4	815.2	1091.2	1214.4
140°	589.5	646.4	813.8	1055.4	1165.0
142.5°	606.9	660.4	811.0	1023.1	1119.1
145°	633.8	681.4	807.7	981.6	1056.4
147.5°	658.3	700.5	803.9	944.0	1001.4
150°	676.4	713.8	802.5	923.5	969.4
152.5°	693.1	725.8	801.8	904.6	942.3
155°	715.5	743.6	800.8	880.5	909.4
157.5°	738.8	758.4	800.9	863.8	882.8
160°	752.1	768.2	801.6	853.2	866.8
162.5°	762.5	775.9	802.3	844.8	855.0
165°	779.0	786.7	804.2	835.6	839.9
167.5°	790.3	795.6	804.4	827.8	829.8
170°	797.3	799.8	805.1	824.2	824.2
172.5°	802.8	803.3	805.1	820.0	819.4
175°	808.6	807.7	805.1	815.5	813.8
177.5°	810.5	808.4	804.9	811.8	809.8
180°	807.7	807.7	807.7	807.7	807.7

(END OF REPORT)