

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563740

Luminaire Tested: **SQ4-PP3-125U-125D-840-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563740
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19944.3 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 152.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563740
CATALOG NUMBER: SQ4-PP3-125U-125D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563740

CATALOG NUMBER: SQ4-PP3-125U-125D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17738	17738	17738
5°	17868	17759	17696
10°	17838	17712	17633
15°	17720	17623	17527
20°	17602	17503	17371
25°	17393	17273	17101
30°	17071	16982	16766
35°	16625	16511	16302
40°	16093	15991	15809
45°	15653	15543	15390
50°	15091	14995	14849
55°	14310	14121	14013
60°	13027	12655	12592
65°	11477	10998	10961
70°	9908	9499	9499
75°	8529	8409	8290
80°	7521	7608	7430
85°	5886	6420	6420



TEST NUMBER: P563740

CATALOG NUMBER: SQ4-PP3-125U-125D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.6	1.8
10°-20°	1038.2	5.2
20°-30°	1555.0	7.8
30°-40°	1824.0	9.1
40°-50°	1829.7	9.2
50°-60°	1560.9	7.8
60°-70°	1018.0	5.1
70°-80°	510.7	2.6
80°-90°	145.0	0.7
90°-100°	731.8	3.7
100°-110°	1971.4	9.9
110°-120°	2068.9	10.4
120°-130°	1678.9	8.4
130°-140°	1316.7	6.6
140°-150°	1010.9	5.1
150°-160°	726.8	3.6
160°-170°	444.1	2.2
170°-180°	149.7	0.8
0°-30°	2956.8	14.8
0°-40°	4780.8	24.0
0°-60°	8171.3	41.0
0°-90°	9845.0	49.4
90°-120°	4772.2	23.9
90°-150°	8778.6	44.0
90°-180°	10099.0	50.6
0°-180°	19944.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3845	3845	3845	3845	3845	
5°	3859	3822	3835	3822	3822	366
15°	3710	3674	3690	3676	3670	1047
25°	3417	3378	3394	3363	3360	1571
35°	2952	2922	2932	2898	2895	1844
45°	2399	2383	2382	2359	2359	1847
55°	1779	1773	1756	1746	1742	1581
65°	1051	1032	1008	1001	1004	1049
75°	478	478	472	468	465	519
85°	111	121	121	121	121	131
90°	4	12	24	26	26	12
95°	112	398	1200	614	424	117
105°	365	567	2180	3262	3061	383
115°	644	788	1816	3508	3968	633
125°	879	1009	1630	2755	3242	785
135°	1058	1181	1584	2223	2517	817
145°	1224	1319	1564	1900	2041	767
155°	1389	1440	1550	1705	1760	639
165°	1507	1524	1556	1618	1626	425
175°	1566	1564	1558	1580	1576	149
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P563740

CATALOG NUMBER: SQ4-PP3-125U-125D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3845.1	3845.1	3845.1	3845.1	3845.1
2.5°	3869.4	3837.7	3845.1	3839.3	3823.5
5°	3858.6	3822.3	3835.0	3821.5	3821.5
7.5°	3832.3	3792.8	3805.3	3791.8	3791.2
10°	3808.0	3768.5	3781.1	3767.5	3764.2
12.5°	3773.0	3733.4	3748.7	3732.5	3731.9
15°	3710.3	3674.1	3690.1	3676.5	3669.9
17.5°	3639.5	3600.0	3619.3	3600.4	3597.7
20°	3585.6	3546.1	3565.4	3538.4	3538.4
22.5°	3520.9	3481.4	3503.4	3468.3	3468.3
25°	3417.1	3377.6	3393.5	3363.1	3359.8
27.5°	3293.8	3254.9	3271.5	3237.1	3236.5
30°	3204.8	3168.6	3188.0	3150.8	3147.5
32.5°	3107.8	3074.1	3088.2	3051.1	3047.8
35°	2952.1	2922.4	2931.8	2898.1	2894.8
37.5°	2788.3	2758.0	2768.7	2739.7	2738.4
40°	2672.4	2652.6	2655.5	2631.8	2625.2
42.5°	2564.5	2542.1	2545.0	2521.4	2520.0
45°	2399.4	2382.9	2382.5	2359.0	2359.0
47.5°	2224.2	2211.6	2208.0	2188.4	2187.8
50°	2102.8	2093.0	2089.4	2072.4	2069.1
52.5°	1976.1	1971.5	1960.0	1945.8	1945.1
55°	1779.3	1772.7	1755.7	1745.6	1742.3
57.5°	1565.7	1552.5	1533.3	1518.6	1521.2
60°	1412.0	1398.8	1371.6	1364.8	1364.8
62.5°	1263.7	1247.9	1220.6	1211.3	1216.5
65°	1051.4	1031.7	1007.6	1000.9	1004.2
67.5°	858.7	840.9	814.9	814.8	812.2
70°	734.6	724.8	704.3	704.3	704.3
72.5°	624.1	619.5	604.6	604.5	601.9
75°	478.5	478.5	471.8	468.3	465.1
77.5°	358.6	359.9	356.5	353.0	347.1
80°	283.1	289.7	286.4	283.0	279.7
82.5°	213.0	219.6	219.0	213.0	212.3
85°	111.2	121.1	121.3	121.3	121.3
87.5°	30.5	42.6	47.9	48.4	51.0
90°	4.0	11.8	23.9	25.9	25.9
92.5°	48.6	171.8	339.6	163.5	113.6
95°	111.6	398.0	1199.7	613.5	424.5
97.5°	178.2	455.6	1881.7	1572.0	1185.4
100°	229.2	478.6	2098.5	2195.6	1821.5
102.5°	278.6	510.9	2170.3	2662.7	2355.6
105°	364.7	567.4	2180.2	3261.8	3061.1
107.5°	446.0	626.8	2087.4	3569.7	3621.5
110°	500.2	671.7	2002.9	3665.2	3854.3



TEST NUMBER: P563740

CATALOG NUMBER: SQ4-PP3-125U-125D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	557.6	716.6	1921.5	3644.1	3954.7
115°	643.7	787.9	1815.5	3508.0	3967.9
117.5°	722.2	857.5	1733.4	3290.7	3802.8
120°	773.2	903.8	1692.0	3134.8	3660.9
122.5°	817.9	946.9	1661.7	2975.4	3499.9
125°	878.9	1009.4	1630.2	2755.3	3242.4
127.5°	937.5	1066.1	1610.3	2561.2	2996.1
130°	972.5	1101.1	1602.3	2450.0	2831.9
132.5°	1007.6	1134.7	1594.3	2352.0	2702.8
135°	1058.2	1181.0	1584.4	2222.8	2517.0
137.5°	1106.5	1224.2	1579.2	2113.2	2354.8
140°	1139.9	1253.0	1574.4	2045.7	2263.9
142.5°	1175.0	1280.2	1571.2	1982.7	2166.7
145°	1223.6	1319.1	1564.4	1900.4	2040.7
147.5°	1276.2	1359.3	1557.6	1831.2	1941.5
150°	1311.3	1383.4	1554.5	1787.7	1879.3
152.5°	1343.2	1406.0	1552.9	1752.3	1826.7
155°	1389.0	1439.7	1550.5	1705.2	1759.7
157.5°	1429.3	1468.7	1550.9	1672.1	1708.7
160°	1454.8	1487.9	1552.5	1652.7	1680.0
162.5°	1477.1	1504.0	1554.1	1636.6	1656.1
165°	1506.6	1524.2	1556.5	1618.4	1626.2
167.5°	1530.5	1540.7	1558.4	1604.4	1607.5
170°	1546.5	1550.4	1558.4	1596.3	1596.3
172.5°	1556.1	1556.8	1560.0	1588.3	1588.3
175°	1566.4	1564.5	1558.4	1580.3	1576.4
177.5°	1570.8	1567.7	1559.6	1572.3	1569.2
180°	1564.4	1564.4	1564.4	1564.4	1564.4

(END OF REPORT)