

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563462

Luminaire Tested: **SQ4-PP3-075U-125D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563462
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-125D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6800.5 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563462
CATALOG NUMBER: SQ4-PP3-075U-125D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563462

CATALOG NUMBER: SQ4-PP3-075U-125D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57	53
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	67	61	78	70	63	58	62	57	52	54	50	47	47	44	42	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	31	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	28	25	22
8	56	44	36	30	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15181	15181	15181
5°	15292	15199	15146
10°	15267	15158	15091
15°	15166	15083	15001
20°	15065	14981	14867
25°	14886	14783	14637
30°	14610	14534	14349
35°	14229	14131	13953
40°	13773	13687	13530
45°	13398	13304	13172
50°	12917	12833	12710
55°	12247	12085	11993
60°	11149	10830	10778
65°	9822	9414	9381
70°	8481	8130	8130
75°	7301	7197	7094
80°	6434	6514	6360
85°	5039	5494	5494



TEST NUMBER: P563462

CATALOG NUMBER: SQ4-PP3-075U-125D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.6	2.3
10°-20°	444.3	6.5
20°-30°	665.5	9.8
30°-40°	780.5	11.5
40°-50°	783.0	11.5
50°-60°	668.0	9.8
60°-70°	435.6	6.4
70°-80°	218.6	3.2
80°-90°	61.5	0.9
90°-100°	187.4	2.8
100°-110°	515.5	7.6
110°-120°	532.1	7.8
120°-130°	426.3	6.3
130°-140°	334.8	4.9
140°-150°	256.6	3.8
150°-160°	184.5	2.7
160°-170°	112.8	1.7
170°-180°	38.0	0.6
0°-30°	1265.3	18.6
0°-40°	2045.9	30.1
0°-60°	3496.8	51.4
0°-90°	4212.4	61.9
90°-120°	1235.0	18.2
90°-150°	2252.7	33.1
90°-180°	2588.0	38.1
0°-180°	6800.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1645	1645	1645	1645	1645	
5°	1651	1636	1641	1635	1635	157
15°	1588	1572	1579	1573	1570	448
25°	1462	1445	1452	1439	1438	672
35°	1263	1251	1255	1240	1239	789
45°	1027	1020	1020	1010	1010	791
55°	761	759	751	747	746	677
65°	450	442	431	428	430	449
75°	205	205	202	200	199	222
85°	48	52	52	52	52	56
90°	1	3	6	8	8	4
95°	28	102	331	142	90	29
105°	92	142	568	865	807	97
115°	163	199	456	907	1030	161
125°	225	256	413	699	819	201
135°	271	301	402	566	640	209
145°	314	335	396	482	519	197
155°	355	367	393	433	446	163
165°	384	389	395	411	413	108
175°	397	398	396	401	400	38
180°	397	397	397	397	397	

TEST NUMBER: P563462

CATALOG NUMBER: SQ4-PP3-075U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1645.4	1645.4	1645.4	1645.4	1645.4
2.5°	1655.8	1642.3	1645.4	1643.0	1636.2
5°	1651.2	1635.7	1641.1	1635.4	1635.4
7.5°	1640.0	1623.0	1628.4	1622.7	1622.4
10°	1629.6	1612.7	1618.0	1612.2	1610.8
12.5°	1614.6	1597.7	1604.2	1597.3	1597.0
15°	1587.8	1572.3	1579.1	1573.3	1570.5
17.5°	1557.5	1540.6	1548.8	1540.7	1539.6
20°	1534.4	1517.5	1525.8	1514.2	1514.2
22.5°	1506.7	1489.8	1499.2	1484.2	1484.2
25°	1462.3	1445.4	1452.2	1439.2	1437.8
27.5°	1409.5	1392.9	1400.0	1385.3	1385.0
30°	1371.4	1355.9	1364.2	1348.3	1346.9
32.5°	1329.9	1315.5	1321.6	1305.7	1304.2
35°	1263.3	1250.6	1254.6	1240.2	1238.8
37.5°	1193.2	1180.2	1184.8	1172.4	1171.9
40°	1143.6	1135.1	1136.4	1126.2	1123.4
42.5°	1097.4	1087.9	1089.1	1079.0	1078.4
45°	1026.8	1019.7	1019.6	1009.5	1009.5
47.5°	951.8	946.4	944.9	936.5	936.2
50°	899.9	895.6	894.1	886.9	885.5
52.5°	845.7	843.7	838.7	832.7	832.4
55°	761.4	758.6	751.3	747.0	745.6
57.5°	670.0	664.4	656.2	649.8	651.0
60°	604.2	598.6	586.9	584.1	584.1
62.5°	540.8	534.0	522.3	518.3	520.6
65°	449.9	441.5	431.2	428.3	429.7
67.5°	367.5	359.8	348.7	348.7	347.5
70°	314.4	310.2	301.4	301.4	301.4
72.5°	267.1	265.1	258.7	258.7	257.6
75°	204.8	204.8	201.9	200.4	199.0
77.5°	153.4	154.0	152.6	151.1	148.5
80°	121.1	124.0	122.6	121.1	119.7
82.5°	91.1	94.0	93.7	91.1	90.9
85°	47.6	51.8	51.9	51.9	51.9
87.5°	12.9	17.9	19.6	20.0	21.1
90°	0.8	3.3	5.9	7.6	7.6
92.5°	11.7	49.8	86.4	33.2	27.2
95°	27.9	102.3	331.3	141.7	90.4
97.5°	45.5	113.4	505.6	389.6	274.9
100°	58.3	120.3	560.4	565.6	461.5
102.5°	70.5	128.5	574.6	701.8	606.2
105°	92.1	141.7	568.0	865.1	807.2
107.5°	112.8	158.0	535.7	945.1	962.2
110°	127.6	169.0	511.4	964.9	1024.5

TEST NUMBER: P563462

CATALOG NUMBER: SQ4-PP3-075U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.2	181.2	487.0	952.1	1042.7
115°	163.1	198.7	455.6	907.2	1029.5
117.5°	184.1	216.8	435.6	844.2	982.5
120°	196.9	228.4	426.9	796.9	939.9
122.5°	208.4	239.8	420.8	755.5	891.2
125°	224.8	256.2	413.3	699.2	819.1
127.5°	240.4	270.3	408.4	652.2	757.4
130°	248.5	279.1	405.7	624.3	720.2
132.5°	258.0	288.6	403.7	599.7	686.4
135°	271.3	301.1	401.5	565.5	639.9
137.5°	283.8	311.4	399.6	537.8	599.1
140°	293.3	318.9	399.0	519.4	574.8
142.5°	301.4	325.1	397.6	503.0	550.4
145°	313.6	335.1	395.6	481.8	519.0
147.5°	326.6	345.1	394.6	463.0	492.8
150°	334.7	351.3	393.9	452.7	475.9
152.5°	342.2	357.4	393.2	443.9	463.0
155°	355.0	366.6	393.0	433.1	445.5
157.5°	364.3	373.7	393.0	424.2	432.8
160°	371.1	378.5	393.0	419.4	426.0
162.5°	376.5	382.6	393.7	415.3	420.6
165°	383.7	388.7	394.7	410.9	413.3
167.5°	388.8	392.6	395.6	407.1	407.8
170°	392.2	394.7	395.6	405.7	405.7
172.5°	394.9	396.1	395.6	403.7	403.0
175°	397.3	398.1	395.6	400.6	399.8
177.5°	397.9	397.9	395.2	399.3	397.9
180°	397.3	397.3	397.3	397.3	397.3

(END OF REPORT)