

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563534

Luminaire Tested: **SQ4-PP3-0U-100D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563534
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-100D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3300.2 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563534
CATALOG NUMBER: SQ4-PP3-0U-100D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563534

CATALOG NUMBER: SQ4-PP3-OU-100D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11896	11896	11896
5°	11983	11910	11869
10°	11964	11878	11826
15°	11884	11819	11754
20°	11806	11739	11650
25°	11665	11585	11470
30°	11449	11389	11245
35°	11149	11074	10933
40°	10793	10725	10602
45°	10498	10425	10321
50°	10122	10056	9960
55°	9598	9471	9397
60°	8737	8486	8446
65°	7698	7377	7353
70°	6647	6372	6372
75°	5721	5639	5557
80°	5042	5106	4984
85°	3949	4308	4308



TEST NUMBER: P563534

CATALOG NUMBER: SQ4-PP3-0U-100D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.9	3.7
10°-20°	348.1	10.5
20°-30°	521.5	15.8
30°-40°	611.6	18.5
40°-50°	613.6	18.6
50°-60°	523.4	15.9
60°-70°	341.4	10.3
70°-80°	171.3	5.2
80°-90°	47.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	991.5	30.0
0°-40°	1603.2	48.6
0°-60°	2740.1	83.0
0°-90°	3300.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3300.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1289	1289	1289	1289	1289	
5°	1294	1282	1286	1282	1282	123
15°	1244	1232	1237	1233	1231	351
25°	1146	1133	1138	1128	1127	527
35°	990	980	983	972	971	618
45°	805	799	799	791	791	620
55°	597	594	589	585	584	530
65°	353	346	338	336	337	352
75°	160	160	158	157	156	174
85°	37	41	41	41	41	45
90°	0	0	0	0	0	



TEST NUMBER: P563534

CATALOG NUMBER: SQ4-PP3-0U-100D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1289.4	1289.4	1289.4	1289.4	1289.4
2.5°	1297.5	1286.9	1289.4	1287.5	1282.2
5°	1293.9	1281.8	1286.0	1281.5	1281.5
7.5°	1285.1	1271.8	1276.1	1271.5	1271.3
10°	1277.0	1263.7	1267.9	1263.4	1262.3
12.5°	1265.2	1252.0	1257.1	1251.7	1251.4
15°	1244.2	1232.0	1237.4	1232.8	1230.6
17.5°	1220.5	1207.2	1213.7	1207.3	1206.5
20°	1202.4	1189.1	1195.6	1186.6	1186.6
22.5°	1180.7	1167.4	1174.8	1163.1	1163.1
25°	1145.9	1132.6	1138.0	1127.8	1126.7
27.5°	1104.5	1091.5	1097.1	1085.5	1085.3
30°	1074.7	1062.5	1069.0	1056.6	1055.5
32.5°	1042.1	1030.9	1035.6	1023.1	1022.0
35°	989.9	980.0	983.2	971.8	970.7
37.5°	935.0	924.8	928.5	918.7	918.3
40°	896.1	889.5	890.5	882.5	880.3
42.5°	860.0	852.5	853.4	845.5	845.1
45°	804.6	799.1	799.0	791.0	791.0
47.5°	745.8	741.6	740.4	733.9	733.6
50°	705.2	701.8	700.6	695.0	693.9
52.5°	662.7	661.1	657.2	652.5	652.3
55°	596.7	594.5	588.8	585.3	584.2
57.5°	525.0	520.6	514.2	509.2	510.1
60°	473.5	469.1	459.9	457.7	457.7
62.5°	423.8	418.5	409.3	406.2	408.0
65°	352.6	346.0	337.9	335.7	336.8
67.5°	287.9	282.0	273.2	273.2	272.3
70°	246.4	243.0	236.2	236.2	236.2
72.5°	209.3	207.7	202.7	202.7	201.8
75°	160.5	160.5	158.2	157.1	155.9
77.5°	120.2	120.7	119.6	118.4	116.4
80°	94.9	97.1	96.1	94.9	93.8
82.5°	71.4	73.6	73.5	71.4	71.2
85°	37.3	40.6	40.7	40.7	40.7
87.5°	9.9	13.5	14.5	14.5	15.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)