

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563606

Luminaire Tested: **SQ4-PP3-100U-075D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563606
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5956.9 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 49.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563606
CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563606

CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	45	43	40	38	34	32	30	26
4	73	63	55	49	67	57	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	29	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8953	8953	8953
5°	9019	8964	8933
10°	9004	8940	8900
15°	8944	8895	8847
20°	8885	8835	8768
25°	8779	8719	8632
30°	8617	8572	8463
35°	8391	8334	8229
40°	8122	8072	7979
45°	7902	7846	7769
50°	7617	7569	7495
55°	7224	7127	7073
60°	6576	6388	6357
65°	5794	5552	5532
70°	5001	4796	4796
75°	4306	4246	4185
80°	3794	3841	3751
85°	2975	3239	3239



TEST NUMBER: P563606

CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.8	1.5
10°-20°	262.0	4.4
20°-30°	392.5	6.6
30°-40°	460.3	7.7
40°-50°	461.8	7.8
50°-60°	393.9	6.6
60°-70°	256.9	4.3
70°-80°	128.9	2.2
80°-90°	36.8	0.6
90°-100°	250.2	4.2
100°-110°	690.9	11.6
110°-120°	712.5	12.0
120°-130°	572.6	9.6
130°-140°	450.0	7.6
140°-150°	345.1	5.8
150°-160°	248.0	4.2
160°-170°	151.7	2.5
170°-180°	51.1	0.9
0°-30°	746.2	12.5
0°-40°	1206.6	20.3
0°-60°	2062.3	34.6
0°-90°	2484.9	41.7
90°-120°	1653.6	27.8
90°-150°	3021.2	50.7
90°-180°	3472.0	58.3
0°-180°	5956.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	974	965	968	964	964	92
15°	936	927	931	928	926	264
25°	862	852	856	849	848	397
35°	745	738	740	731	731	465
45°	606	601	601	595	595	466
55°	449	447	443	440	440	399
65°	265	260	254	253	253	265
75°	121	121	119	118	117	131
85°	28	31	31	31	31	33
90°	2	3	7	8	8	4
95°	37	135	454	187	121	39
105°	123	190	760	1160	1093	131
115°	221	267	612	1212	1378	217
125°	303	344	555	939	1102	269
135°	364	404	540	761	858	282
145°	422	452	533	648	697	264
155°	476	492	528	581	599	219
165°	516	522	531	552	556	145
175°	534	535	532	540	538	51
180°	534	534	534	534	534	

TEST NUMBER: P563606

CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	970.4	970.4	970.4	970.4	970.4
2.5°	976.5	968.6	970.4	969.0	965.0
5°	973.8	964.7	967.9	964.5	964.5
7.5°	967.2	957.2	960.4	957.0	956.8
10°	961.1	951.1	954.3	950.8	950.0
12.5°	952.2	942.2	946.1	942.0	941.8
15°	936.4	927.3	931.3	927.9	926.2
17.5°	918.5	908.6	913.4	908.7	908.0
20°	904.9	895.0	899.8	893.0	893.0
22.5°	888.6	878.6	884.2	875.3	875.3
25°	862.4	852.4	856.5	848.8	847.9
27.5°	831.3	821.5	825.7	817.0	816.8
30°	808.8	799.7	804.6	795.2	794.4
32.5°	784.3	775.8	779.4	770.0	769.2
35°	745.0	737.6	739.9	731.4	730.6
37.5°	703.7	696.1	698.8	691.4	691.1
40°	674.4	669.5	670.2	664.2	662.5
42.5°	647.2	641.6	642.3	636.3	636.0
45°	605.6	601.4	601.3	595.4	595.4
47.5°	561.3	558.2	557.2	552.3	552.1
50°	530.7	528.2	527.3	523.0	522.2
52.5°	498.7	497.6	494.7	491.1	490.9
55°	449.1	447.4	443.1	440.5	439.7
57.5°	395.1	391.8	387.0	383.3	383.9
60°	356.4	353.0	346.2	344.5	344.5
62.5°	318.9	314.9	308.1	305.7	307.0
65°	265.4	260.4	254.3	252.6	253.4
67.5°	216.7	212.2	205.7	205.6	205.0
70°	185.4	182.9	177.8	177.8	177.8
72.5°	157.5	156.3	152.6	152.6	151.9
75°	120.8	120.8	119.1	118.2	117.4
77.5°	90.5	90.8	90.0	89.1	87.6
80°	71.4	73.1	72.3	71.4	70.6
82.5°	53.8	55.4	55.3	53.7	53.6
85°	28.1	30.6	30.6	30.6	30.6
87.5°	7.8	10.8	12.3	12.4	13.3
90°	1.7	3.4	6.8	7.7	8.5
92.5°	15.4	63.9	114.2	41.7	32.5
95°	36.8	135.4	454.0	186.6	121.4
97.5°	60.9	151.7	672.5	517.8	375.0
100°	78.7	161.4	753.2	758.6	616.4
102.5°	95.8	172.5	769.0	937.3	802.5
105°	123.1	190.0	760.1	1160.4	1092.7
107.5°	152.2	211.7	717.7	1268.0	1292.7
110°	172.7	226.2	684.8	1291.1	1371.4



TEST NUMBER: P563606

CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	191.2	242.7	654.1	1272.9	1391.2
115°	220.6	266.6	612.2	1211.9	1378.2
117.5°	246.2	292.0	584.6	1126.0	1315.3
120°	263.3	308.5	573.7	1067.9	1258.5
122.5°	279.8	322.9	564.8	1013.7	1194.2
125°	302.7	344.5	554.9	939.1	1102.1
127.5°	322.2	364.0	549.1	876.0	1016.6
130°	335.2	377.0	546.3	837.4	965.3
132.5°	347.5	387.3	543.6	805.0	920.8
135°	364.2	403.5	539.5	760.6	857.6
137.5°	383.0	418.8	537.4	723.3	806.1
140°	393.3	428.4	536.1	698.5	771.2
142.5°	404.9	437.4	534.7	676.4	740.4
145°	422.4	451.6	532.7	647.5	696.8
147.5°	439.1	464.7	530.8	623.1	661.4
150°	451.4	472.3	530.1	608.6	639.5
152.5°	461.0	480.6	529.4	596.2	621.7
155°	476.2	492.1	528.4	581.0	599.3
157.5°	490.2	502.5	528.6	569.9	582.4
160°	498.5	509.3	529.2	563.6	572.8
162.5°	505.3	514.8	529.9	558.1	565.3
165°	515.6	522.2	530.9	551.6	555.7
167.5°	523.4	527.4	531.8	547.6	548.9
170°	527.5	530.9	531.8	545.5	545.5
172.5°	530.9	533.0	531.8	542.7	542.1
175°	534.4	535.2	531.8	539.5	537.8
177.5°	535.7	535.1	531.6	536.4	535.0
180°	534.4	534.4	534.4	534.4	534.4

(END OF REPORT)