

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563630

Luminaire Tested: **SQ4-PP3-100U-100D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563630
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6773.3 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 57.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563630
CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563630

CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41				
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	38	36	34	30				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22				
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20	17				
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11896	11896	11896
5°	11983	11910	11869
10°	11964	11878	11826
15°	11884	11819	11754
20°	11806	11739	11650
25°	11665	11585	11470
30°	11449	11389	11245
35°	11149	11074	10933
40°	10793	10725	10602
45°	10498	10425	10321
50°	10122	10056	9960
55°	9598	9471	9397
60°	8737	8486	8446
65°	7698	7377	7353
70°	6647	6372	6372
75°	5721	5639	5557
80°	5042	5106	4984
85°	3949	4308	4308



TEST NUMBER: P563630

CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.9	1.8
10°-20°	348.1	5.1
20°-30°	521.5	7.7
30°-40°	611.6	9.0
40°-50°	613.6	9.1
50°-60°	523.4	7.7
60°-70°	341.4	5.0
70°-80°	171.3	2.5
80°-90°	48.5	0.7
90°-100°	250.2	3.7
100°-110°	690.9	10.2
110°-120°	712.5	10.5
120°-130°	572.6	8.5
130°-140°	450.0	6.6
140°-150°	345.1	5.1
150°-160°	248.0	3.7
160°-170°	151.7	2.2
170°-180°	51.1	0.8
0°-30°	991.5	14.6
0°-40°	1603.2	23.7
0°-60°	2740.1	40.5
0°-90°	3301.3	48.7
90°-120°	1653.6	24.4
90°-150°	3021.2	44.6
90°-180°	3472.0	51.3
0°-180°	6773.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1289	1289	1289	1289	1289	
5°	1294	1282	1286	1282	1282	123
15°	1244	1232	1237	1233	1231	351
25°	1146	1133	1138	1128	1127	527
35°	990	980	983	972	971	618
45°	805	799	799	791	791	620
55°	597	594	589	585	584	530
65°	353	346	338	336	337	352
75°	160	160	158	157	156	174
85°	37	41	41	41	41	44
90°	2	3	7	8	8	4
95°	37	135	454	187	121	39
105°	123	190	760	1160	1093	131
115°	221	267	612	1212	1378	217
125°	303	344	555	939	1102	269
135°	364	404	540	761	858	282
145°	422	452	533	648	697	264
155°	476	492	528	581	599	219
165°	516	522	531	552	556	145
175°	534	535	532	540	538	51
180°	534	534	534	534	534	

TEST NUMBER: P563630

CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1289.4	1289.4	1289.4	1289.4	1289.4
2.5°	1297.5	1286.9	1289.4	1287.5	1282.2
5°	1293.9	1281.8	1286.0	1281.5	1281.5
7.5°	1285.1	1271.8	1276.1	1271.5	1271.3
10°	1277.0	1263.7	1267.9	1263.4	1262.3
12.5°	1265.2	1252.0	1257.1	1251.7	1251.4
15°	1244.2	1232.0	1237.4	1232.8	1230.6
17.5°	1220.5	1207.2	1213.7	1207.3	1206.5
20°	1202.4	1189.1	1195.6	1186.6	1186.6
22.5°	1180.7	1167.4	1174.8	1163.1	1163.1
25°	1145.9	1132.6	1138.0	1127.8	1126.7
27.5°	1104.5	1091.5	1097.1	1085.5	1085.3
30°	1074.7	1062.5	1069.0	1056.6	1055.5
32.5°	1042.1	1030.9	1035.6	1023.1	1022.0
35°	989.9	980.0	983.2	971.8	970.7
37.5°	935.0	924.8	928.5	918.7	918.3
40°	896.1	889.5	890.5	882.5	880.3
42.5°	860.0	852.5	853.4	845.5	845.1
45°	804.6	799.1	799.0	791.0	791.0
47.5°	745.8	741.6	740.4	733.9	733.6
50°	705.2	701.8	700.6	695.0	693.9
52.5°	662.7	661.1	657.2	652.5	652.3
55°	596.7	594.5	588.8	585.3	584.2
57.5°	525.0	520.6	514.2	509.2	510.1
60°	473.5	469.1	459.9	457.7	457.7
62.5°	423.8	418.5	409.3	406.2	408.0
65°	352.6	346.0	337.9	335.7	336.8
67.5°	287.9	282.0	273.2	273.2	272.3
70°	246.4	243.0	236.2	236.2	236.2
72.5°	209.3	207.7	202.7	202.7	201.8
75°	160.5	160.5	158.2	157.1	155.9
77.5°	120.2	120.7	119.6	118.4	116.4
80°	94.9	97.1	96.1	94.9	93.8
82.5°	71.4	73.6	73.5	71.4	71.2
85°	37.3	40.6	40.7	40.7	40.7
87.5°	10.3	14.2	15.8	16.0	17.1
90°	1.7	3.4	6.8	7.7	8.5
92.5°	15.4	63.9	114.2	41.7	32.5
95°	36.8	135.4	454.0	186.6	121.4
97.5°	60.9	151.7	672.5	517.8	375.0
100°	78.7	161.4	753.2	758.6	616.4
102.5°	95.8	172.5	769.0	937.3	802.5
105°	123.1	190.0	760.1	1160.4	1092.7
107.5°	152.2	211.7	717.7	1268.0	1292.7
110°	172.7	226.2	684.8	1291.1	1371.4



TEST NUMBER: P563630

CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	191.2	242.7	654.1	1272.9	1391.2
115°	220.6	266.6	612.2	1211.9	1378.2
117.5°	246.2	292.0	584.6	1126.0	1315.3
120°	263.3	308.5	573.7	1067.9	1258.5
122.5°	279.8	322.9	564.8	1013.7	1194.2
125°	302.7	344.5	554.9	939.1	1102.1
127.5°	322.2	364.0	549.1	876.0	1016.6
130°	335.2	377.0	546.3	837.4	965.3
132.5°	347.5	387.3	543.6	805.0	920.8
135°	364.2	403.5	539.5	760.6	857.6
137.5°	383.0	418.8	537.4	723.3	806.1
140°	393.3	428.4	536.1	698.5	771.2
142.5°	404.9	437.4	534.7	676.4	740.4
145°	422.4	451.6	532.7	647.5	696.8
147.5°	439.1	464.7	530.8	623.1	661.4
150°	451.4	472.3	530.1	608.6	639.5
152.5°	461.0	480.6	529.4	596.2	621.7
155°	476.2	492.1	528.4	581.0	599.3
157.5°	490.2	502.5	528.6	569.9	582.4
160°	498.5	509.3	529.2	563.6	572.8
162.5°	505.3	514.8	529.9	558.1	565.3
165°	515.6	522.2	530.9	551.6	555.7
167.5°	523.4	527.4	531.8	547.6	548.9
170°	527.5	530.9	531.8	545.5	545.5
172.5°	530.9	533.0	531.8	542.7	542.1
175°	534.4	535.2	531.8	539.5	537.8
177.5°	535.7	535.1	531.6	536.4	535.0
180°	534.4	534.4	534.4	534.4	534.4

(END OF REPORT)