

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563798

Luminaire Tested: **SQ4-PP3-150U-075D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563798
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7693.0 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 63.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563798
CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563798

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8953	8953	8953
5°	9019	8964	8933
10°	9004	8940	8900
15°	8944	8895	8847
20°	8885	8835	8768
25°	8779	8719	8632
30°	8617	8572	8463
35°	8391	8334	8229
40°	8122	8072	7979
45°	7902	7846	7769
50°	7617	7569	7495
55°	7224	7127	7073
60°	6576	6388	6357
65°	5794	5552	5532
70°	5001	4796	4796
75°	4306	4246	4185
80°	3794	3841	3751
85°	2975	3239	3239



TEST NUMBER: P563798

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.8	1.2
10°-20°	262.0	3.4
20°-30°	392.5	5.1
30°-40°	460.3	6.0
40°-50°	461.8	6.0
50°-60°	393.9	5.1
60°-70°	256.9	3.3
70°-80°	128.9	1.7
80°-90°	37.3	0.5
90°-100°	375.4	4.9
100°-110°	1014.9	13.2
110°-120°	1067.1	13.9
120°-130°	866.7	11.3
130°-140°	679.9	8.8
140°-150°	521.8	6.8
150°-160°	375.3	4.9
160°-170°	229.3	3.0
170°-180°	77.3	1.0
0°-30°	746.2	9.7
0°-40°	1206.6	15.7
0°-60°	2062.3	26.8
0°-90°	2485.4	32.3
90°-120°	2457.4	31.9
90°-150°	4525.8	58.8
90°-180°	5208.0	67.7
0°-180°	7693.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	974	965	968	964	964	92
15°	936	927	931	928	926	264
25°	862	852	856	849	848	397
35°	745	738	740	731	731	465
45°	606	601	601	595	595	466
55°	449	447	443	440	440	399
65°	265	260	254	253	253	265
75°	121	121	119	118	117	131
85°	28	31	31	31	31	33
90°	2	5	11	12	11	5
95°	58	204	624	323	192	61
105°	189	292	1126	1661	1593	199
115°	332	406	934	1808	2041	328
125°	455	521	842	1420	1668	405
135°	545	610	819	1147	1298	421
145°	634	681	808	982	1056	397
155°	716	744	801	880	909	330
165°	779	787	804	836	840	219
175°	809	808	805	816	814	77
180°	808	808	808	808	808	



TEST NUMBER: P563798

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	970.4	970.4	970.4	970.4	970.4
2.5°	976.5	968.6	970.4	969.0	965.0
5°	973.8	964.7	967.9	964.5	964.5
7.5°	967.2	957.2	960.4	957.0	956.8
10°	961.1	951.1	954.3	950.8	950.0
12.5°	952.2	942.2	946.1	942.0	941.8
15°	936.4	927.3	931.3	927.9	926.2
17.5°	918.5	908.6	913.4	908.7	908.0
20°	904.9	895.0	899.8	893.0	893.0
22.5°	888.6	878.6	884.2	875.3	875.3
25°	862.4	852.4	856.5	848.8	847.9
27.5°	831.3	821.5	825.7	817.0	816.8
30°	808.8	799.7	804.6	795.2	794.4
32.5°	784.3	775.8	779.4	770.0	769.2
35°	745.0	737.6	739.9	731.4	730.6
37.5°	703.7	696.1	698.8	691.4	691.1
40°	674.4	669.5	670.2	664.2	662.5
42.5°	647.2	641.6	642.3	636.3	636.0
45°	605.6	601.4	601.3	595.4	595.4
47.5°	561.3	558.2	557.2	552.3	552.1
50°	530.7	528.2	527.3	523.0	522.2
52.5°	498.7	497.6	494.7	491.1	490.9
55°	449.1	447.4	443.1	440.5	439.7
57.5°	395.1	391.8	387.0	383.3	383.9
60°	356.4	353.0	346.2	344.5	344.5
62.5°	318.9	314.9	308.1	305.7	307.0
65°	265.4	260.4	254.3	252.6	253.4
67.5°	216.7	212.2	205.7	205.6	205.0
70°	185.4	182.9	177.8	177.8	177.8
72.5°	157.5	156.3	152.6	152.6	151.9
75°	120.8	120.8	119.1	118.2	117.4
77.5°	90.5	90.8	90.0	89.1	87.6
80°	71.4	73.1	72.3	71.4	70.6
82.5°	53.8	55.4	55.3	53.7	53.6
85°	28.1	30.6	30.6	30.6	30.6
87.5°	7.8	11.2	13.1	13.3	13.8
90°	1.7	5.1	11.3	12.2	11.3
92.5°	24.7	90.0	177.5	77.1	55.8
95°	58.3	204.5	624.3	323.1	192.1
97.5°	93.6	234.5	973.1	805.3	591.4
100°	120.0	246.6	1081.6	1128.0	912.0
102.5°	144.3	263.5	1119.8	1372.6	1211.1
105°	188.7	291.5	1125.9	1660.8	1592.8
107.5°	229.7	323.6	1076.7	1840.6	1863.2
110°	261.7	346.7	1032.9	1888.9	1984.9



TEST NUMBER: P563798

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.2	369.8	992.6	1879.2	2040.6
115°	332.1	406.1	933.8	1807.6	2040.6
117.5°	373.2	442.5	895.0	1698.3	1962.3
120°	398.2	466.2	872.0	1619.8	1889.3
122.5°	421.9	488.5	858.1	1535.7	1807.2
125°	454.7	521.0	841.6	1420.2	1668.5
127.5°	485.0	550.1	831.9	1326.0	1544.3
130°	501.7	568.8	827.7	1267.8	1465.0
132.5°	519.1	585.5	823.5	1215.3	1396.8
135°	545.1	609.7	819.0	1146.7	1298.1
137.5°	571.4	632.4	815.2	1091.2	1214.4
140°	589.5	646.4	813.8	1055.4	1165.0
142.5°	606.9	660.4	811.0	1023.1	1119.1
145°	633.8	681.4	807.7	981.6	1056.4
147.5°	658.3	700.5	803.9	944.0	1001.4
150°	676.4	713.8	802.5	923.5	969.4
152.5°	693.1	725.8	801.8	904.6	942.3
155°	715.5	743.6	800.8	880.5	909.4
157.5°	738.8	758.4	800.9	863.8	882.8
160°	752.1	768.2	801.6	853.2	866.8
162.5°	762.5	775.9	802.3	844.8	855.0
165°	779.0	786.7	804.2	835.6	839.9
167.5°	790.3	795.6	804.4	827.8	829.8
170°	797.3	799.8	805.1	824.2	824.2
172.5°	802.8	803.3	805.1	820.0	819.4
175°	808.6	807.7	805.1	815.5	813.8
177.5°	810.5	808.4	804.9	811.8	809.8
180°	807.7	807.7	807.7	807.7	807.7

(END OF REPORT)