

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564038

Luminaire Tested: **SQ4-PR1-050U-125D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564038  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-050U-125D-940-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5909.5 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 55.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564038  
CATALOG NUMBER: SQ4-PR1-050U-125D-940-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564038

CATALOG NUMBER: SQ4-PR1-050U-125D-940-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	75	75	75	71	
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	64	64	64	60	
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	55	55	55	51	
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	47	47	47	44	
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	41	41	41	38	
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	36	36	36	33	
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32	32	32	32	29	
7	62	50	42	36	59	48	40	35	43	37	33	40	34	30	36	32	28	28	28	28	26	
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	25	25	25	25	23	
9	54	41	34	29	51	40	33	28	37	30	26	33	28	25	31	26	23	23	23	23	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	21	21	21	19	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15451	15451	15451
5°	15590	15470	15390
10°	15541	15433	15351
15°	15473	15376	15293
20°	15394	15295	15182
25°	15286	15183	15007
30°	15122	15014	14799
35°	14898	14768	14556
40°	14559	14402	14142
45°	13965	13720	13438
50°	12920	12609	12360
55°	11276	11022	10788
60°	9503	9422	9235
65°	8219	8250	8187
70°	7548	7588	7588
75°	7251	7251	7301
80°	6822	6896	6822
85°	5494	6108	6108



TEST NUMBER: P564038

CATALOG NUMBER: SQ4-PR1-050U-125D-940-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.4	2.7
10°-20°	453.1	7.7
20°-30°	683.4	11.6
30°-40°	814.3	13.8
40°-50°	802.8	13.6
50°-60°	613.6	10.4
60°-70°	379.7	6.4
70°-80°	215.7	3.6
80°-90°	66.6	1.1
90°-100°	126.6	2.1
100°-110°	343.9	5.8
110°-120°	353.6	6.0
120°-130°	282.7	4.8
130°-140°	222.2	3.8
140°-150°	170.3	2.9
150°-160°	122.5	2.1
160°-170°	74.9	1.3
170°-180°	25.2	0.4
0°-30°	1294.9	21.9
0°-40°	2109.2	35.7
0°-60°	3525.6	59.7
0°-90°	4187.5	70.9
90°-120°	824.1	13.9
90°-150°	1499.3	25.4
90°-180°	1722.0	29.1
0°-180°	5909.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1683	1665	1670	1664	1662	160
15°	1620	1603	1610	1604	1601	457
25°	1502	1483	1492	1476	1474	691
35°	1323	1307	1311	1294	1292	826
45°	1070	1056	1052	1033	1030	820
55°	701	690	685	674	671	628
65°	376	374	378	375	375	381
75°	203	203	203	205	205	215
85°	52	55	58	58	58	60
90°	1	3	6	8	8	3
95°	19	69	220	96	64	20
105°	61	95	378	576	542	65
115°	108	132	303	602	686	107
125°	149	170	274	462	544	133
135°	180	200	266	376	424	139
145°	208	223	263	319	343	130
155°	235	243	261	287	295	108
165°	254	258	262	273	274	72
175°	264	265	263	266	265	25
180°	264	264	264	264	264	

TEST NUMBER: P564038

CATALOG NUMBER: SQ4-PR1-050U-125D-940-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1674.7	1674.7	1674.7	1674.7	1674.7
2.5°	1685.1	1670.4	1674.7	1671.0	1663.1
5°	1683.3	1665.0	1670.4	1664.5	1661.7
7.5°	1670.4	1652.3	1657.7	1651.9	1650.2
10°	1658.8	1641.9	1647.3	1641.4	1638.6
12.5°	1646.1	1628.1	1634.6	1627.6	1624.8
15°	1619.9	1602.9	1609.8	1603.9	1601.1
17.5°	1591.0	1573.0	1579.8	1573.1	1569.4
20°	1567.9	1551.0	1557.8	1547.7	1546.3
22.5°	1542.6	1525.6	1532.5	1518.9	1518.6
25°	1501.6	1483.3	1491.5	1475.6	1474.2
27.5°	1452.8	1435.9	1442.7	1426.5	1424.9
30°	1419.4	1402.4	1409.3	1391.9	1389.1
32.5°	1381.3	1365.5	1371.2	1353.8	1352.2
35°	1322.7	1307.2	1311.2	1293.8	1292.4
37.5°	1256.1	1242.0	1244.3	1225.2	1223.8
40°	1208.8	1194.7	1195.8	1175.6	1174.2
42.5°	1156.8	1142.7	1141.6	1121.3	1119.9
45°	1070.3	1056.2	1051.5	1032.7	1029.9
47.5°	971.6	957.5	948.8	933.5	931.5
50°	900.1	886.0	878.5	865.4	861.1
52.5°	822.8	808.7	802.3	790.4	786.1
55°	701.0	689.7	685.2	673.6	670.7
57.5°	585.3	577.7	576.4	565.1	564.0
60°	515.0	510.7	510.6	500.5	500.5
62.5°	454.9	451.8	454.1	447.4	446.3
65°	376.5	373.7	377.9	375.0	375.0
67.5°	314.5	314.5	317.1	315.9	315.9
70°	279.8	279.8	281.3	281.3	281.3
72.5°	248.7	247.6	251.3	251.2	250.1
75°	203.4	203.4	203.4	204.8	204.8
77.5°	158.4	158.7	159.8	159.5	158.4
80°	128.4	129.8	129.8	128.4	128.4
82.5°	98.4	99.8	99.8	99.5	98.4
85°	51.9	54.7	57.7	57.7	57.7
87.5°	15.2	20.2	24.3	24.6	23.5
90°	0.8	3.3	5.9	7.6	7.6
92.5°	7.6	34.7	60.2	25.9	21.9
95°	18.7	69.2	220.5	96.0	64.4
97.5°	30.9	76.5	338.0	263.0	184.7
100°	39.0	81.3	374.0	379.1	306.1
102.5°	47.1	86.1	383.5	468.8	404.5
105°	61.1	95.1	378.2	575.9	541.9
107.5°	75.5	105.5	356.3	631.1	640.6
110°	85.6	113.0	340.1	642.0	682.6

TEST NUMBER: P564038

CATALOG NUMBER: SQ4-PR1-050U-125D-940-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	94.5	120.5	323.8	633.0	694.2
115°	108.5	131.8	302.7	602.3	686.0
117.5°	121.8	144.0	289.3	558.8	653.1
120°	130.6	152.2	283.2	529.6	623.3
122.5°	138.1	159.6	279.2	500.3	590.7
125°	149.2	170.0	273.9	461.5	544.4
127.5°	159.3	179.8	271.0	432.1	503.2
130°	165.4	185.3	269.7	413.6	477.4
132.5°	171.5	191.4	268.3	397.8	454.4
135°	179.8	199.7	266.3	375.9	424.0
137.5°	188.8	206.8	265.3	356.6	397.0
140°	194.2	211.6	264.6	344.3	380.8
142.5°	199.6	215.7	263.9	334.6	365.2
145°	207.8	222.7	262.9	319.4	343.4
147.5°	216.9	229.7	262.0	307.4	326.3
150°	223.0	233.8	262.0	300.5	315.5
152.5°	227.8	237.2	261.4	294.4	306.6
155°	234.9	243.2	261.2	286.8	295.1
157.5°	241.9	248.3	261.2	281.7	288.0
160°	245.9	251.7	261.2	278.3	283.2
162.5°	250.0	254.5	261.9	275.5	279.2
165°	254.4	257.7	262.0	273.1	273.9
167.5°	259.0	260.6	262.9	270.2	270.9
170°	260.3	262.0	262.9	268.8	268.8
172.5°	261.7	262.7	262.9	267.5	267.5
175°	263.7	264.6	262.9	266.3	265.4
177.5°	264.4	264.4	262.4	265.1	263.7
180°	263.7	263.7	263.7	263.7	263.7

(END OF REPORT)