

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564398

Luminaire Tested: **SQ4-PR1-125U-100D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564398
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-100D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7604.0 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 64.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564398
CATALOG NUMBER: SQ4-PR1-125U-100D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564398

CATALOG NUMBER: SQ4-PR1-125U-100D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	96	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	59	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12108	12108	12108
5°	12217	12122	12059
10°	12178	12093	12030
15°	12125	12048	11984
20°	12064	11986	11897
25°	11979	11898	11760
30°	11849	11765	11596
35°	11674	11573	11407
40°	11408	11285	11082
45°	10943	10751	10531
50°	10123	9881	9686
55°	8836	8636	8454
60°	7446	7383	7237
65°	6440	6464	6416
70°	5916	5945	5945
75°	5682	5682	5721
80°	5345	5403	5345
85°	4308	4785	4785



TEST NUMBER: P564398

CATALOG NUMBER: SQ4-PR1-125U-100D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	1.6
10°-20°	355.1	4.7
20°-30°	535.5	7.0
30°-40°	638.1	8.4
40°-50°	629.1	8.3
50°-60°	480.8	6.3
60°-70°	297.5	3.9
70°-80°	169.0	2.2
80°-90°	53.0	0.7
90°-100°	313.2	4.1
100°-110°	843.6	11.1
110°-120°	885.4	11.6
120°-130°	718.5	9.4
130°-140°	563.5	7.4
140°-150°	432.6	5.7
150°-160°	311.0	4.1
160°-170°	190.0	2.5
170°-180°	64.1	0.8
0°-30°	1014.7	13.3
0°-40°	1652.8	21.7
0°-60°	2762.7	36.3
0°-90°	3282.2	43.2
90°-120°	2042.2	26.9
90°-150°	3756.7	49.4
90°-180°	4322.0	56.8
0°-180°	7604.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1312	1312	1312	1312	1312	
5°	1319	1305	1309	1304	1302	125
15°	1269	1256	1261	1257	1255	358
25°	1177	1162	1169	1156	1155	542
35°	1036	1024	1028	1014	1013	647
45°	839	828	824	809	807	643
55°	549	540	537	528	526	492
65°	295	293	296	294	294	299
75°	159	159	159	160	160	168
85°	41	43	45	45	45	47
90°	2	5	10	11	11	5
95°	48	170	513	262	182	50
105°	156	243	933	1396	1310	164
115°	276	337	777	1501	1698	271
125°	376	432	698	1179	1388	336
135°	453	505	678	951	1077	350
145°	524	564	670	813	873	328
155°	594	616	664	730	753	274
165°	645	652	666	693	696	182
175°	670	670	667	676	675	64
180°	670	670	670	670	670	

TEST NUMBER: P564398

CATALOG NUMBER: SQ4-PR1-125U-100D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1312.3	1312.3	1312.3	1312.3	1312.3
2.5°	1320.4	1309.0	1312.3	1309.5	1303.3
5°	1319.1	1304.7	1308.9	1304.3	1302.1
7.5°	1308.9	1294.8	1299.0	1294.4	1293.1
10°	1299.9	1286.6	1290.8	1286.3	1284.1
12.5°	1289.9	1275.8	1280.9	1275.4	1273.2
15°	1269.4	1256.1	1261.4	1256.9	1254.7
17.5°	1246.8	1232.6	1237.9	1232.7	1229.8
20°	1228.7	1215.4	1220.8	1212.8	1211.7
22.5°	1208.8	1195.5	1200.9	1190.2	1190.0
25°	1176.7	1162.3	1168.8	1156.3	1155.2
27.5°	1138.5	1125.2	1130.6	1117.9	1116.5
30°	1112.2	1099.0	1104.3	1090.7	1088.5
32.5°	1082.4	1070.0	1074.5	1060.9	1059.6
35°	1036.5	1024.4	1027.5	1013.9	1012.8
37.5°	984.3	973.2	975.0	960.1	959.0
40°	947.2	936.2	937.0	921.2	920.1
42.5°	906.5	895.5	894.5	878.7	877.6
45°	838.7	827.7	824.0	809.3	807.1
47.5°	761.4	750.3	743.5	731.5	730.0
50°	705.3	694.3	688.4	678.1	674.8
52.5°	644.7	633.7	628.7	619.3	616.0
55°	549.3	540.5	536.9	527.8	525.6
57.5°	458.7	452.7	451.7	442.8	442.0
60°	403.5	400.2	400.1	392.2	392.2
62.5°	356.5	354.1	355.8	350.6	349.7
65°	295.0	292.8	296.1	293.9	293.9
67.5°	246.4	246.4	248.4	247.5	247.5
70°	219.3	219.3	220.4	220.4	220.4
72.5°	194.9	194.0	196.9	196.9	196.0
75°	159.4	159.4	159.4	160.5	160.5
77.5°	124.1	124.3	125.2	125.0	124.1
80°	100.6	101.7	101.7	100.6	100.6
82.5°	77.1	78.2	78.2	78.0	77.1
85°	40.7	42.9	45.2	45.2	45.2
87.5°	12.1	16.3	20.1	20.3	19.4
90°	1.7	5.0	10.2	11.1	11.1
92.5°	20.8	73.5	145.3	70.0	48.6
95°	47.8	170.3	513.4	262.5	181.7
97.5°	76.2	195.0	805.2	672.7	507.3
100°	98.1	204.8	898.0	939.6	779.5
102.5°	119.2	218.6	928.7	1139.5	1008.0
105°	156.1	242.8	933.0	1395.8	1309.9
107.5°	190.9	268.2	893.3	1527.6	1549.8
110°	214.1	287.4	857.1	1568.5	1649.4



TEST NUMBER: P564398

CATALOG NUMBER: SQ4-PR1-125U-100D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	238.6	306.7	822.3	1559.4	1692.4
115°	275.5	337.2	776.9	1501.2	1698.0
117.5°	309.1	366.9	741.8	1408.2	1627.4
120°	330.9	386.8	724.1	1341.5	1566.6
122.5°	350.0	405.2	711.1	1273.3	1497.7
125°	376.1	432.0	697.6	1179.1	1387.6
127.5°	401.2	456.2	689.1	1096.0	1282.1
130°	416.2	471.2	685.7	1048.4	1211.9
132.5°	431.2	485.6	682.3	1006.5	1156.6
135°	452.9	505.4	678.0	951.2	1077.1
137.5°	473.5	523.9	675.8	904.3	1007.7
140°	487.8	536.2	673.7	875.4	968.8
142.5°	502.8	547.9	672.4	848.5	927.2
145°	523.6	564.5	669.5	813.3	873.3
147.5°	546.2	581.7	666.6	783.6	830.8
150°	561.2	592.0	665.2	765.0	804.2
152.5°	574.8	601.7	664.5	749.8	781.7
155°	594.4	616.1	663.5	729.7	753.0
157.5°	611.6	628.5	663.7	715.5	731.2
160°	622.6	636.7	664.4	707.3	718.9
162.5°	632.1	643.6	665.0	700.4	708.7
165°	644.7	652.2	666.1	692.6	695.9
167.5°	655.0	659.3	666.9	686.6	687.9
170°	661.8	663.5	666.9	683.1	683.1
172.5°	665.9	666.2	667.6	679.7	679.7
175°	670.3	669.5	666.9	676.3	674.6
177.5°	672.2	670.9	667.4	672.9	671.5
180°	669.5	669.5	669.5	669.5	669.5

(END OF REPORT)