

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564662

Luminaire Tested: **SQ4-PW1-050U-075D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564662
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-075D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4179.6 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564662
CATALOG NUMBER: SQ4-PW1-050U-075D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564662

CATALOG NUMBER: SQ4-PW1-050U-075D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	55	50
2	91	84	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	74	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	54	48	43	46	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	32	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	23
7	60	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	30	52	40	33	28	36	30	26	31	27	23	27	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8908	8908	8908
5°	8966	8895	8856
10°	8894	8822	8775
15°	8800	8703	8670
20°	8695	8562	8545
25°	8574	8418	8391
30°	8393	8265	8211
35°	8153	8038	7991
40°	7900	7777	7745
45°	7593	7492	7459
50°	7277	7217	7168
55°	6938	6938	6828
60°	6514	6639	6405
65°	5962	6259	5814
70°	5255	5759	5117
75°	4488	5155	4367
80°	3480	4341	3528
85°	2255	3335	2975



TEST NUMBER: P564662

CATALOG NUMBER: SQ4-PW1-050U-075D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	2.2
10°-20°	256.7	6.1
20°-30°	380.8	9.1
30°-40°	445.5	10.7
40°-50°	443.5	10.6
50°-60°	383.0	9.2
60°-70°	275.7	6.6
70°-80°	144.6	3.5
80°-90°	36.9	0.9
90°-100°	126.6	3.0
100°-110°	343.9	8.2
110°-120°	353.6	8.5
120°-130°	282.7	6.8
130°-140°	222.2	5.3
140°-150°	170.3	4.1
150°-160°	122.5	2.9
160°-170°	74.9	1.8
170°-180°	25.2	0.6
0°-30°	728.4	17.4
0°-40°	1173.9	28.1
0°-60°	2000.5	47.9
0°-90°	2457.6	58.8
90°-120°	824.1	19.7
90°-150°	1499.3	35.9
90°-180°	1722.0	41.2
0°-180°	4179.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	966	966	966	966	966	
5°	968	957	960	958	956	92
15°	921	910	911	909	908	260
25°	842	828	827	822	824	387
35°	724	714	714	707	710	453
45°	582	577	574	572	572	449
55°	431	430	431	425	424	385
65°	273	281	287	275	266	271
75°	126	138	145	135	122	135
85°	21	28	32	30	28	28
90°	1	3	6	8	8	2
95°	19	69	220	96	64	20
105°	61	95	378	576	542	65
115°	108	132	303	602	686	107
125°	149	170	274	462	544	133
135°	180	200	266	376	424	139
145°	208	223	263	319	343	130
155°	235	243	261	287	295	108
165°	254	258	262	273	274	72
175°	264	265	263	266	265	25
180°	264	264	264	264	264	

TEST NUMBER: P564662

CATALOG NUMBER: SQ4-PW1-050U-075D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	965.5	965.5	965.5	965.5	965.5
2.5°	971.0	963.0	965.5	963.4	958.7
5°	968.1	957.3	960.4	957.9	956.2
7.5°	958.2	948.3	950.6	947.8	946.8
10°	949.4	939.4	941.7	938.3	936.6
12.5°	939.2	928.5	930.8	927.4	926.4
15°	921.3	909.7	911.1	909.4	907.7
17.5°	900.6	888.7	889.0	886.3	885.9
20°	885.6	873.1	872.0	868.6	870.3
22.5°	869.2	856.1	855.0	850.2	852.6
25°	842.2	828.1	826.9	821.8	824.3
27.5°	810.9	796.9	796.9	789.9	792.5
30°	787.8	774.4	775.8	767.4	770.7
32.5°	763.3	751.3	752.0	743.6	746.9
35°	723.9	714.0	713.7	707.0	709.5
37.5°	683.8	675.0	673.6	669.7	670.4
40°	655.9	648.4	645.7	643.1	643.1
42.5°	626.6	619.8	617.1	615.2	614.5
45°	581.9	576.9	574.2	572.5	571.7
47.5°	537.6	533.0	530.7	529.5	528.6
50°	507.0	503.7	502.8	500.2	499.4
52.5°	476.4	474.4	473.5	470.2	469.4
55°	431.3	430.5	431.3	425.3	424.5
57.5°	384.3	385.7	388.4	380.4	378.4
60°	353.0	356.4	359.8	350.4	347.1
62.5°	321.1	326.4	331.3	320.4	315.8
65°	273.1	281.4	286.7	275.4	266.3
67.5°	226.8	237.1	243.5	231.3	221.0
70°	194.8	206.5	213.5	201.4	189.7
72.5°	166.9	179.9	185.6	174.1	162.5
75°	125.9	137.5	144.6	135.0	122.5
77.5°	89.3	100.3	106.2	97.8	87.5
80°	65.5	77.1	81.7	74.7	66.4
82.5°	46.4	56.1	59.2	55.0	49.3
85°	21.3	27.9	31.5	29.7	28.1
87.5°	5.6	10.8	14.1	14.5	15.1
90°	0.8	3.3	5.9	7.6	7.6
92.5°	7.6	34.7	60.2	25.9	21.9
95°	18.7	69.2	220.5	96.0	64.4
97.5°	30.9	76.5	338.0	263.0	184.7
100°	39.0	81.3	374.0	379.1	306.1
102.5°	47.1	86.1	383.5	468.8	404.5
105°	61.1	95.1	378.2	575.9	541.9
107.5°	75.5	105.5	356.3	631.1	640.6
110°	85.6	113.0	340.1	642.0	682.6

TEST NUMBER: P564662

CATALOG NUMBER: SQ4-PW1-050U-075D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	94.5	120.5	323.8	633.0	694.2
115°	108.5	131.8	302.7	602.3	686.0
117.5°	121.8	144.0	289.3	558.8	653.1
120°	130.6	152.2	283.2	529.6	623.3
122.5°	138.1	159.6	279.2	500.3	590.7
125°	149.2	170.0	273.9	461.5	544.4
127.5°	159.3	179.8	271.0	432.1	503.2
130°	165.4	185.3	269.7	413.6	477.4
132.5°	171.5	191.4	268.3	397.8	454.4
135°	179.8	199.7	266.3	375.9	424.0
137.5°	188.8	206.8	265.3	356.6	397.0
140°	194.2	211.6	264.6	344.3	380.8
142.5°	199.6	215.7	263.9	334.6	365.2
145°	207.8	222.7	262.9	319.4	343.4
147.5°	216.9	229.7	262.0	307.4	326.3
150°	223.0	233.8	262.0	300.5	315.5
152.5°	227.8	237.2	261.4	294.4	306.6
155°	234.9	243.2	261.2	286.8	295.1
157.5°	241.9	248.3	261.2	281.7	288.0
160°	245.9	251.7	261.2	278.3	283.2
162.5°	250.0	254.5	261.9	275.5	279.2
165°	254.4	257.7	262.0	273.1	273.9
167.5°	259.0	260.6	262.9	270.2	270.9
170°	260.3	262.0	262.9	268.8	268.8
172.5°	261.7	262.7	262.9	267.5	267.5
175°	263.7	264.6	262.9	266.3	265.4
177.5°	264.4	264.4	262.4	265.1	263.7
180°	263.7	263.7	263.7	263.7	263.7

(END OF REPORT)