

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565022

Luminaire Tested: **SQ4-PW1-125U-050D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565022
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-050D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5990.2 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 47.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565022
CATALOG NUMBER: SQ4-PW1-125U-050D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P565022

CATALOG NUMBER: SQ4-PW1-125U-050D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	32	31	30	24
2	85	77	72	67	75	69	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22	17
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	53	46	40	58	48	41	36	38	33	30	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	18	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6044	6044	6044
5°	6083	6035	6009
10°	6034	5986	5954
15°	5971	5905	5883
20°	5899	5809	5798
25°	5817	5711	5694
30°	5694	5608	5571
35°	5532	5455	5422
40°	5360	5276	5256
45°	5151	5083	5061
50°	4938	4896	4863
55°	4707	4707	4633
60°	4419	4504	4346
65°	4045	4246	3945
70°	3566	3909	3472
75°	3044	3497	2962
80°	2359	2943	2391
85°	1524	2265	2011



TEST NUMBER: P565022

CATALOG NUMBER: SQ4-PW1-125U-050D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.7	1.0
10°-20°	174.2	2.9
20°-30°	258.3	4.3
30°-40°	302.3	5.0
40°-50°	300.9	5.0
50°-60°	259.9	4.3
60°-70°	187.1	3.1
70°-80°	98.1	1.6
80°-90°	25.9	0.4
90°-100°	313.2	5.2
100°-110°	843.6	14.1
110°-120°	885.4	14.8
120°-130°	718.5	12.0
130°-140°	563.5	9.4
140°-150°	432.6	7.2
150°-160°	311.0	5.2
160°-170°	190.0	3.2
170°-180°	64.1	1.1
0°-30°	494.2	8.3
0°-40°	796.5	13.3
0°-60°	1357.3	22.7
0°-90°	1668.3	27.9
90°-120°	2042.2	34.1
90°-150°	3756.7	62.7
90°-180°	4322.0	72.2
0°-180°	5990.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	655	655	655	655	655	
5°	657	650	652	650	649	62
15°	625	617	618	617	616	176
25°	571	562	561	558	559	263
35°	491	484	484	480	481	307
45°	395	391	390	388	388	305
55°	293	292	293	289	288	261
65°	185	191	194	187	181	184
75°	85	93	98	92	83	92
85°	14	19	21	20	19	19
90°	2	5	10	11	11	4
95°	48	170	513	262	182	50
105°	156	243	933	1396	1310	164
115°	276	337	777	1501	1698	271
125°	376	432	698	1179	1388	336
135°	453	505	678	951	1077	350
145°	524	564	670	813	873	328
155°	594	616	664	730	753	274
165°	645	652	666	693	696	182
175°	670	670	667	676	675	64
180°	670	670	670	670	670	

TEST NUMBER: P565022

CATALOG NUMBER: SQ4-PW1-125U-050D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	655.1	655.1	655.1	655.1	655.1
2.5°	658.8	653.4	655.1	653.6	650.5
5°	656.8	649.5	651.6	649.9	648.8
7.5°	650.1	643.4	644.9	643.1	642.4
10°	644.1	637.4	638.9	636.6	635.5
12.5°	637.2	630.0	631.6	629.2	628.6
15°	625.1	617.2	618.2	617.0	615.9
17.5°	611.0	603.0	603.2	601.3	601.1
20°	600.8	592.4	591.6	589.3	590.5
22.5°	589.8	580.9	580.1	576.9	578.5
25°	571.4	561.8	561.0	557.6	559.3
27.5°	550.2	540.7	540.7	535.9	537.7
30°	534.5	525.4	526.4	520.7	522.9
32.5°	517.9	509.7	510.2	504.5	506.8
35°	491.2	484.4	484.3	479.7	481.4
37.5°	463.9	458.0	457.0	454.4	454.8
40°	445.0	439.9	438.1	436.4	436.4
42.5°	425.2	420.5	418.7	417.4	417.0
45°	394.8	391.4	389.6	388.4	387.9
47.5°	364.8	361.6	360.0	359.2	358.7
50°	344.0	341.7	341.1	339.4	338.8
52.5°	323.2	321.9	321.3	319.1	318.5
55°	292.6	292.1	292.6	288.6	288.0
57.5°	260.8	261.7	263.5	258.1	256.7
60°	239.5	241.8	244.1	237.7	235.5
62.5°	217.8	221.4	224.8	217.4	214.3
65°	185.3	190.9	194.5	186.9	180.7
67.5°	153.9	160.9	165.2	157.0	150.0
70°	132.2	140.1	144.9	136.6	128.7
72.5°	113.2	122.0	125.9	118.1	110.2
75°	85.4	93.3	98.1	91.6	83.1
77.5°	60.6	68.1	72.0	66.3	59.3
80°	44.4	52.3	55.4	50.7	45.0
82.5°	31.5	38.1	40.2	37.3	33.5
85°	14.4	18.9	21.4	20.2	19.0
87.5°	4.0	7.9	10.8	11.0	11.5
90°	1.7	5.0	10.2	11.1	11.1
92.5°	20.8	73.5	145.3	70.0	48.6
95°	47.8	170.3	513.4	262.5	181.7
97.5°	76.2	195.0	805.2	672.7	507.3
100°	98.1	204.8	898.0	939.6	779.5
102.5°	119.2	218.6	928.7	1139.5	1008.0
105°	156.1	242.8	933.0	1395.8	1309.9
107.5°	190.9	268.2	893.3	1527.6	1549.8
110°	214.1	287.4	857.1	1568.5	1649.4

TEST NUMBER: P565022

CATALOG NUMBER: SQ4-PW1-125U-050D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	238.6	306.7	822.3	1559.4	1692.4
115°	275.5	337.2	776.9	1501.2	1698.0
117.5°	309.1	366.9	741.8	1408.2	1627.4
120°	330.9	386.8	724.1	1341.5	1566.6
122.5°	350.0	405.2	711.1	1273.3	1497.7
125°	376.1	432.0	697.6	1179.1	1387.6
127.5°	401.2	456.2	689.1	1096.0	1282.1
130°	416.2	471.2	685.7	1048.4	1211.9
132.5°	431.2	485.6	682.3	1006.5	1156.6
135°	452.9	505.4	678.0	951.2	1077.1
137.5°	473.5	523.9	675.8	904.3	1007.7
140°	487.8	536.2	673.7	875.4	968.8
142.5°	502.8	547.9	672.4	848.5	927.2
145°	523.6	564.5	669.5	813.3	873.3
147.5°	546.2	581.7	666.6	783.6	830.8
150°	561.2	592.0	665.2	765.0	804.2
152.5°	574.8	601.7	664.5	749.8	781.7
155°	594.4	616.1	663.5	729.7	753.0
157.5°	611.6	628.5	663.7	715.5	731.2
160°	622.6	636.7	664.4	707.3	718.9
162.5°	632.1	643.6	665.0	700.4	708.7
165°	644.7	652.2	666.1	692.6	695.9
167.5°	655.0	659.3	666.9	686.6	687.9
170°	661.8	663.5	666.9	683.1	683.1
172.5°	665.9	666.2	667.6	679.7	679.7
175°	670.3	669.5	666.9	676.3	674.6
177.5°	672.2	670.9	667.4	672.9	671.5
180°	669.5	669.5	669.5	669.5	669.5

(END OF REPORT)