

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518475

Luminaire Tested: **SQ4-BB-050U-125D-840-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518475
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-050U-125D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15274.3 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 167
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518475
CATALOG NUMBER: SQ4-BB-050U-125D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P518475

CATALOG NUMBER: SQ4-BB-050U-125D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	102	99	96	93	96	93	90	88	81	79	78	71	70	68	61	61	60	55
2	95	89	84	79	89	84	79	76	74	71	68	65	63	61	57	55	54	50
3	88	80	74	69	83	76	70	66	67	63	60	60	57	54	52	50	48	45
4	82	73	66	61	77	69	63	58	61	57	53	55	51	48	48	46	44	41
5	76	66	59	54	72	63	56	52	56	51	48	50	47	44	45	42	40	37
6	71	60	53	48	67	57	51	46	52	47	43	47	43	40	42	39	36	34
7	66	55	48	43	62	53	46	42	48	43	39	43	39	36	39	36	33	31
8	62	51	44	39	59	49	42	38	44	39	35	40	36	33	36	33	31	29
9	58	47	40	36	55	45	39	35	41	36	33	37	33	30	34	31	28	26
10	55	44	37	33	52	42	36	32	38	33	30	35	31	28	32	29	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23808	23808	23808
5°	23425	23367	23540
10°	21918	22210	22830
15°	19926	20558	21703
20°	17687	18607	20237
25°	15403	16623	18593
30°	13194	14643	17037
35°	10939	12430	15158
40°	8405	9939	12916
45°	6076	7526	10393
50°	4140	5609	8243
55°	2691	4056	6406
60°	1543	2856	4630
65°	409	1744	2344
70°	202	539	673
75°	89	44	0
80°	66	0	0
85°	0	0	0



TEST NUMBER: P518475

CATALOG NUMBER: SQ4-BB-050U-125D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	706.5	4.6
10°-20°	1806.7	11.8
20°-30°	2261.8	14.8
30°-40°	2089.2	13.7
40°-50°	1403.8	9.2
50°-60°	725.1	4.7
60°-70°	227.1	1.5
70°-80°	14.4	0.1
80°-90°	3.8	0.0
90°-100°	443.8	2.9
100°-110°	1205.5	7.9
110°-120°	1239.5	8.1
120°-130°	991.0	6.5
130°-140°	778.7	5.1
140°-150°	597.1	3.9
150°-160°	429.4	2.8
160°-170°	262.6	1.7
170°-180°	88.5	0.6
0°-30°	4775.0	31.3
0°-40°	6864.2	44.9
0°-60°	8993.1	58.9
0°-90°	9238.4	60.5
90°-120°	2888.8	18.9
90°-150°	5255.5	34.4
90°-180°	6036.0	39.5
0°-180°	15274.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	7741	7741	7741	7741	7741	
5°	7588	7511	7569	7596	7625	703
15°	6258	6236	6457	6674	6816	1743
25°	4539	4576	4899	5234	5479	2081
35°	2914	2987	3311	3700	4037	1805
45°	1397	1481	1730	2067	2390	1097
55°	502	586	756	971	1195	468
65°	56	107	240	289	322	95
75°	8	8	4	0	0	11
85°	0	0	0	0	0	1
90°	3	12	21	27	27	5
95°	65	243	773	336	226	69
105°	214	333	1326	2019	1899	227
115°	380	462	1061	2111	2405	375
125°	523	596	960	1618	1908	466
135°	630	700	933	1318	1486	487
145°	728	781	922	1120	1204	457
155°	823	852	916	1005	1034	380
165°	892	903	918	957	960	252
175°	924	927	922	933	930	88
180°	924	924	924	924	924	



TEST NUMBER: P518475

CATALOG NUMBER: SQ4-BB-050U-125D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	7741.4	7741.4	7741.4	7741.4	7741.4
2.5°	7759.4	7686.2	7705.5	7705.0	7684.5
5°	7587.9	7511.0	7569.1	7596.0	7625.3
7.5°	7267.3	7207.2	7319.0	7402.7	7463.5
10°	7018.6	6967.3	7112.2	7226.5	7310.7
12.5°	6731.0	6691.4	6866.5	7023.3	7131.0
15°	6258.3	6236.3	6456.8	6673.5	6816.4
17.5°	5752.0	5751.2	6002.9	6272.0	6444.1
20°	5404.4	5415.4	5685.3	5982.0	6183.4
22.5°	5056.8	5082.5	5370.7	5680.0	5910.8
25°	4539.2	4575.9	4898.8	5233.9	5479.3
27.5°	4041.9	4095.3	4435.1	4783.5	5082.3
30°	3715.3	3777.5	4123.5	4490.1	4797.7
32.5°	3394.7	3468.7	3805.9	4193.6	4507.0
35°	2913.8	2987.0	3310.8	3700.5	4037.4
37.5°	2417.2	2489.0	2805.2	3188.7	3552.7
40°	2093.6	2174.2	2475.6	2847.3	3217.2
42.5°	1800.0	1880.5	2164.0	2529.2	2878.6
45°	1397.0	1481.2	1730.3	2067.2	2389.5
47.5°	1062.9	1154.5	1373.0	1677.8	1971.5
50°	865.2	956.7	1172.3	1440.8	1722.8
52.5°	706.4	795.0	989.5	1242.6	1501.1
55°	501.9	586.1	756.5	971.4	1194.7
57.5°	346.8	419.3	572.3	751.5	926.6
60°	250.9	320.5	464.4	610.0	752.8
62.5°	167.0	230.8	371.5	483.1	579.0
65°	56.2	107.4	239.7	289.1	322.1
67.5°	28.5	34.3	125.8	132.8	143.8
70°	22.5	22.5	59.9	63.9	74.9
72.5°	16.5	16.5	24.0	30.8	33.0
75°	7.5	7.5	3.7	0.0	0.0
77.5°	3.7	3.7	3.0	0.0	0.0
80°	3.7	3.7	0.0	0.0	0.0
82.5°	0.7	0.7	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	2.3	4.2	5.4	5.4
90°	3.0	11.7	20.8	26.8	26.8
92.5°	26.8	121.5	211.0	90.6	76.7
95°	65.4	242.7	772.8	336.3	225.9
97.5°	108.2	268.0	1184.8	921.8	647.4
100°	136.7	285.0	1310.9	1328.8	1073.1
102.5°	165.3	301.9	1344.1	1643.4	1417.9
105°	214.0	333.2	1325.7	2018.6	1899.4
107.5°	264.5	369.8	1249.0	2212.3	2245.4
110°	300.2	396.1	1192.0	2250.4	2392.8

TEST NUMBER: P518475

CATALOG NUMBER: SQ4-BB-050U-125D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.1	422.4	1134.9	2218.8	2433.2
115°	380.5	461.9	1061.2	2111.2	2404.7
117.5°	426.8	504.7	1014.2	1958.6	2289.4
120°	457.8	533.3	992.8	1856.3	2184.8
122.5°	483.9	559.5	978.5	1753.8	2070.6
125°	523.2	595.8	960.1	1617.7	1908.3
127.5°	558.2	630.3	950.0	1514.5	1763.9
130°	579.6	649.4	945.2	1449.7	1673.5
132.5°	601.0	670.8	940.5	1394.4	1592.6
135°	630.2	699.9	933.4	1317.7	1486.2
137.5°	661.7	725.0	929.8	1249.9	1391.7
140°	680.7	741.7	927.4	1206.7	1334.6
142.5°	699.7	756.1	925.0	1173.0	1279.9
145°	728.3	780.6	921.5	1119.6	1203.8
147.5°	760.4	805.1	918.5	1077.5	1143.8
150°	781.8	819.5	918.5	1053.4	1105.8
152.5°	798.4	831.5	916.1	1031.8	1074.8
155°	823.4	852.4	915.5	1005.3	1034.4
157.5°	847.7	870.4	915.5	987.4	1009.4
160°	862.0	882.4	915.5	975.4	992.8
162.5°	876.3	892.0	917.9	965.7	978.5
165°	891.7	903.4	918.5	957.2	960.1
167.5°	907.8	913.6	921.5	947.1	949.4
170°	912.5	918.4	921.5	942.3	942.3
172.5°	917.3	920.8	921.5	937.5	937.5
175°	924.4	927.3	921.5	933.3	930.4
177.5°	926.8	926.8	919.7	929.1	924.4
180°	924.4	924.4	924.4	924.4	924.4

(END OF REPORT)