

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P518547

Luminaire Tested: **SQ4-BB-075U-100D-840-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518547
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-075U-100D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16477.6 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 162.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518547
CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P518547

CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	98	95	91	88	90	87	84	82	73	71	69	60	59	58	48	47	47	41
2	91	84	79	75	83	78	74	70	66	63	60	55	53	51	44	43	42	37
3	84	76	69	64	77	70	65	60	60	56	53	50	47	45	41	39	38	33
4	78	68	61	56	71	63	57	53	54	50	46	46	42	40	38	36	34	30
5	72	62	55	49	66	57	51	46	49	45	41	42	38	36	35	32	31	28
6	67	56	49	44	62	52	46	41	45	40	37	38	35	32	32	30	28	25
7	62	51	44	39	57	48	42	37	41	37	33	36	32	29	30	27	26	23
8	58	47	40	35	54	44	38	33	38	33	30	33	29	27	28	25	23	21
9	54	43	36	32	50	41	34	30	35	31	27	31	27	25	26	24	22	20
10	51	40	33	29	47	38	32	28	33	28	25	29	25	23	24	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19084	19084	19084
5°	18777	18730	18869
10°	17569	17803	18300
15°	15972	16479	17396
20°	14178	14914	16221
25°	12347	13325	14904
30°	10575	11738	13656
35°	8769	9963	12150
40°	6737	7967	10353
45°	4870	6032	8330
50°	3318	4495	6607
55°	2157	3251	5135
60°	1237	2290	3711
65°	327	1398	1879
70°	162	432	540
75°	71	36	0
80°	53	0	0
85°	0	0	0



TEST NUMBER: P518547

CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	566.3	3.4
10°-20°	1448.2	8.8
20°-30°	1813.0	11.0
30°-40°	1674.6	10.2
40°-50°	1125.3	6.8
50°-60°	581.2	3.5
60°-70°	182.0	1.1
70°-80°	11.5	0.1
80°-90°	3.7	0.0
90°-100°	656.8	4.0
100°-110°	1807.0	11.0
110°-120°	1865.1	11.3
120°-130°	1494.3	9.1
130°-140°	1173.7	7.1
140°-150°	899.4	5.5
150°-160°	646.7	3.9
160°-170°	395.4	2.4
170°-180°	133.3	0.8
0°-30°	3827.5	23.2
0°-40°	5502.1	33.4
0°-60°	7208.6	43.7
0°-90°	7405.9	44.9
90°-120°	4328.8	26.3
90°-150°	7896.3	47.9
90°-180°	9072.0	55.1
0°-180°	16477.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6205	6205	6205	6205	6205	
5°	6082	6020	6067	6089	6112	564
15°	5016	4999	5176	5349	5464	1397
25°	3638	3668	3927	4195	4392	1668
35°	2336	2394	2654	2966	3236	1447
45°	1120	1187	1387	1657	1915	879
55°	402	470	606	779	958	375
65°	45	86	192	232	258	76
75°	6	6	3	0	0	9
85°	0	0	0	0	0	1
90°	3	12	21	27	27	7
95°	98	358	1161	497	317	103
105°	323	497	1991	3032	2830	340
115°	572	696	1597	3180	3609	564
125°	788	898	1449	2451	2871	703
135°	951	1055	1407	1982	2243	734
145°	1099	1174	1387	1689	1819	689
155°	1244	1285	1378	1518	1561	572
165°	1345	1362	1384	1440	1449	379
175°	1392	1395	1387	1404	1401	132
180°	1392	1392	1392	1392	1392	

TEST NUMBER: P518547

CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6205.3	6205.3	6205.3	6205.3	6205.3
2.5°	6219.7	6161.0	6176.4	6176.1	6159.6
5°	6082.2	6020.5	6067.2	6088.7	6112.2
7.5°	5825.2	5777.1	5866.6	5933.8	5982.5
10°	5625.9	5584.8	5700.9	5792.5	5860.0
12.5°	5395.3	5363.6	5504.0	5629.6	5715.9
15°	5016.4	4998.8	5175.6	5349.3	5463.8
17.5°	4610.6	4610.0	4811.7	5027.4	5165.4
20°	4332.0	4340.8	4557.1	4795.0	4956.4
22.5°	4053.4	4073.9	4305.0	4552.9	4737.9
25°	3638.5	3667.9	3926.7	4195.4	4392.0
27.5°	3239.8	3282.7	3555.0	3834.3	4073.8
30°	2978.0	3027.9	3305.3	3599.1	3845.6
32.5°	2721.1	2780.4	3050.7	3361.4	3612.7
35°	2335.6	2394.3	2653.8	2966.2	3236.2
37.5°	1937.5	1995.1	2248.5	2556.0	2847.8
40°	1678.2	1742.7	1984.4	2282.3	2578.8
42.5°	1442.8	1507.4	1734.6	2027.4	2307.4
45°	1119.8	1187.3	1387.0	1657.0	1915.3
47.5°	852.0	925.4	1100.6	1344.9	1580.3
50°	693.5	766.9	939.6	1154.9	1380.9
52.5°	566.2	637.2	793.1	996.0	1203.2
55°	402.3	469.8	606.4	778.6	957.7
57.5°	278.0	336.1	458.7	602.4	742.7
60°	201.1	256.9	372.3	488.9	603.4
62.5°	133.9	185.0	297.8	387.2	464.1
65°	45.0	86.1	192.1	231.8	258.2
67.5°	22.8	27.5	100.9	106.5	115.3
70°	18.0	18.0	48.0	51.2	60.0
72.5°	13.2	13.2	19.2	24.7	26.4
75°	6.0	6.0	3.0	0.0	0.0
77.5°	3.0	3.0	2.4	0.0	0.0
80°	3.0	3.0	0.0	0.0	0.0
82.5°	0.6	0.6	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	2.3	4.1	5.3	5.3
90°	3.0	11.7	20.7	26.7	26.7
92.5°	40.9	174.7	302.8	116.3	95.4
95°	97.8	358.5	1161.4	496.6	317.0
97.5°	159.4	397.5	1772.4	1365.6	963.5
100°	204.4	421.7	1964.3	1982.7	1617.7
102.5°	247.1	450.5	2014.1	2459.8	2124.9
105°	322.9	496.8	1991.0	3032.3	2829.5
107.5°	395.2	554.0	1877.8	3312.6	3372.9
110°	447.4	592.2	1792.5	3382.3	3590.9



TEST NUMBER: P518547

CATALOG NUMBER: SQ4-BB-075U-100D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	494.8	635.0	1707.2	3337.4	3654.9
115°	571.8	696.4	1597.0	3180.0	3608.7
117.5°	645.3	760.0	1527.0	2959.0	3444.0
120°	690.3	800.4	1496.2	2793.5	3294.6
122.5°	730.6	840.7	1474.9	2648.3	3124.0
125°	788.1	898.2	1448.8	2450.9	2871.0
127.5°	842.6	947.5	1431.6	2286.2	2654.7
130°	871.1	978.3	1422.2	2188.3	2524.3
132.5°	904.3	1011.4	1415.0	2102.2	2405.8
135°	951.1	1055.4	1407.3	1982.1	2242.8
137.5°	994.9	1091.7	1400.8	1885.1	2100.0
140°	1028.1	1117.9	1398.4	1820.6	2014.7
142.5°	1056.5	1139.4	1393.7	1763.1	1929.4
145°	1099.2	1174.5	1386.6	1688.8	1819.2
147.5°	1144.8	1209.7	1383.0	1623.0	1727.3
150°	1173.3	1231.2	1380.7	1586.9	1668.1
152.5°	1199.3	1252.7	1378.3	1555.8	1623.0
155°	1244.4	1284.9	1377.7	1517.9	1561.4
157.5°	1277.0	1310.0	1377.7	1486.8	1517.0
160°	1300.7	1326.7	1377.7	1470.1	1493.3
162.5°	1319.6	1341.1	1380.1	1455.8	1474.3
165°	1345.1	1362.5	1383.6	1440.1	1448.8
167.5°	1362.9	1376.2	1386.6	1426.9	1429.3
170°	1374.7	1383.4	1386.6	1422.2	1422.2
172.5°	1384.2	1388.3	1386.6	1415.0	1412.7
175°	1392.5	1395.4	1386.6	1404.3	1401.4
177.5°	1394.9	1394.9	1385.4	1399.5	1394.9
180°	1392.5	1392.5	1392.5	1392.5	1392.5

(END OF REPORT)