

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519064

Luminaire Tested: **SQ4-WB-025U-125D-940-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519064
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-125D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4392.8 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519064
CATALOG NUMBER: SQ4-WB-025U-125D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519064

CATALOG NUMBER: SQ4-WB-025U-125D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	84	84	84	81	
1	106	103	99	96	102	99	96	93	91	89	87	84	82	81	77	76	75	75	75	75	72	
2	99	92	86	82	94	89	84	79	82	78	75	76	73	70	71	68	66	66	66	66	63	
3	91	83	76	71	87	80	74	69	74	69	65	69	65	62	64	61	59	59	59	59	56	
4	85	75	67	62	81	72	66	60	67	62	58	63	59	55	59	55	52	52	52	52	50	
5	79	68	60	55	75	66	59	54	62	56	51	58	53	49	54	50	47	47	47	47	45	
6	73	62	54	49	70	60	53	48	56	51	46	53	48	44	50	46	43	43	43	43	40	
7	69	57	49	44	66	55	48	43	52	46	42	49	44	40	46	42	39	39	39	39	37	
8	64	52	45	40	62	51	44	39	48	42	38	46	40	37	43	39	35	35	35	35	34	
9	60	49	41	37	58	47	41	36	45	39	35	42	37	34	40	36	33	33	33	33	31	
10	57	45	38	34	55	44	37	33	42	36	32	40	35	31	38	33	30	30	30	30	28	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22469	22469	22469
5°	22188	22109	22238
10°	20963	21153	21644
15°	19352	19801	20689
20°	17574	18235	19441
25°	15763	16622	18112
30°	14094	15016	16735
35°	12324	13215	15105
40°	10373	11197	13076
45°	8561	9299	10917
50°	7148	7791	9096
55°	6067	6687	7512
60°	5185	5798	5993
65°	4128	4875	3873
70°	3661	3806	2363
75°	3390	3087	1447
80°	3124	2837	1249
85°	2826	2604	1016



TEST NUMBER: P519064

CATALOG NUMBER: SQ4-WB-025U-125D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.4	5.1
10°-20°	581.0	13.2
20°-30°	752.6	17.1
30°-40°	737.0	16.8
40°-50°	564.1	12.8
50°-60°	375.9	8.6
60°-70°	205.1	4.7
70°-80°	85.5	1.9
80°-90°	24.9	0.6
90°-100°	63.4	1.4
100°-110°	166.7	3.8
110°-120°	172.9	3.9
120°-130°	138.7	3.2
130°-140°	108.8	2.5
140°-150°	83.5	1.9
150°-160°	60.2	1.4
160°-170°	36.8	0.8
170°-180°	12.4	0.3
0°-30°	1556.9	35.4
0°-40°	2293.9	52.2
0°-60°	3233.9	73.6
0°-90°	3549.3	80.8
90°-120°	403.0	9.2
90°-150°	734.0	16.7
90°-180°	843.0	19.2
0°-180°	4392.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2435	2435	2435	2435	2435	
5°	2396	2372	2387	2393	2401	223
15°	2026	2019	2073	2129	2166	566
25°	1548	1552	1633	1704	1779	712
35°	1094	1099	1173	1252	1341	680
45°	656	669	713	767	837	512
55°	377	393	416	431	467	342
65°	189	205	223	195	177	197
75°	95	95	87	59	41	102
85°	27	27	25	16	10	29
90°	1	2	7	3	3	2
95°	8	33	109	56	38	9
105°	30	46	184	280	261	32
115°	53	65	148	295	336	53
125°	74	83	134	227	268	66
135°	88	97	130	183	208	68
145°	103	109	128	156	168	64
155°	116	119	128	141	145	53
165°	125	127	128	134	135	35
175°	130	130	129	131	131	12
180°	130	130	130	130	130	

TEST NUMBER: P519064

CATALOG NUMBER: SQ4-WB-025U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2435.3	2435.3	2435.3	2435.3	2435.3
2.5°	2441.3	2419.5	2425.0	2424.9	2418.2
5°	2395.7	2371.7	2387.2	2392.7	2401.1
7.5°	2306.8	2288.7	2316.9	2337.8	2354.7
10°	2237.6	2221.9	2257.9	2288.3	2310.3
12.5°	2157.2	2144.1	2188.7	2229.5	2258.1
15°	2026.0	2018.7	2073.0	2129.4	2166.0
17.5°	1885.6	1882.1	1944.4	2010.2	2057.0
20°	1789.9	1788.8	1857.2	1925.7	1980.1
22.5°	1693.3	1695.6	1767.4	1838.7	1900.6
25°	1548.4	1552.5	1632.8	1703.9	1779.2
27.5°	1414.4	1416.2	1499.2	1574.3	1654.6
30°	1322.9	1328.1	1409.5	1487.2	1570.8
32.5°	1231.4	1237.5	1317.1	1397.5	1482.8
35°	1094.2	1099.4	1173.3	1252.3	1341.1
37.5°	952.7	959.8	1025.4	1100.1	1187.4
40°	861.3	871.7	929.7	1000.0	1085.7
42.5°	773.2	786.2	839.9	906.6	983.9
45°	656.1	668.6	712.7	766.7	836.7
47.5°	555.2	569.7	603.5	650.0	709.7
50°	498.0	511.5	542.8	577.2	633.7
52.5°	447.5	461.1	489.0	515.5	563.6
55°	377.2	392.9	415.7	431.4	467.0
57.5°	319.5	334.5	352.6	359.7	381.3
60°	281.0	297.8	314.2	313.4	324.8
62.5°	246.0	260.2	276.5	265.2	265.9
65°	189.1	204.8	223.3	195.1	177.4
67.5°	152.8	156.1	175.2	136.1	115.0
70°	135.7	135.7	141.1	105.4	87.6
72.5°	119.5	119.5	114.6	85.7	67.1
75°	95.1	95.1	86.6	59.4	40.6
77.5°	73.3	72.5	66.3	44.3	29.5
80°	58.8	58.8	53.4	35.0	23.5
82.5°	45.9	45.9	41.5	27.3	17.5
85°	26.7	26.7	24.6	15.9	9.6
87.5°	9.6	9.9	9.9	5.8	4.9
90°	0.8	2.5	6.7	3.3	3.3
92.5°	3.5	16.9	37.4	16.5	10.7
95°	8.3	32.8	109.3	56.3	38.4
97.5°	14.5	36.0	163.5	130.0	95.8
100°	19.2	38.8	180.2	182.6	141.8
102.5°	23.2	41.5	184.8	227.4	192.5
105°	30.0	45.5	184.3	279.8	261.1
107.5°	37.0	51.4	173.8	307.1	311.6
110°	41.7	54.8	165.2	314.1	333.7



TEST NUMBER: P519064

CATALOG NUMBER: SQ4-WB-025U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	46.4	58.8	157.2	309.6	339.7
115°	53.4	64.8	147.6	294.6	336.2
117.5°	60.2	70.7	141.1	273.6	319.8
120°	64.2	74.0	138.5	259.6	304.5
122.5°	68.2	78.0	136.5	245.6	289.8
125°	74.2	83.2	134.3	227.0	267.8
127.5°	79.1	88.2	132.5	212.0	246.4
130°	81.7	91.5	131.8	202.6	234.4
132.5°	84.4	94.2	131.1	194.5	223.0
135°	88.4	97.4	130.1	183.2	207.7
137.5°	92.6	101.4	130.0	174.8	194.9
140°	95.9	104.1	129.3	168.1	186.8
142.5°	98.6	106.1	129.3	163.4	179.5
145°	102.6	109.1	128.5	156.3	168.5
147.5°	106.6	113.0	128.5	150.4	160.5
150°	109.3	115.0	128.5	147.0	155.1
152.5°	111.9	116.3	128.5	144.3	150.5
155°	115.9	119.2	128.5	141.1	145.1
157.5°	118.9	122.0	128.5	138.2	141.1
160°	120.9	123.4	128.5	136.8	138.5
162.5°	123.0	124.7	128.5	135.5	137.1
165°	125.1	126.8	128.5	133.5	135.1
167.5°	127.1	127.9	129.3	132.6	133.3
170°	128.5	129.3	129.3	132.6	132.6
172.5°	129.1	129.3	129.3	131.9	131.3
175°	130.1	130.1	129.3	131.0	131.0
177.5°	130.1	130.1	129.5	130.8	130.1
180°	130.1	130.1	130.1	130.1	130.1

(END OF REPORT)