

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520227

Luminaire Tested: **SQ4-F-100U-100D-840-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P520227
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G3-1910-536-19)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-F-100U-100D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24105.2 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 183.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520227
CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P520227

CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	42
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	31	27	25	22
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	45	37	32	53	42	35	30	36	31	26	31	26	23	25	22	19	17
8	54	41	33	28	49	38	31	27	33	27	23	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	34	27	22	43	32	26	21	28	23	19	24	19	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13453	13453	13453
5°	13514	13328	13430
10°	13445	13276	13380
15°	13364	13182	13287
20°	13226	13069	13177
25°	13082	12929	13030
30°	12922	12784	12848
35°	12760	12602	12670
40°	12548	12403	12415
45°	12327	12157	12118
50°	12009	11865	11837
55°	11655	11526	11446
60°	11302	11099	11062
65°	10750	10509	10421
70°	9989	9746	9557
75°	8918	8634	8456
80°	7339	7072	6753
85°	4344	4767	4873



TEST NUMBER: P520227

CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	412.9	1.7
10°-20°	1175.7	4.9
20°-30°	1765.6	7.3
30°-40°	2107.1	8.7
40°-50°	2159.8	9.0
50°-60°	1923.3	8.0
60°-70°	1433.7	5.9
70°-80°	776.2	3.2
80°-90°	180.5	0.7
90°-100°	877.2	3.6
100°-110°	2421.6	10.0
110°-120°	2497.4	10.4
120°-130°	2006.9	8.3
130°-140°	1577.2	6.5
140°-150°	1209.6	5.0
150°-160°	869.4	3.6
160°-170°	531.7	2.2
170°-180°	179.2	0.7
0°-30°	3354.2	13.9
0°-40°	5461.4	22.7
0°-60°	9544.5	39.6
0°-90°	11935.0	49.5
90°-120°	5796.2	24.0
90°-150°	10589.9	43.9
90°-180°	12170.0	50.5
0°-180°	24105.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4374	4374	4374	4374	4374	
5°	4378	4369	4317	4356	4350	415
15°	4197	4183	4140	4173	4173	1182
25°	3855	3846	3810	3831	3840	1776
35°	3399	3384	3357	3363	3375	2122
45°	2834	2820	2795	2780	2786	2181
55°	2174	2177	2150	2129	2135	1946
65°	1477	1471	1444	1429	1432	1461
75°	750	742	727	712	712	799
85°	123	135	135	138	138	172
90°	6	12	24	27	30	12
95°	129	475	1591	654	426	138
105°	432	666	2664	4067	3830	459
115°	773	934	2146	4248	4831	760
125°	1061	1207	1945	3292	3863	944
135°	1277	1414	1891	2666	3006	988
145°	1480	1583	1867	2270	2442	927
155°	1669	1725	1852	2036	2101	769
165°	1807	1830	1861	1933	1948	509
175°	1873	1876	1864	1891	1885	178
180°	1873	1873	1873	1873	1873	



TEST NUMBER: P520227

CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4374.5	4374.5	4374.5	4374.5	4374.5
2.5°	4391.3	4381.9	4343.3	4374.4	4369.6
5°	4377.5	4368.6	4317.4	4356.3	4350.4
7.5°	4336.6	4327.8	4282.6	4318.5	4313.2
10°	4305.4	4296.6	4251.3	4287.3	4284.4
12.5°	4264.6	4255.8	4210.5	4246.5	4243.6
15°	4197.3	4182.7	4140.3	4173.3	4173.3
17.5°	4108.4	4097.3	4058.0	4085.7	4086.3
20°	4041.2	4032.4	3993.2	4023.2	4026.2
22.5°	3974.0	3965.2	3921.1	3948.8	3954.2
25°	3855.1	3846.3	3810.0	3831.2	3840.0
27.5°	3732.5	3719.6	3683.9	3702.7	3709.1
30°	3638.9	3633.0	3599.9	3609.1	3617.9
32.5°	3540.4	3534.6	3506.2	3510.8	3526.6
35°	3398.7	3384.1	3356.7	3363.0	3374.6
37.5°	3231.2	3224.1	3197.6	3194.2	3205.3
40°	3125.5	3113.8	3089.5	3083.6	3092.5
42.5°	3010.2	2998.4	2969.4	2963.6	2974.7
45°	2834.2	2819.6	2795.2	2780.3	2786.2
47.5°	2637.3	2637.3	2612.1	2594.9	2603.7
50°	2510.0	2510.0	2479.9	2465.2	2474.0
52.5°	2377.9	2380.3	2347.9	2340.0	2337.1
55°	2173.8	2176.6	2149.7	2128.8	2134.7
57.5°	1976.8	1970.3	1938.9	1925.2	1928.1
60°	1837.5	1828.7	1804.4	1783.8	1798.4
62.5°	1695.8	1691.6	1667.6	1644.1	1642.3
65°	1477.2	1471.3	1444.1	1429.2	1432.1
67.5°	1259.8	1252.8	1227.9	1206.5	1214.2
70°	1110.9	1110.9	1083.9	1071.7	1062.9
72.5°	974.0	962.2	942.2	925.2	918.7
75°	750.5	741.8	726.6	711.6	711.6
77.5°	546.4	538.8	529.0	518.7	515.8
80°	414.4	411.4	399.3	395.9	381.3
82.5°	291.8	291.2	284.1	276.2	275.6
85°	123.1	134.9	135.1	138.1	138.1
87.5°	22.8	38.0	38.4	34.3	34.8
90°	6.0	11.9	23.9	27.0	30.0
92.5°	53.9	223.9	400.4	146.1	113.9
95°	128.9	474.6	1591.4	654.2	425.6
97.5°	213.4	531.6	2357.4	1814.9	1314.5
100°	275.7	565.8	2640.2	2658.9	2160.7
102.5°	335.6	604.6	2695.4	3285.3	2812.9
105°	431.6	665.9	2664.3	4067.4	3830.1
107.5°	533.5	742.1	2515.6	4444.6	4531.3
110°	605.4	793.0	2400.5	4525.8	4807.0



TEST NUMBER: P520227

CATALOG NUMBER: SQ4-F-100U-100D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	670.1	850.6	2292.6	4461.7	4876.5
115°	773.2	934.4	2145.8	4247.9	4831.0
117.5°	863.1	1023.6	2049.3	3947.0	4610.5
120°	923.0	1081.3	2010.9	3743.3	4411.4
122.5°	980.6	1131.8	1979.7	3553.2	4186.1
125°	1060.9	1207.4	1945.0	3291.6	3863.0
127.5°	1129.2	1275.8	1924.6	3070.4	3563.4
130°	1174.8	1321.3	1915.0	2935.2	3383.5
132.5°	1217.9	1357.4	1905.4	2821.5	3227.6
135°	1276.7	1414.4	1891.1	2665.9	3005.9
137.5°	1342.6	1468.0	1883.9	2535.4	2825.5
140°	1378.6	1501.6	1879.0	2448.3	2703.2
142.5°	1419.3	1533.0	1874.3	2370.9	2595.3
145°	1480.5	1583.0	1867.1	2269.6	2442.5
147.5°	1539.2	1628.8	1860.5	2184.2	2318.4
150°	1582.4	1655.7	1858.0	2133.2	2241.7
152.5°	1615.9	1684.5	1855.7	2089.7	2179.3
155°	1669.3	1725.0	1852.1	2036.4	2100.8
157.5°	1718.5	1761.2	1852.7	1997.5	2041.4
160°	1747.2	1785.2	1855.1	1975.7	2007.9
162.5°	1771.2	1804.5	1857.5	1956.4	1981.6
165°	1807.1	1830.5	1861.1	1933.3	1948.0
167.5°	1834.7	1848.8	1864.1	1919.3	1924.0
170°	1849.0	1860.8	1864.1	1912.1	1912.1
172.5°	1861.1	1868.1	1864.1	1902.4	1900.0
175°	1873.1	1876.0	1864.1	1890.9	1885.1
177.5°	1877.8	1875.6	1863.5	1880.1	1875.5
180°	1873.1	1873.1	1873.1	1873.1	1873.1

(END OF REPORT)