

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936917

Luminaire Tested: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936917
REPORT IS A COMBINATION OF REPORTS P933464 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17971.7 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 168
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936917
CATALOG NUMBER: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P936917

CATALOG NUMBER: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67	67	67	67
1	101	96	92	88	95	91	87	83	80	78	75	71	69	67	62	61	59	55	55	55	55
2	91	83	76	71	86	78	72	67	70	65	61	61	58	55	54	51	49	45	45	45	45
3	83	72	64	58	77	68	61	55	61	55	50	54	49	45	47	44	41	37	37	37	37
4	75	64	55	48	70	60	52	46	53	47	42	47	42	38	42	38	34	31	31	31	31
5	69	56	47	41	64	53	45	39	47	41	36	42	37	32	37	33	29	26	26	26	26
6	63	50	41	35	59	47	39	34	42	36	31	38	32	28	33	29	25	23	23	23	23
7	58	45	36	30	55	43	35	29	38	32	27	34	29	24	30	26	22	20	20	20	20
8	54	41	32	27	51	39	31	26	35	28	24	31	26	22	27	23	20	17	17	17	17
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17	15	15	15	15
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4825	4825	4825
5°	4715	5578	6485
10°	4279	8133	10752
15°	3638	10628	12983
20°	2963	12319	13231
25°	2473	12895	12963
30°	2086	12980	12938
35°	1845	12767	13272
40°	1609	12491	13618
45°	1458	12290	13672
50°	1338	12108	13445
55°	1283	11843	12849
60°	1315	11328	11908
65°	1370	10543	10615
70°	1463	9201	8967
75°	1627	7509	6998
80°	1791	5213	4716
85°	1627	2771	2413

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13672 cd/sqm



TEST NUMBER: P936917

CATALOG NUMBER: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.8	1.1
10°-20°	894.3	5.0
20°-30°	1564.3	8.7
30°-40°	2013.7	11.2
40°-50°	2249.2	12.5
50°-60°	2154.2	12.0
60°-70°	1707.2	9.5
70°-80°	1003.9	5.6
80°-90°	282.4	1.6
90°-100°	443.7	2.5
100°-110°	1166.5	6.5
110°-120°	1209.5	6.7
120°-130°	970.2	5.4
130°-140°	761.3	4.2
140°-150°	584.3	3.3
150°-160°	420.8	2.3
160°-170°	257.5	1.4
170°-180°	87.0	0.5
0°-30°	2660.3	14.8
0°-40°	4674.0	26.0
0°-60°	9077.4	50.5
0°-90°	12070.9	67.2
90°-120°	2819.7	15.7
90°-150°	5135.5	28.6
90°-180°	5901.0	32.8
0°-180°	17971.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1560	1560	1560	1560	1560	
5°	1520	1630	1836	2077	2152	140
15°	1139	2102	3541	4294	4429	317
25°	727	2382	4218	4404	4409	335
35°	492	2277	3972	4198	4364	307
45°	336	1816	3511	4023	4203	260
55°	241	1154	2979	3461	3556	219
65°	191	612	2212	2488	2523	189
75°	140	376	1214	1334	1339	147
85°	50	115	301	331	336	53
90°	6	17	46	23	23	8
95°	59	230	764	394	268	65
105°	210	318	1290	1958	1827	223
115°	373	453	1033	2061	2352	369
125°	519	582	940	1588	1873	461
135°	619	681	910	1282	1453	479
145°	718	764	899	1094	1179	450
155°	811	834	899	987	1015	373
165°	876	887	899	934	946	247
175°	910	910	905	916	916	86
180°	910	910	910	910	910	



TEST NUMBER: P936917

CATALOG NUMBER: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1560.0	1560.0	1560.0	1560.0	1560.0	1560.0	1560.0	1560.0	1560.0	1560.0	1560.0
2.5°	1560.0	1560.0	1569.9	1575.0	1584.9	1590.0	1600.1	1610.0	1640.2	1645.2	1655.2
5°	1519.7	1539.8	1605.0	1630.1	1700.3	1795.7	1835.8	1901.0	2036.4	2076.6	2101.6
7.5°	1459.6	1504.7	1665.3	1705.4	1881.0	2131.7	2237.0	2377.5	2593.2	2698.5	2783.8
10°	1364.3	1459.6	1745.5	1840.7	2126.7	2507.8	2703.5	2899.1	3225.1	3370.6	3425.8
12.5°	1259.0	1414.4	1830.8	1961.2	2372.5	2929.2	3165.0	3380.6	3751.8	3947.5	3977.5
15°	1138.6	1349.2	1911.0	2101.6	2633.3	3280.4	3541.1	3807.0	4153.1	4293.6	4328.6
17.5°	1033.3	1299.1	1986.3	2186.8	2833.9	3596.3	3862.2	4082.8	4363.7	4459.0	4484.1
20°	902.8	1218.8	2036.4	2297.2	3044.6	3827.0	4082.8	4253.3	4444.0	4504.2	4514.2
22.5°	807.5	1133.5	2066.5	2337.3	3185.0	3967.5	4183.2	4318.5	4449.0	4469.0	4474.1
25°	727.3	1038.3	2061.5	2382.5	3305.4	4052.8	4218.3	4318.5	4393.8	4403.8	4403.8
27.5°	652.1	933.0	2041.4	2392.5	3395.7	4072.8	4203.2	4273.4	4308.6	4328.6	4328.6
30°	586.9	832.6	1991.2	2372.5	3435.8	4052.8	4158.1	4193.2	4228.3	4258.4	4273.4
32.5°	536.7	737.3	1916.0	2332.4	3440.8	4002.6	4077.9	4097.9	4148.0	4218.3	4243.4
35°	491.5	642.0	1830.8	2277.1	3410.8	3922.4	3972.5	3992.6	4092.9	4198.2	4233.3
37.5°	446.4	571.8	1720.4	2181.9	3365.6	3827.0	3862.2	3897.3	4052.8	4178.2	4218.3
40°	401.2	511.6	1590.0	2076.6	3295.4	3711.7	3741.8	3797.0	4002.6	4148.0	4188.1
42.5°	366.2	461.5	1449.6	1966.2	3205.1	3581.3	3626.5	3706.7	3942.4	4097.9	4143.1
45°	336.0	411.3	1299.1	1815.7	3089.7	3445.8	3511.1	3621.4	3872.2	4022.6	4062.8
47.5°	306.0	376.2	1143.6	1660.2	2964.3	3310.4	3395.7	3521.0	3776.9	3922.4	3957.4
50°	280.9	341.1	988.1	1494.7	2828.9	3165.0	3265.2	3395.7	3656.5	3791.9	3837.1
52.5°	260.8	311.0	842.7	1329.2	2673.4	3014.5	3129.9	3265.2	3511.1	3641.5	3671.5
55°	240.8	285.9	717.3	1153.6	2512.9	2853.9	2979.4	3109.8	3350.5	3460.9	3480.9
57.5°	230.7	265.9	612.0	988.1	2342.4	2673.4	2813.8	2934.3	3159.9	3245.2	3265.2
60°	215.7	250.8	531.6	847.7	2156.8	2502.9	2623.2	2743.7	2934.3	3004.4	3019.5
62.5°	200.7	240.8	471.5	712.2	1966.2	2302.2	2422.6	2532.9	2693.5	2743.7	2763.7
65°	190.6	230.7	426.3	612.0	1770.6	2091.6	2211.9	2307.3	2437.7	2487.8	2497.9
67.5°	180.6	220.7	391.2	526.7	1575.0	1881.0	1971.2	2061.5	2161.8	2211.9	2217.0
70°	165.5	210.6	361.1	466.4	1374.3	1640.2	1715.4	1810.7	1890.9	1916.0	1931.0
72.5°	155.5	195.6	341.1	421.3	1168.7	1409.5	1479.6	1534.9	1605.0	1630.1	1630.1
75°	140.4	175.6	321.0	376.2	958.0	1153.6	1213.9	1269.0	1324.1	1334.2	1319.2
77.5°	125.4	155.5	275.8	316.0	747.3	912.9	963.0	993.1	1038.3	1048.3	1053.3
80°	105.3	135.5	215.7	245.8	541.7	672.1	707.2	732.3	772.4	772.4	782.5
82.5°	80.2	105.3	155.5	175.6	366.2	461.5	491.5	506.5	531.6	531.6	531.6
85°	50.2	65.2	100.3	115.4	220.7	280.9	300.9	306.0	326.0	331.1	331.1
87.5°	25.1	35.1	65.2	70.2	115.4	145.4	145.4	155.5	155.5	150.5	145.4
90°	6.1	11.0	15.9	17.1	26.9	39.9	46.4	41.3	30.9	23.2	23.2
92.5°	24.4	65.9	107.5	117.9	165.7	229.5	261.4	229.1	164.5	116.1	111.4
95°	58.7	134.7	210.7	229.7	407.8	645.5	764.2	681.9	517.4	394.0	380.0
97.5°	101.4	168.5	235.5	252.3	549.4	945.5	1143.6	1091.6	987.6	909.7	883.1
100°	134.4	195.2	256.0	271.2	600.9	1040.5	1260.3	1264.0	1271.7	1277.4	1245.7
102.5°	162.5	219.2	275.9	290.2	624.5	1070.4	1293.3	1359.5	1492.0	1591.4	1564.2
105°	210.1	258.2	306.2	318.2	642.0	1073.8	1289.6	1438.1	1735.1	1957.9	1943.3
107.5°	259.1	303.8	348.7	359.8	645.4	1026.0	1216.3	1423.5	1837.9	2148.6	2152.2
110°	292.1	332.5	373.0	383.0	640.4	983.7	1155.3	1386.9	1850.0	2197.4	2212.6



TEST NUMBER: P936917

CATALOG NUMBER: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	324.4	362.9	401.4	411.1	640.6	946.6	1099.6	1336.7	1810.7	2166.3	2189.6
115°	373.3	408.8	444.4	453.3	646.5	904.2	1033.1	1261.4	1718.0	2060.6	2093.0
117.5°	421.5	453.8	486.1	494.2	658.5	877.6	987.2	1193.3	1605.4	1914.5	1950.4
120°	449.6	480.1	510.4	518.0	668.3	868.7	968.9	1157.2	1533.8	1816.2	1851.1
122.5°	477.1	507.8	538.5	546.2	682.4	864.0	954.8	1124.3	1463.5	1717.8	1752.2
125°	519.3	547.3	575.2	582.2	701.4	860.2	939.6	1083.6	1371.6	1587.7	1619.4
127.5°	553.5	581.7	610.0	617.0	720.3	857.9	926.7	1050.4	1297.7	1483.3	1510.1
130°	571.9	602.3	632.6	640.2	734.1	859.3	921.9	1032.0	1252.2	1417.3	1442.0
132.5°	590.7	621.2	651.6	659.2	745.3	860.2	917.6	1016.2	1213.3	1361.1	1383.2
135°	618.9	646.5	674.2	681.1	757.5	859.4	910.2	992.8	1157.9	1281.7	1300.8
137.5°	647.5	675.0	702.5	709.3	775.9	864.7	909.1	978.8	1118.4	1223.0	1238.7
140°	671.3	696.6	721.8	728.2	787.0	865.5	904.7	965.0	1085.6	1176.0	1190.6
142.5°	689.7	713.0	736.5	742.3	796.4	868.6	904.7	957.7	1063.6	1143.0	1155.6
145°	717.8	738.1	758.5	763.6	808.7	868.6	898.7	942.0	1028.6	1093.5	1103.0
147.5°	745.9	765.7	785.6	790.5	826.6	874.7	898.7	932.8	1000.9	1052.0	1059.9
150°	764.2	782.1	800.1	804.5	835.9	877.7	898.7	927.4	984.9	1028.1	1034.5
152.5°	783.2	796.7	810.4	813.7	842.1	879.8	898.7	923.3	972.4	1009.2	1014.1
155°	811.2	821.3	831.4	833.9	855.5	884.3	898.7	918.2	957.3	986.6	989.8
157.5°	832.1	841.9	851.6	854.0	868.9	888.8	898.7	913.9	944.2	967.1	969.3
160°	846.1	853.7	861.3	863.2	875.1	890.8	898.7	911.7	937.7	957.3	958.6
162.5°	860.2	865.9	871.6	873.0	881.6	893.0	898.7	909.7	931.6	948.1	949.3
165°	875.5	880.6	885.7	887.0	890.9	896.1	898.7	906.6	922.3	934.1	935.3
167.5°	889.5	891.9	894.3	894.9	898.2	902.5	904.7	909.8	920.2	927.9	928.5
170°	898.7	901.1	903.5	904.1	904.3	904.6	904.7	909.8	920.2	927.9	927.9
172.5°	903.5	904.0	904.6	904.7	904.7	904.7	904.7	908.8	917.0	923.1	922.6
175°	910.2	910.2	910.2	910.2	908.4	905.9	904.7	907.3	912.5	916.4	916.4
177.5°	910.2	910.2	910.2	910.2	908.9	907.0	906.0	908.1	912.1	915.2	914.6
180°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2



TEST NUMBER: P936917

CATALOG NUMBER: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1560.0	1560.0
2.5°	1665.3	1655.2
5°	2141.8	2151.8
7.5°	2884.1	2879.0
10°	3586.2	3631.4
12.5°	4097.9	4107.9
15°	4408.9	4428.9
17.5°	4529.3	4534.2
20°	4534.2	4524.2
22.5°	4479.1	4469.0
25°	4413.9	4408.9
27.5°	4353.7	4358.8
30°	4328.6	4343.6
32.5°	4328.6	4353.7
35°	4338.6	4363.7
37.5°	4333.7	4363.7
40°	4313.6	4348.7
42.5°	4258.4	4283.5
45°	4173.1	4203.2
47.5°	4062.8	4082.8
50°	3922.4	3942.4
52.5°	3746.8	3751.8
55°	3536.2	3556.2
57.5°	3310.4	3315.4
60°	3059.6	3074.7
62.5°	2793.8	2793.8
65°	2512.9	2523.0
67.5°	2222.0	2247.1
70°	1926.1	1931.0
72.5°	1635.1	1635.1
75°	1334.2	1339.2
77.5°	1048.3	1048.3
80°	777.5	782.5
82.5°	536.7	546.8
85°	336.0	336.0
87.5°	155.5	140.4
90°	23.2	23.2
92.5°	93.0	74.5
95°	324.1	268.1
97.5°	776.6	670.2
100°	1118.9	992.1
102.5°	1455.6	1347.0
105°	1885.0	1826.6
107.5°	2166.2	2180.3
110°	2273.4	2334.2



TEST NUMBER: P936917

CATALOG NUMBER: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2283.1	2376.4
115°	2222.5	2352.0
117.5°	2094.1	2237.7
120°	1990.7	2130.2
122.5°	1889.9	2027.6
125°	1746.2	1873.1
127.5°	1617.0	1724.0
130°	1540.9	1639.7
132.5°	1471.7	1560.2
135°	1377.1	1453.3
137.5°	1301.1	1363.5
140°	1248.9	1307.3
142.5°	1205.9	1256.0
145°	1141.0	1179.1
147.5°	1091.3	1122.9
150°	1060.0	1085.6
152.5°	1033.3	1052.6
155°	1002.6	1015.4
157.5°	978.2	987.2
160°	963.8	968.9
162.5°	954.2	959.2
165°	940.6	945.7
167.5°	930.7	932.9
170°	927.9	927.9
172.5°	920.7	918.8
175°	916.4	916.4
177.5°	912.4	910.2
180°	910.2	910.2



TEST NUMBER: P936917
 CATALOG NUMBER: SQ4-FB-050U-125D-840-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.91	9.00	8.69	9.82	10.82	21.10	22.19	21.88	23.01	24.01
	3H	8.63	9.62	9.43	10.44	11.47	22.96	23.95	23.76	24.77	25.80
	4H	8.94	9.87	9.75	10.70	11.74	23.62	24.55	24.43	25.39	26.42
	6H	9.20	10.06	10.03	10.90	11.96	24.07	24.93	24.89	25.77	26.82
	8H	9.27	10.10	10.11	10.96	12.01	24.20	25.02	25.03	25.88	26.93
	12H	9.30	10.09	10.14	10.94	12.02	24.27	25.06	25.12	25.92	27.00
4H	2H	15.16	16.09	15.98	16.92	17.96	21.40	22.33	22.22	23.17	24.20
	3H	16.74	17.53	17.58	18.39	19.45	23.47	24.26	24.30	25.12	26.18
	4H	16.85	17.57	17.70	18.43	19.51	24.25	24.97	25.10	25.83	26.91
	6H	16.87	17.50	17.74	18.38	19.47	24.81	25.43	25.67	26.32	27.40
	8H	16.86	17.44	17.72	18.32	19.42	24.98	25.56	25.85	26.44	27.54
	12H	16.83	17.35	17.71	18.25	19.36	25.09	25.61	25.97	26.52	27.62
8H	4H	18.32	18.90	19.18	19.78	20.88	24.33	24.91	25.20	25.80	26.90
	6H	18.57	19.05	19.47	19.98	21.08	24.98	25.46	25.87	26.38	27.48
	8H	18.59	19.02	19.50	19.94	21.06	25.20	25.63	26.11	26.55	27.67
	12H	18.57	18.95	19.48	19.86	21.03	25.36	25.74	26.27	26.65	27.82
12H	4H	18.47	19.00	19.36	19.90	21.01	24.30	24.82	25.18	25.72	26.83
	6H	18.83	19.26	19.74	20.18	21.30	24.96	25.39	25.87	26.31	27.43
	8H	18.92	19.29	19.82	20.20	21.37	25.21	25.59	26.12	26.50	27.66