

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519761

Luminaire Tested: **SQ4-125U-0D-940-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519761
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6482.7 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 47.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519761
CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519761

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5053	54348	19231
100°	5210	47712	41414
105°	5563	33259	46696
110°	5775	23120	44494
115°	6014	16961	37069
120°	6105	13361	28909
125°	6049	11221	22319
130°	5974	9842	17394
135°	5909	8846	14054
140°	5875	8114	11668
145°	5898	7540	9836
150°	5978	7087	8568
155°	6051	6754	7666
160°	6112	6523	7059
165°	6158	6362	6647
170°	6200	6248	6400
175°	6208	6177	6248



TEST NUMBER: P519761

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	469.8	7.2
100°-110°	1265.4	19.5
110°-120°	1328.0	20.5
120°-130°	1077.7	16.6
130°-140°	845.2	13.0
140°-150°	648.9	10.0
150°-160°	466.6	7.2
160°-170°	285.0	4.4
170°-180°	96.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3063.3	47.3
90°-150°	5635.0	86.9
90°-180°	6483.0	100.0
0°-180°	6482.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	8	15	17	17	
95°	72	256	770	394	272	79
105°	234	364	1400	2094	1965	246
115°	413	506	1165	2252	2547	407
125°	564	648	1046	1769	2081	504
135°	679	758	1017	1427	1616	524
145°	786	847	1004	1220	1310	493
155°	892	924	995	1094	1130	410
165°	967	978	999	1039	1044	273
175°	1006	1004	1000	1014	1012	96
180°	1004	1004	1004	1004	1004	



TEST NUMBER: P519761

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.6	7.6	15.4	16.6	16.6
92.5°	31.2	110.3	218.0	104.9	72.9
95°	71.6	255.5	770.1	393.8	272.5
97.5°	114.4	292.5	1207.9	1009.1	760.9
100°	147.1	307.2	1347.0	1409.4	1169.2
102.5°	178.8	327.9	1393.1	1709.2	1512.1
105°	234.1	364.2	1399.5	2093.7	1964.9
107.5°	286.3	402.4	1339.9	2291.4	2324.6
110°	321.1	431.2	1285.6	2352.7	2474.1
112.5°	357.9	460.0	1233.4	2339.1	2538.5
115°	413.2	505.8	1165.4	2251.8	2547.0
117.5°	463.6	550.4	1112.7	2112.3	2441.0
120°	496.3	580.2	1086.1	2012.2	2350.0
122.5°	525.0	607.8	1066.6	1909.9	2246.6
125°	564.1	648.0	1046.4	1768.6	2081.3
127.5°	601.8	684.3	1033.6	1644.0	1923.2
130°	624.3	706.8	1028.5	1572.6	1817.8
132.5°	646.8	728.3	1023.4	1509.8	1734.9
135°	679.3	758.1	1017.0	1426.8	1615.7
137.5°	710.2	785.8	1013.7	1356.5	1511.6
140°	731.7	804.3	1010.6	1313.1	1453.2
142.5°	754.2	821.8	1008.6	1272.7	1390.8
145°	785.5	846.7	1004.2	1219.9	1309.9
147.5°	819.2	872.5	999.9	1175.4	1246.2
150°	841.7	888.0	997.8	1147.5	1206.3
152.5°	862.2	902.5	996.8	1124.8	1172.6
155°	891.6	924.2	995.2	1094.5	1129.6
157.5°	917.5	942.7	995.5	1073.3	1096.8
160°	933.8	955.1	996.5	1060.9	1078.4
162.5°	948.2	965.4	997.6	1050.5	1063.0
165°	967.1	978.4	999.1	1038.9	1043.9
167.5°	982.5	989.0	1000.4	1029.8	1031.8
170°	992.7	995.2	1000.4	1024.7	1024.7
172.5°	998.8	999.3	1001.4	1019.6	1019.6
175°	1005.5	1004.2	1000.4	1014.4	1011.9
177.5°	1008.3	1006.3	1001.1	1009.3	1007.3
180°	1004.2	1004.2	1004.2	1004.2	1004.2

(END OF REPORT)