

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563257

Luminaire Tested: **SQ4-PP3-025U-125D-840-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563257  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-025U-125D-840-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 17691.4 lumens  
Efficiency: N/A  
Efficacy: 113.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 156.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563257  
CATALOG NUMBER: SQ4-PP3-025U-125D-840-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563257

CATALOG NUMBER: SQ4-PP3-025U-125D-840-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	83
1	106	101	97	94	101	97	94	91	90	87	85	84	81	79	77	76	74	71
2	96	89	82	77	92	86	80	75	79	75	71	74	70	67	68	66	63	60
3	88	78	71	65	84	76	69	63	70	65	60	65	61	57	61	57	54	51
4	81	70	61	55	77	67	60	54	63	56	51	58	53	49	55	50	47	44
5	74	62	54	48	71	60	52	47	56	50	45	53	47	43	49	45	41	38
6	69	56	48	42	66	54	46	41	51	44	39	48	42	37	45	40	36	34
7	64	51	43	37	61	49	42	36	46	40	35	44	38	33	41	36	32	30
8	59	46	38	33	57	45	37	32	42	36	31	40	34	30	38	33	29	27
9	55	43	35	29	53	41	34	29	39	32	28	37	31	27	35	30	26	24
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	32	27	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17738	17738	17738
5°	17868	17759	17696
10°	17838	17712	17633
15°	17720	17623	17527
20°	17602	17503	17371
25°	17393	17273	17101
30°	17071	16981	16766
35°	16625	16511	16302
40°	16093	15992	15809
45°	15653	15543	15389
50°	15092	14995	14850
55°	14311	14121	14013
60°	13027	12654	12592
65°	11477	10998	10962
70°	9909	9500	9500
75°	8529	8409	8289
80°	7520	7610	7431
85°	5886	6422	6422



TEST NUMBER: P563257

CATALOG NUMBER: SQ4-PP3-025U-125D-840-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	545.4	3.1
10°-20°	1557.3	8.8
20°-30°	2332.6	13.2
30°-40°	2736.0	15.5
40°-50°	2744.5	15.5
50°-60°	2341.3	13.2
60°-70°	1526.9	8.6
70°-80°	766.1	4.3
80°-90°	214.4	1.2
90°-100°	220.1	1.2
100°-110°	578.6	3.3
110°-120°	600.0	3.4
120°-130°	481.3	2.7
130°-140°	377.6	2.1
140°-150°	289.8	1.6
150°-160°	208.7	1.2
160°-170°	127.7	0.7
170°-180°	43.1	0.2
0°-30°	4435.2	25.1
0°-40°	7171.2	40.5
0°-60°	12257.0	69.3
0°-90°	14764.4	83.5
90°-120°	1398.7	7.9
90°-150°	2547.3	14.4
90°-180°	2927.0	16.5
0°-180°	17691.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	5768	5768	5768	5768	5768	
5°	5788	5734	5752	5732	5732	550
15°	5566	5511	5535	5515	5505	1570
25°	5126	5066	5090	5045	5040	2357
35°	4428	4384	4398	4347	4342	2766
45°	3599	3574	3574	3538	3538	2771
55°	2669	2659	2634	2618	2613	2372
65°	1577	1548	1511	1501	1506	1574
75°	718	718	708	702	698	779
85°	167	182	182	182	182	196
90°	3	9	23	12	12	9
95°	29	114	379	195	133	32
105°	104	158	640	971	906	110
115°	185	225	512	1022	1167	183
125°	258	289	466	788	929	229
135°	307	338	452	636	721	237
145°	356	379	446	542	585	223
155°	402	414	446	490	504	185
165°	434	440	446	463	469	123
175°	452	452	449	454	454	43
180°	452	452	452	452	452	



TEST NUMBER: P563257

CATALOG NUMBER: SQ4-PP3-025U-125D-840-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	5767.7	5767.7	5767.7	5767.7	5767.7
2.5°	5804.0	5756.6	5767.7	5759.0	5735.3
5°	5787.9	5733.5	5752.5	5732.3	5732.3
7.5°	5748.4	5689.1	5708.0	5687.8	5686.8
10°	5712.0	5652.7	5671.6	5651.3	5646.3
12.5°	5659.5	5600.2	5623.1	5598.8	5597.8
15°	5565.5	5511.1	5535.1	5514.7	5504.8
17.5°	5459.3	5400.0	5429.0	5400.6	5396.6
20°	5378.4	5319.1	5348.1	5307.7	5307.7
22.5°	5281.4	5222.1	5255.1	5202.5	5202.5
25°	5125.7	5066.4	5090.3	5044.7	5039.7
27.5°	4940.7	4882.3	4907.3	4855.7	4854.7
30°	4807.2	4752.8	4781.9	4726.2	4721.3
32.5°	4661.6	4611.2	4632.3	4576.6	4571.7
35°	4428.1	4383.6	4397.8	4347.1	4342.2
37.5°	4182.4	4137.0	4153.1	4109.6	4107.6
40°	4008.5	3978.9	3983.3	3947.7	3937.8
42.5°	3846.8	3813.2	3817.5	3782.0	3780.1
45°	3599.1	3574.4	3573.8	3538.4	3538.4
47.5°	3336.2	3317.5	3312.0	3282.6	3281.6
50°	3154.3	3139.4	3134.0	3108.7	3103.7
52.5°	2964.2	2957.3	2939.9	2918.7	2917.7
55°	2669.0	2659.1	2633.6	2618.3	2613.4
57.5°	2348.5	2328.7	2300.0	2277.8	2281.8
60°	2118.0	2098.2	2057.3	2047.2	2047.2
62.5°	1895.6	1871.9	1830.9	1816.9	1824.8
65°	1577.1	1547.5	1511.4	1501.4	1506.4
67.5°	1288.0	1261.3	1222.3	1222.2	1218.2
70°	1102.0	1087.1	1056.5	1056.5	1056.5
72.5°	936.2	929.2	906.9	906.8	902.8
75°	717.8	717.8	707.7	702.5	697.6
77.5°	537.8	539.8	534.8	529.6	520.7
80°	424.6	434.5	429.7	424.5	419.6
82.5°	319.5	329.4	328.6	319.4	318.5
85°	166.8	181.6	182.0	182.0	182.0
87.5°	45.1	62.0	69.3	67.1	71.1
90°	2.9	8.6	23.2	11.6	11.6
92.5°	12.2	58.6	129.7	57.4	37.1
95°	28.9	113.9	379.2	195.4	133.2
97.5°	50.4	125.1	567.4	451.2	332.3
100°	66.6	134.5	625.3	633.6	492.1
102.5°	80.5	143.9	641.5	789.2	668.1
105°	104.2	158.0	639.7	971.1	906.0
107.5°	128.5	178.3	603.3	1065.6	1081.5
110°	144.7	190.0	573.2	1090.0	1157.9

TEST NUMBER: P563257

CATALOG NUMBER: SQ4-PP3-025U-125D-840-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	160.9	204.0	545.4	1074.6	1178.7
115°	185.3	224.9	512.4	1022.2	1166.6
117.5°	209.0	245.2	489.8	949.6	1109.8
120°	222.9	256.9	480.5	900.9	1056.6
122.5°	236.8	270.8	473.6	852.2	1005.6
125°	257.6	288.8	466.0	787.7	929.2
127.5°	274.4	306.1	459.7	735.7	855.1
130°	283.7	317.6	457.4	703.0	813.4
132.5°	292.9	326.9	455.0	675.0	774.0
135°	306.8	338.0	451.6	635.9	720.8
137.5°	321.3	351.9	451.0	606.6	676.2
140°	332.9	361.2	448.7	583.3	648.4
142.5°	342.2	368.2	448.7	566.9	622.9
145°	356.0	378.7	445.8	542.3	584.7
147.5°	369.9	392.0	445.8	521.8	556.9
150°	379.2	399.0	445.8	510.1	538.4
152.5°	388.5	403.8	445.8	500.7	522.2
155°	402.4	413.7	445.8	489.5	503.7
157.5°	412.8	423.5	445.8	479.6	489.8
160°	419.7	428.2	445.8	474.9	480.5
162.5°	426.7	432.9	445.8	470.2	475.9
165°	434.2	439.9	445.8	463.3	468.9
167.5°	441.2	444.0	448.7	460.3	462.6
170°	445.8	448.6	448.7	460.3	460.3
172.5°	448.1	448.7	448.7	457.9	455.6
175°	451.6	451.6	448.7	454.5	454.5
177.5°	451.6	451.6	449.3	453.8	451.6
180°	451.6	451.6	451.6	451.6	451.6

(END OF REPORT)