

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518465

Luminaire Tested: **SQ4-BB-050U-100D-940-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P518465  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2009-966-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-BB-050U-100D-940-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5752.2 lumens  
Efficiency: N/A  
Efficacy: 78.4 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 73.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P518465  
CATALOG NUMBER: SQ4-BB-050U-100D-940-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P518465

CATALOG NUMBER: SQ4-BB-050U-100D-940-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	101	97	94	91	94	91	88	86	78	77	75	67	66	65	57	56	55	50
2	94	87	82	78	87	82	77	74	71	68	65	61	59	57	52	51	50	45
3	87	79	72	67	81	74	68	64	65	61	57	56	53	51	48	46	45	41
4	80	71	64	59	75	67	61	56	59	54	51	52	48	46	45	42	40	37
5	75	65	57	52	70	61	55	50	54	49	45	47	44	41	41	39	37	34
6	70	59	52	46	65	56	49	45	49	44	41	44	40	37	38	36	33	31
7	65	54	47	42	61	51	45	40	46	41	37	40	37	34	36	33	31	28
8	61	50	43	38	57	47	41	36	42	37	34	38	34	31	33	30	28	26
9	57	46	39	34	53	44	37	33	39	34	31	35	31	28	31	28	26	24
10	54	42	36	31	50	40	34	30	36	32	28	33	29	26	29	26	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16333	16333	16333
5°	16070	16031	16149
10°	15036	15237	15662
15°	13670	14103	14889
20°	12134	12765	13883
25°	10567	11404	12756
30°	9051	10046	11688
35°	7505	8528	10399
40°	5766	6818	8860
45°	4168	5163	7129
50°	2840	3848	5655
55°	1846	2783	4395
60°	1059	1960	3176
65°	281	1196	1608
70°	138	370	462
75°	62	31	0
80°	46	0	0
85°	0	0	0



TEST NUMBER: P518465

CATALOG NUMBER: SQ4-BB-050U-100D-940-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	242.3	4.2
10°-20°	619.7	10.8
20°-30°	775.8	13.5
30°-40°	716.6	12.5
40°-50°	481.5	8.4
50°-60°	248.7	4.3
60°-70°	77.9	1.4
70°-80°	4.9	0.1
80°-90°	1.6	0.0
90°-100°	189.9	3.3
100°-110°	515.9	9.0
110°-120°	530.4	9.2
120°-130°	424.1	7.4
130°-140°	333.2	5.8
140°-150°	255.5	4.4
150°-160°	183.7	3.2
160°-170°	112.4	2.0
170°-180°	37.9	0.7
0°-30°	1637.9	28.5
0°-40°	2354.6	40.9
0°-60°	3084.8	53.6
0°-90°	3169.3	55.1
90°-120°	1236.2	21.5
90°-150°	2249.0	39.1
90°-180°	2583.0	44.9
0°-180°	5752.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2655	2655	2655	2655	2655	
5°	2603	2576	2596	2606	2616	241
15°	2147	2139	2215	2289	2338	598
25°	1557	1570	1680	1795	1880	714
35°	1000	1025	1136	1269	1385	619
45°	479	508	594	709	820	376
55°	172	201	260	333	410	161
65°	19	37	82	99	110	33
75°	3	3	1	0	0	4
85°	0	0	0	0	0	0
90°	1	5	9	11	11	2
95°	28	104	331	144	97	30
105°	92	143	567	864	813	97
115°	163	198	454	903	1029	161
125°	224	255	411	692	817	200
135°	270	300	399	564	636	209
145°	312	334	394	479	515	196
155°	352	365	392	430	443	162
165°	382	387	393	410	411	108
175°	396	397	394	399	398	38
180°	396	396	396	396	396	



TEST NUMBER: P518465

CATALOG NUMBER: SQ4-BB-050U-100D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2655.4	2655.4	2655.4	2655.4	2655.4
2.5°	2661.6	2636.5	2643.1	2643.0	2635.9
5°	2602.8	2576.4	2596.4	2605.6	2615.6
7.5°	2492.8	2472.2	2510.5	2539.3	2560.1
10°	2407.5	2389.9	2439.6	2478.8	2507.7
12.5°	2308.8	2295.3	2355.3	2409.1	2446.0
15°	2146.7	2139.2	2214.8	2289.1	2338.1
17.5°	1973.0	1972.8	2059.1	2151.4	2210.4
20°	1853.8	1857.6	1950.2	2051.9	2121.0
22.5°	1734.6	1743.4	1842.2	1948.4	2027.5
25°	1557.0	1569.6	1680.4	1795.3	1879.5
27.5°	1386.4	1404.8	1521.3	1640.8	1743.3
30°	1274.4	1295.8	1414.4	1540.2	1645.7
32.5°	1164.4	1189.8	1305.5	1438.5	1546.0
35°	999.5	1024.6	1135.7	1269.3	1384.9
37.5°	829.1	853.8	962.2	1093.8	1218.7
40°	718.1	745.8	849.2	976.7	1103.5
42.5°	617.4	645.1	742.3	867.6	987.4
45°	479.2	508.1	593.5	709.1	819.6
47.5°	364.6	396.0	471.0	575.5	676.3
50°	296.8	328.2	402.1	494.2	591.0
52.5°	242.3	272.7	339.4	426.2	514.9
55°	172.1	201.0	259.5	333.2	409.8
57.5°	119.0	143.8	196.3	257.8	317.8
60°	86.1	109.9	159.3	209.2	258.2
62.5°	57.3	79.2	127.4	165.7	198.6
65°	19.3	36.9	82.2	99.2	110.5
67.5°	9.8	11.8	43.2	45.6	49.3
70°	7.7	7.7	20.6	21.9	25.7
72.5°	5.7	5.7	8.2	10.6	11.3
75°	2.6	2.6	1.3	0.0	0.0
77.5°	1.3	1.3	1.0	0.0	0.0
80°	1.3	1.3	0.0	0.0	0.0
82.5°	0.3	0.3	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.3	1.0	1.8	2.3	2.3
90°	1.3	5.0	8.9	11.4	11.4
92.5°	11.4	52.0	90.3	38.8	32.8
95°	28.0	103.9	330.7	143.9	96.7
97.5°	46.3	114.7	507.0	394.5	277.0
100°	58.5	121.9	561.0	568.6	459.2
102.5°	70.7	129.2	575.2	703.3	606.8
105°	91.6	142.6	567.3	863.8	812.8
107.5°	113.2	158.2	534.5	946.7	960.9
110°	128.5	169.5	510.1	963.0	1024.0

TEST NUMBER: P518465

CATALOG NUMBER: SQ4-BB-050U-100D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	180.8	485.7	949.5	1041.3
115°	162.8	197.6	454.1	903.4	1029.1
117.5°	182.7	216.0	434.0	838.2	979.7
120°	195.9	228.2	424.9	794.4	934.9
122.5°	207.1	239.4	418.7	750.5	886.1
125°	223.9	255.0	410.9	692.3	816.6
127.5°	238.9	269.7	406.5	648.1	754.8
130°	248.0	277.9	404.5	620.4	716.1
132.5°	257.2	287.1	402.5	596.7	681.5
135°	269.7	299.5	399.4	563.9	636.0
137.5°	283.2	310.3	397.9	534.9	595.6
140°	291.3	317.4	396.9	516.4	571.1
142.5°	299.4	323.6	395.9	502.0	547.7
145°	311.6	334.0	394.3	479.1	515.2
147.5°	325.4	344.5	393.1	461.1	489.5
150°	334.5	350.7	393.1	450.8	473.2
152.5°	341.7	355.8	392.0	441.6	460.0
155°	352.3	364.8	391.8	430.2	442.7
157.5°	362.8	372.5	391.8	422.5	432.0
160°	368.9	377.6	391.8	417.4	424.9
162.5°	375.0	381.7	392.8	413.3	418.7
165°	381.6	386.6	393.1	409.6	410.9
167.5°	388.5	391.0	394.3	405.3	406.3
170°	390.5	393.0	394.3	403.2	403.2
172.5°	392.5	394.0	394.3	401.2	401.2
175°	395.6	396.8	394.3	399.4	398.1
177.5°	396.6	396.6	393.6	397.6	395.6
180°	395.6	395.6	395.6	395.6	395.6

(END OF REPORT)