

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563401

Luminaire Tested: **SQ4-PP3-075U-075D-840-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563401  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 17781.3 lumens  
Efficiency: N/A  
Efficacy: 133.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 133.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563401  
CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563401

CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10461	10461	10461
5°	10538	10473	10437
10°	10520	10446	10399
15°	10450	10393	10336
20°	10381	10323	10244
25°	10258	10187	10086
30°	10068	10015	9888
35°	9805	9737	9614
40°	9491	9431	9323
45°	9232	9167	9076
50°	8901	8843	8758
55°	8440	8328	8264
60°	7683	7463	7426
65°	6768	6487	6465
70°	5844	5603	5603
75°	5030	4960	4888
80°	4435	4488	4382
85°	3472	3786	3786



TEST NUMBER: P563401

CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	321.6	1.8
10°-20°	918.4	5.2
20°-30°	1375.6	7.7
30°-40°	1613.6	9.1
40°-50°	1618.6	9.1
50°-60°	1380.8	7.8
60°-70°	900.5	5.1
70°-80°	451.8	2.5
80°-90°	128.6	0.7
90°-100°	656.8	3.7
100°-110°	1807.0	10.2
110°-120°	1865.1	10.5
120°-130°	1494.3	8.4
130°-140°	1173.7	6.6
140°-150°	899.4	5.1
150°-160°	646.7	3.6
160°-170°	395.4	2.2
170°-180°	133.3	0.7
0°-30°	2615.7	14.7
0°-40°	4229.3	23.8
0°-60°	7228.7	40.7
0°-90°	8709.6	49.0
90°-120°	4328.8	24.3
90°-150°	7896.3	44.4
90°-180°	9072.0	51.0
0°-180°	17781.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3402	3402	3402	3402	3402	
5°	3414	3381	3393	3381	3381	324
15°	3282	3250	3264	3252	3246	926
25°	3023	2988	3002	2975	2972	1390
35°	2612	2585	2594	2564	2561	1631
45°	2123	2108	2108	2087	2087	1634
55°	1574	1568	1553	1544	1541	1399
65°	930	913	891	886	888	928
75°	423	423	417	414	411	459
85°	98	107	107	107	107	116
90°	3	12	21	27	27	10
95°	98	358	1161	497	317	103
105°	323	497	1991	3032	2830	340
115°	572	696	1597	3180	3609	564
125°	788	898	1449	2451	2871	703
135°	951	1055	1407	1982	2243	734
145°	1099	1174	1387	1689	1819	689
155°	1244	1285	1378	1518	1561	572
165°	1345	1362	1384	1440	1449	379
175°	1392	1395	1387	1404	1401	132
180°	1392	1392	1392	1392	1392	

TEST NUMBER: P563401

CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3401.5	3401.5	3401.5	3401.5	3401.5
2.5°	3423.0	3395.0	3401.5	3396.4	3382.5
5°	3413.5	3381.4	3392.6	3380.7	3380.7
7.5°	3390.2	3355.2	3366.4	3354.4	3353.8
10°	3368.7	3333.8	3344.9	3332.9	3330.0
12.5°	3337.7	3302.8	3316.3	3301.9	3301.4
15°	3282.3	3250.2	3264.4	3252.3	3246.5
17.5°	3219.7	3184.7	3201.8	3185.0	3182.7
20°	3172.0	3137.0	3154.1	3130.2	3130.2
22.5°	3114.7	3079.8	3099.2	3068.2	3068.2
25°	3022.9	2987.9	3002.1	2975.2	2972.2
27.5°	2913.8	2879.4	2894.1	2863.7	2863.1
30°	2835.1	2803.0	2820.2	2787.3	2784.4
32.5°	2749.3	2719.5	2732.0	2699.1	2696.2
35°	2611.5	2585.3	2593.6	2563.8	2560.8
37.5°	2466.6	2439.8	2449.3	2423.7	2422.5
40°	2364.1	2346.6	2349.2	2328.2	2322.3
42.5°	2268.7	2248.9	2251.4	2230.5	2229.3
45°	2122.6	2108.0	2107.7	2086.8	2086.8
47.5°	1967.6	1956.5	1953.3	1936.0	1935.4
50°	1860.3	1851.5	1848.3	1833.4	1830.4
52.5°	1748.2	1744.1	1733.9	1721.3	1720.7
55°	1574.1	1568.2	1553.2	1544.2	1541.3
57.5°	1385.1	1373.4	1356.4	1343.4	1345.7
60°	1249.1	1237.5	1213.3	1207.4	1207.4
62.5°	1117.9	1104.0	1079.8	1071.5	1076.2
65°	930.1	912.6	891.4	885.5	888.4
67.5°	759.6	743.9	720.9	720.8	718.5
70°	649.9	641.2	623.1	623.1	623.1
72.5°	552.1	548.0	534.8	534.8	532.4
75°	423.3	423.3	417.4	414.3	411.4
77.5°	317.2	318.4	315.4	312.3	307.1
80°	250.4	256.2	253.4	250.4	247.4
82.5°	188.4	194.2	193.8	188.4	187.8
85°	98.4	107.1	107.3	107.3	107.3
87.5°	26.8	37.9	42.3	43.5	45.9
90°	3.0	11.7	20.7	26.7	26.7
92.5°	40.9	174.7	302.8	116.3	95.4
95°	97.8	358.5	1161.4	496.6	317.0
97.5°	159.4	397.5	1772.4	1365.6	963.5
100°	204.4	421.7	1964.3	1982.7	1617.7
102.5°	247.1	450.5	2014.1	2459.8	2124.9
105°	322.9	496.8	1991.0	3032.3	2829.5
107.5°	395.2	554.0	1877.8	3312.6	3372.9
110°	447.4	592.2	1792.5	3382.3	3590.9

TEST NUMBER: P563401

CATALOG NUMBER: SQ4-PP3-075U-075D-840-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	494.8	635.0	1707.2	3337.4	3654.9
115°	571.8	696.4	1597.0	3180.0	3608.7
117.5°	645.3	760.0	1527.0	2959.0	3444.0
120°	690.3	800.4	1496.2	2793.5	3294.6
122.5°	730.6	840.7	1474.9	2648.3	3124.0
125°	788.1	898.2	1448.8	2450.9	2871.0
127.5°	842.6	947.5	1431.6	2286.2	2654.7
130°	871.1	978.3	1422.2	2188.3	2524.3
132.5°	904.3	1011.4	1415.0	2102.2	2405.8
135°	951.1	1055.4	1407.3	1982.1	2242.8
137.5°	994.9	1091.7	1400.8	1885.1	2100.0
140°	1028.1	1117.9	1398.4	1820.6	2014.7
142.5°	1056.5	1139.4	1393.7	1763.1	1929.4
145°	1099.2	1174.5	1386.6	1688.8	1819.2
147.5°	1144.8	1209.7	1383.0	1623.0	1727.3
150°	1173.3	1231.2	1380.7	1586.9	1668.1
152.5°	1199.3	1252.7	1378.3	1555.8	1623.0
155°	1244.4	1284.9	1377.7	1517.9	1561.4
157.5°	1277.0	1310.0	1377.7	1486.8	1517.0
160°	1300.7	1326.7	1377.7	1470.1	1493.3
162.5°	1319.6	1341.1	1380.1	1455.8	1474.3
165°	1345.1	1362.5	1383.6	1440.1	1448.8
167.5°	1362.9	1376.2	1386.6	1426.9	1429.3
170°	1374.7	1383.4	1386.6	1422.2	1422.2
172.5°	1384.2	1388.3	1386.6	1415.0	1412.7
175°	1392.5	1395.4	1386.6	1404.3	1401.4
177.5°	1394.9	1394.9	1385.4	1399.5	1394.9
180°	1392.5	1392.5	1392.5	1392.5	1392.5

(END OF REPORT)