

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563785

Luminaire Tested: **SQ4-PP3-150U-075D-840-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563785
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-075D-840-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26965.7 lumens
Efficiency: N/A
Efficacy: 138.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 194.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563785
CATALOG NUMBER: SQ4-PP3-150U-075D-840-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563785

CATALOG NUMBER: SQ4-PP3-150U-075D-840-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10461	10461	10461
5°	10538	10473	10437
10°	10520	10446	10399
15°	10450	10393	10336
20°	10381	10323	10244
25°	10258	10187	10086
30°	10068	10015	9888
35°	9805	9737	9614
40°	9491	9431	9323
45°	9232	9167	9076
50°	8901	8843	8758
55°	8440	8328	8264
60°	7683	7463	7426
65°	6768	6487	6465
70°	5844	5603	5603
75°	5030	4960	4888
80°	4435	4488	4382
85°	3472	3786	3786



TEST NUMBER: P563785

CATALOG NUMBER: SQ4-PP3-150U-075D-840-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	321.6	1.2
10°-20°	918.4	3.4
20°-30°	1375.6	5.1
30°-40°	1613.6	6.0
40°-50°	1618.6	6.0
50°-60°	1380.8	5.1
60°-70°	900.5	3.3
70°-80°	451.8	1.7
80°-90°	130.9	0.5
90°-100°	1315.8	4.9
100°-110°	3557.5	13.2
110°-120°	3740.2	13.9
120°-130°	3038.1	11.3
130°-140°	2383.1	8.8
140°-150°	1829.1	6.8
150°-160°	1315.4	4.9
160°-170°	803.6	3.0
170°-180°	270.9	1.0
0°-30°	2615.7	9.7
0°-40°	4229.3	15.7
0°-60°	7228.7	26.8
0°-90°	8712.0	32.3
90°-120°	8613.5	31.9
90°-150°	15863.8	58.8
90°-180°	18254.0	67.7
0°-180°	26965.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3402	3402	3402	3402	3402	
5°	3414	3381	3393	3381	3381	324
15°	3282	3250	3264	3252	3246	926
25°	3023	2988	3002	2975	2972	1390
35°	2612	2585	2594	2564	2561	1631
45°	2123	2108	2108	2087	2087	1634
55°	1574	1568	1553	1544	1541	1399
65°	930	913	891	886	888	928
75°	423	423	417	414	411	459
85°	98	107	107	107	107	116
90°	6	18	40	43	40	17
95°	204	717	2188	1132	674	214
105°	661	1022	3947	5822	5583	696
115°	1164	1423	3273	6336	7153	1150
125°	1594	1826	2950	4978	5848	1421
135°	1911	2137	2871	4020	4550	1477
145°	2222	2388	2831	3441	3703	1390
155°	2508	2606	2807	3086	3188	1157
165°	2731	2757	2819	2929	2944	769
175°	2834	2831	2822	2858	2852	269
180°	2831	2831	2831	2831	2831	

TEST NUMBER: P563785

CATALOG NUMBER: SQ4-PP3-150U-075D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3401.5	3401.5	3401.5	3401.5	3401.5
2.5°	3423.0	3395.0	3401.5	3396.4	3382.5
5°	3413.5	3381.4	3392.6	3380.7	3380.7
7.5°	3390.2	3355.2	3366.4	3354.4	3353.8
10°	3368.7	3333.8	3344.9	3332.9	3330.0
12.5°	3337.7	3302.8	3316.3	3301.9	3301.4
15°	3282.3	3250.2	3264.4	3252.3	3246.5
17.5°	3219.7	3184.7	3201.8	3185.0	3182.7
20°	3172.0	3137.0	3154.1	3130.2	3130.2
22.5°	3114.7	3079.8	3099.2	3068.2	3068.2
25°	3022.9	2987.9	3002.1	2975.2	2972.2
27.5°	2913.8	2879.4	2894.1	2863.7	2863.1
30°	2835.1	2803.0	2820.2	2787.3	2784.4
32.5°	2749.3	2719.5	2732.0	2699.1	2696.2
35°	2611.5	2585.3	2593.6	2563.8	2560.8
37.5°	2466.6	2439.8	2449.3	2423.7	2422.5
40°	2364.1	2346.6	2349.2	2328.2	2322.3
42.5°	2268.7	2248.9	2251.4	2230.5	2229.3
45°	2122.6	2108.0	2107.7	2086.8	2086.8
47.5°	1967.6	1956.5	1953.3	1936.0	1935.4
50°	1860.3	1851.5	1848.3	1833.4	1830.4
52.5°	1748.2	1744.1	1733.9	1721.3	1720.7
55°	1574.1	1568.2	1553.2	1544.2	1541.3
57.5°	1385.1	1373.4	1356.4	1343.4	1345.7
60°	1249.1	1237.5	1213.3	1207.4	1207.4
62.5°	1117.9	1104.0	1079.8	1071.5	1076.2
65°	930.1	912.6	891.4	885.5	888.4
67.5°	759.6	743.9	720.9	720.8	718.5
70°	649.9	641.2	623.1	623.1	623.1
72.5°	552.1	548.0	534.8	534.8	532.4
75°	423.3	423.3	417.4	414.3	411.4
77.5°	317.2	318.4	315.4	312.3	307.1
80°	250.4	256.2	253.4	250.4	247.4
82.5°	188.4	194.2	193.8	188.4	187.8
85°	98.4	107.1	107.3	107.3	107.3
87.5°	27.5	39.2	46.1	46.7	48.5
90°	6.1	18.0	39.6	42.6	39.6
92.5°	86.6	315.4	622.3	270.1	195.7
95°	204.2	716.7	2188.2	1132.4	673.5
97.5°	327.9	822.0	3410.8	2822.7	2073.0
100°	420.6	864.6	3791.2	3953.8	3196.9
102.5°	505.9	923.7	3925.3	4811.4	4245.3
105°	661.3	1021.9	3946.6	5821.5	5583.1
107.5°	805.2	1134.1	3774.1	6451.7	6530.9
110°	917.3	1215.3	3620.5	6620.9	6957.6

TEST NUMBER: P563785

CATALOG NUMBER: SQ4-PP3-150U-075D-840-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1017.3	1296.2	3479.1	6587.1	7152.6
115°	1164.2	1423.4	3273.1	6336.2	7152.6
117.5°	1308.0	1551.2	3137.2	5952.8	6878.3
120°	1395.8	1634.2	3056.7	5677.7	6622.4
122.5°	1478.7	1712.3	3007.9	5382.9	6334.7
125°	1593.9	1826.3	2950.0	4978.2	5848.3
127.5°	1699.9	1928.2	2915.9	4647.9	5413.1
130°	1758.4	1993.9	2901.3	4443.8	5135.1
132.5°	1819.4	2052.4	2886.7	4259.7	4896.2
135°	1910.8	2137.3	2870.8	4019.6	4550.0
137.5°	2002.9	2216.8	2857.4	3824.8	4256.8
140°	2066.2	2265.9	2852.5	3699.3	4083.7
142.5°	2127.2	2314.9	2842.8	3586.1	3922.8
145°	2221.7	2388.5	2831.2	3440.6	3702.8
147.5°	2307.6	2455.4	2817.8	3308.7	3510.2
150°	2371.0	2502.1	2812.9	3237.1	3398.0
152.5°	2429.5	2543.9	2810.5	3170.6	3302.9
155°	2508.1	2606.5	2806.8	3086.4	3187.8
157.5°	2589.8	2658.4	2807.4	3027.7	3094.5
160°	2636.1	2692.8	2809.9	2990.7	3038.4
162.5°	2672.7	2719.8	2812.3	2961.2	2997.0
165°	2730.6	2757.4	2819.0	2929.0	2943.9
167.5°	2770.2	2788.7	2819.6	2901.4	2908.6
170°	2794.6	2803.6	2822.0	2889.1	2889.1
172.5°	2814.1	2815.9	2822.0	2874.4	2872.0
175°	2834.2	2831.3	2822.0	2858.5	2852.5
177.5°	2840.9	2833.8	2821.4	2845.7	2838.5
180°	2831.2	2831.2	2831.2	2831.2	2831.2

(END OF REPORT)