

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937875

Luminaire Tested: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937875
REPORT IS A COMBINATION OF REPORTS P933605 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8814.2 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 71.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937875
CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P937875
 CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20		
RC	80	70	50	30	10	0													
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		
RCR	0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
	1	92	88	84	80	81	78	75	72	60	58	56	44	42	41	28	28	27	20
	2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	23	22	16
	3	76	66	59	54	67	59	53	48	46	42	38	33	30	28	21	20	19	13
	4	69	58	51	45	61	52	46	41	40	36	32	29	26	24	19	17	16	11
	5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13	10
	6	58	46	38	33	51	41	34	29	32	27	23	23	20	17	15	13	12	8
	7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10	7
	8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9	6
	9	46	34	27	22	40	30	24	20	24	19	16	17	14	12	11	9	8	6
	10	42	31	24	19	38	28	21	17	22	17	14	16	13	10	10	9	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1719	1719	1719
5°	1679	1986	2310
10°	1522	2894	3829
15°	1292	3780	4624
20°	1052	4379	4713
25°	878	4581	4617
30°	739	4609	4608
35°	654	4531	4727
40°	569	4431	4850
45°	515	4356	4869
50°	472	4290	4789
55°	452	4192	4577
60°	463	4007	4241
65°	479	3724	3780
70°	510	3246	3194
75°	563	2643	2493
80°	609	1831	1679
85°	537	970	860

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4869 cd/sqm



TEST NUMBER: P937875

CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	0.4
10°-20°	159.3	1.8
20°-30°	278.6	3.2
30°-40°	358.6	4.1
40°-50°	400.5	4.5
50°-60°	383.6	4.4
60°-70°	304.0	3.4
70°-80°	178.8	2.0
80°-90°	53.6	0.6
90°-100°	500.9	5.7
100°-110°	1316.9	14.9
110°-120°	1365.4	15.5
120°-130°	1095.3	12.4
130°-140°	859.4	9.7
140°-150°	659.6	7.5
150°-160°	475.0	5.4
160°-170°	290.7	3.3
170°-180°	98.2	1.1
0°-30°	473.8	5.4
0°-40°	832.4	9.4
0°-60°	1616.5	18.3
0°-90°	2152.9	24.4
90°-120°	3183.2	36.1
90°-150°	5797.5	65.8
90°-180°	6661.0	75.6
0°-180°	8814.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	278	278	278	278	278	
5°	271	290	327	370	383	25
15°	203	374	631	765	789	56
25°	130	424	751	784	785	60
35°	88	406	707	748	777	55
45°	60	323	625	716	748	46
55°	43	205	531	616	633	39
65°	34	109	394	443	449	34
75°	25	67	216	238	238	26
85°	9	20	54	59	60	9
90°	7	19	52	26	26	6
95°	66	259	863	445	303	74
105°	237	359	1456	2210	2062	252
115°	421	512	1166	2326	2655	416
125°	586	657	1061	1792	2114	520
135°	699	769	1028	1447	1641	541
145°	810	862	1014	1234	1331	508
155°	916	941	1014	1114	1146	421
165°	988	1001	1014	1054	1068	279
175°	1028	1028	1021	1034	1034	98
180°	1028	1028	1028	1028	1028	



TEST NUMBER: P937875
 CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	277.8	277.8	277.8	277.8	277.8	277.8	277.8	277.8	277.8	277.8	277.8
2.5°	277.8	277.8	279.5	280.4	282.3	283.2	285.0	286.7	292.1	293.0	294.7
5°	270.7	274.2	285.8	290.3	302.8	319.8	326.9	338.5	362.7	369.8	374.3
7.5°	259.9	268.0	296.5	303.7	335.0	379.6	398.4	423.4	461.8	480.6	495.8
10°	243.0	259.9	310.8	327.8	378.7	446.6	481.5	516.3	574.4	600.2	610.1
12.5°	224.2	251.9	326.0	349.3	422.5	521.6	563.6	602.1	668.1	702.9	708.3
15°	202.7	240.3	340.3	374.3	469.0	584.1	630.6	678.0	739.6	764.6	770.9
17.5°	184.0	231.3	353.7	389.5	504.7	640.4	687.8	727.1	777.1	794.0	798.5
20°	160.8	217.0	362.7	409.1	542.2	681.5	727.1	757.5	791.4	802.1	803.9
22.5°	143.8	201.8	368.0	416.2	567.2	706.5	744.9	769.0	792.3	795.8	796.7
25°	129.6	184.9	367.1	424.3	588.7	721.7	751.2	769.0	782.4	784.2	784.2
27.5°	116.2	166.1	363.5	426.1	604.7	725.3	748.5	761.0	767.2	770.9	770.9
30°	104.5	148.3	354.6	422.5	611.8	721.7	740.5	746.7	752.9	758.4	761.0
32.5°	95.5	131.3	341.2	415.3	612.7	712.8	726.2	729.8	738.6	751.2	755.7
35°	87.6	114.4	326.0	405.5	607.4	698.5	707.4	711.0	728.9	747.6	753.8
37.5°	79.5	101.9	306.4	388.6	599.3	681.5	687.8	694.1	721.7	744.1	751.2
40°	71.5	91.1	283.2	369.8	586.9	660.9	666.4	676.1	712.8	738.6	745.8
42.5°	65.2	82.1	258.1	350.1	570.7	637.8	645.8	660.1	702.1	729.8	737.8
45°	59.9	73.3	231.3	323.3	550.2	613.6	625.2	644.9	689.5	716.3	723.5
47.5°	54.5	67.0	203.6	295.6	527.9	589.5	604.7	627.0	672.6	698.5	704.7
50°	50.0	60.7	176.0	266.1	503.8	563.6	581.5	604.7	651.2	675.2	683.3
52.5°	46.4	55.4	150.1	236.7	476.1	536.8	557.4	581.5	625.2	648.5	653.8
55°	42.9	50.9	127.7	205.4	447.5	508.2	530.6	553.8	596.6	616.3	619.9
57.5°	41.1	47.3	109.0	176.0	417.1	476.1	501.1	522.5	562.7	577.9	581.5
60°	38.5	44.7	94.7	151.0	384.1	445.7	467.2	488.6	522.5	535.0	537.7
62.5°	35.7	42.9	84.0	126.8	350.1	410.0	431.4	451.1	479.6	488.6	492.1
65°	33.9	41.1	75.9	109.0	315.3	372.4	393.9	410.9	434.1	443.0	444.8
67.5°	32.1	39.3	69.7	93.8	280.4	335.0	351.0	367.1	384.9	393.9	394.8
70°	29.5	37.5	64.3	83.0	244.7	292.1	305.5	322.4	336.7	341.2	343.9
72.5°	27.7	34.8	60.7	75.0	208.1	250.9	263.5	273.3	285.8	290.3	290.3
75°	25.0	31.3	57.2	67.0	170.6	205.4	216.1	226.0	235.8	237.6	234.9
77.5°	22.3	27.7	49.1	56.3	133.1	162.6	171.5	176.9	184.9	186.7	187.5
80°	18.7	24.2	38.5	43.8	96.4	119.7	125.9	130.4	137.6	137.6	139.3
82.5°	14.3	18.7	27.7	31.3	65.2	82.1	87.6	90.2	94.7	94.7	94.7
85°	9.0	11.6	17.8	20.5	39.3	50.0	53.6	54.5	58.1	59.0	59.0
87.5°	4.4	6.2	11.6	12.5	20.5	25.9	25.9	27.7	27.7	26.8	25.9
90°	6.9	12.4	17.9	19.3	30.3	45.0	52.4	46.5	34.9	26.2	26.2
92.5°	27.6	74.5	121.4	133.1	187.1	259.1	295.2	258.7	185.8	131.1	125.8
95°	66.2	152.0	237.8	259.3	460.4	728.7	862.8	769.9	584.1	444.8	429.0
97.5°	114.5	190.1	265.9	284.8	620.2	1067.5	1291.1	1232.4	1115.0	1026.9	996.9
100°	151.8	220.4	289.0	306.2	678.3	1174.6	1422.8	1427.0	1435.6	1442.0	1406.2
102.5°	183.5	247.5	311.6	327.6	705.1	1208.3	1460.0	1534.7	1684.4	1796.5	1765.9
105°	237.3	291.5	345.7	359.3	724.8	1212.2	1455.9	1623.5	1958.8	2210.3	2193.8
107.5°	292.4	342.9	393.6	406.2	728.5	1158.2	1373.1	1607.0	2074.7	2425.5	2429.5
110°	329.6	375.3	420.9	432.4	722.9	1110.4	1304.1	1565.5	2088.5	2480.7	2497.9



TEST NUMBER: P937875
 CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	366.2	409.7	453.2	464.2	723.2	1068.6	1241.3	1508.9	2044.1	2445.5	2471.8
115°	421.4	461.5	501.7	511.8	729.9	1020.8	1166.2	1424.0	1939.6	2326.2	2362.8
117.5°	475.9	512.4	548.8	557.9	743.4	990.7	1114.4	1347.1	1812.4	2161.4	2201.9
120°	507.6	541.9	576.2	584.8	754.4	980.6	1093.7	1306.3	1731.4	2050.3	2089.7
122.5°	538.7	573.3	607.9	616.5	770.3	975.4	1077.9	1269.4	1652.2	1939.3	1978.1
125°	586.2	617.8	649.3	657.2	791.7	971.0	1060.7	1223.3	1548.5	1792.4	1828.2
127.5°	624.8	656.7	688.6	696.5	813.1	968.5	1046.2	1185.8	1465.1	1674.5	1704.7
130°	645.5	679.9	714.1	722.7	828.7	970.0	1040.6	1165.0	1413.5	1600.0	1627.9
132.5°	666.9	701.3	735.5	744.1	841.4	971.0	1035.9	1147.1	1369.7	1536.5	1561.5
135°	698.6	729.8	761.1	768.9	855.1	970.1	1027.6	1120.7	1307.1	1446.9	1468.4
137.5°	731.0	762.0	793.0	800.7	875.8	976.1	1026.2	1104.9	1262.5	1380.7	1398.2
140°	757.9	786.4	814.9	822.0	888.4	977.1	1021.4	1089.4	1225.5	1327.6	1344.1
142.5°	778.6	805.0	831.3	837.9	899.1	980.6	1021.4	1081.1	1200.7	1290.4	1304.6
145°	810.3	833.3	856.3	862.1	912.9	980.6	1014.5	1063.4	1161.1	1234.5	1245.2
147.5°	842.1	864.5	886.8	892.4	933.1	987.4	1014.5	1052.9	1129.9	1187.6	1196.5
150°	862.8	883.0	903.2	908.2	943.7	990.8	1014.5	1047.0	1112.0	1160.7	1167.9
152.5°	884.1	899.5	914.8	918.6	950.6	993.1	1014.5	1042.2	1097.7	1139.3	1144.7
155°	915.9	927.2	938.5	941.4	965.7	998.2	1014.5	1036.6	1080.7	1113.8	1117.5
157.5°	939.3	950.3	961.3	964.1	980.9	1003.3	1014.5	1031.6	1066.0	1091.7	1094.2
160°	955.1	963.7	972.4	974.5	987.8	1005.6	1014.5	1029.2	1058.6	1080.7	1082.1
162.5°	971.0	977.4	983.9	985.5	995.2	1008.1	1014.5	1026.9	1051.7	1070.3	1071.7
165°	988.3	994.1	1000.0	1001.4	1005.7	1011.5	1014.5	1023.3	1041.2	1054.5	1055.9
167.5°	1004.2	1006.9	1009.7	1010.4	1014.0	1018.9	1021.4	1027.2	1038.9	1047.6	1048.2
170°	1014.5	1017.2	1020.0	1020.7	1020.9	1021.2	1021.4	1027.2	1038.9	1047.6	1047.6
172.5°	1020.0	1020.6	1021.2	1021.4	1021.4	1021.4	1021.4	1026.0	1035.1	1042.1	1041.5
175°	1027.6	1027.6	1027.6	1027.6	1025.6	1022.8	1021.4	1024.3	1030.2	1034.5	1034.5
177.5°	1027.6	1027.6	1027.6	1027.6	1026.0	1023.8	1022.7	1025.0	1029.6	1033.1	1032.5
180°	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6



TEST NUMBER: P937875

CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	277.8	277.8
2.5°	296.5	294.7
5°	381.4	383.2
7.5°	513.6	512.7
10°	638.6	646.6
12.5°	729.8	731.5
15°	785.2	788.7
17.5°	806.6	807.5
20°	807.5	805.7
22.5°	797.6	795.8
25°	786.1	785.2
27.5°	775.3	776.2
30°	770.9	773.5
32.5°	770.9	775.3
35°	772.6	777.1
37.5°	771.8	777.1
40°	768.1	774.4
42.5°	758.4	762.8
45°	743.2	748.5
47.5°	723.5	727.1
50°	698.5	702.1
52.5°	667.2	668.1
55°	629.7	633.3
57.5°	589.5	590.4
60°	544.9	547.5
62.5°	497.5	497.5
65°	447.5	449.2
67.5°	395.7	400.1
70°	343.0	343.9
72.5°	291.2	291.2
75°	237.6	238.5
77.5°	186.7	186.7
80°	138.4	139.3
82.5°	95.5	97.3
85°	59.9	59.9
87.5°	27.7	25.0
90°	26.2	26.2
92.5°	105.0	84.1
95°	365.9	302.7
97.5°	876.7	756.6
100°	1263.2	1120.0
102.5°	1643.2	1520.7
105°	2127.9	2062.0
107.5°	2445.4	2461.4
110°	2566.5	2635.1



TEST NUMBER: P937875

CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2577.2	2682.7
115°	2509.0	2655.1
117.5°	2364.0	2526.2
120°	2247.3	2404.8
122.5°	2133.5	2288.9
125°	1971.4	2114.5
127.5°	1825.5	1946.2
130°	1739.5	1851.0
132.5°	1661.4	1761.3
135°	1554.5	1640.7
137.5°	1468.8	1539.3
140°	1410.0	1475.9
142.5°	1361.2	1418.0
145°	1288.1	1331.0
147.5°	1232.1	1267.6
150°	1196.8	1225.5
152.5°	1166.5	1188.2
155°	1131.8	1146.2
157.5°	1104.3	1114.4
160°	1088.0	1093.7
162.5°	1077.2	1082.7
165°	1061.8	1067.6
167.5°	1050.6	1053.1
170°	1047.6	1047.6
172.5°	1039.4	1037.3
175°	1034.5	1034.5
177.5°	1030.1	1027.6
180°	1027.6	1027.6



TEST NUMBER: P937875
 CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.56	1.01	1.69	3.29	13.03	13.72	14.18	14.86	16.45
	3H	0.56	1.18	1.71	2.32	3.93	14.85	15.47	16.01	16.61	18.22
	4H	0.85	1.44	2.01	2.58	4.19	15.49	16.07	16.65	17.22	18.83
	6H	1.09	1.63	2.26	2.78	4.40	15.90	16.44	17.07	17.59	19.21
	8H	1.15	1.67	2.33	2.83	4.45	16.02	16.53	17.19	17.69	19.31
	12H	1.17	1.65	2.34	2.81	4.45	16.08	16.56	17.25	17.72	19.36
4H	2H	7.05	7.64	8.22	8.78	10.40	13.29	13.87	14.45	15.02	16.63
	3H	8.60	9.09	9.78	10.26	11.89	15.31	15.80	16.48	16.97	18.59
	4H	8.69	9.14	9.87	10.30	11.94	16.06	16.52	17.24	17.67	19.32
	6H	8.69	9.08	9.87	10.26	11.89	16.59	16.98	17.77	18.16	19.79
	8H	8.66	9.02	9.84	10.20	11.85	16.74	17.10	17.92	18.28	19.93
	12H	8.61	8.94	9.81	10.12	11.78	16.83	17.15	18.02	18.34	19.99
8H	4H	10.12	10.48	11.30	11.65	13.30	16.11	16.47	17.29	17.64	19.29
	6H	10.35	10.65	11.55	11.86	13.51	16.73	17.02	17.93	18.24	19.89
	8H	10.37	10.63	11.57	11.82	13.49	16.94	17.20	18.15	18.39	20.06
	12H	10.33	10.55	11.54	11.74	13.44	17.07	17.30	18.28	18.49	20.19
12H	4H	10.25	10.58	11.45	11.76	13.42	16.05	16.38	17.25	17.57	19.22
	6H	10.61	10.87	11.81	12.06	13.73	16.71	16.97	17.91	18.16	19.83
	8H	10.67	10.89	11.88	12.08	13.78	16.93	17.15	18.14	18.34	20.04