

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938075

Luminaire Tested: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938075
REPORT IS A COMBINATION OF REPORTS P933607 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10899.3 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 96.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938075
CATALOG NUMBER: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P938075

CATALOG NUMBER: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	95	90	86	83	86	82	79	76	67	65	62	53	51	50	40	39	38	32				
2	86	78	72	67	78	71	66	61	58	54	51	46	43	41	35	33	31	26				
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26	21				
4	71	60	52	46	64	55	48	42	45	40	35	35	32	29	27	24	22	18				
5	65	53	45	39	59	49	41	36	40	34	30	31	27	24	24	21	19	15				
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13				
7	55	43	35	29	50	39	32	27	32	26	23	25	21	18	19	16	14	11				
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13	10				
9	47	35	27	22	43	32	25	21	26	21	17	21	17	14	16	13	11	9				
10	44	32	25	20	40	29	23	18	24	19	16	19	15	13	15	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3386	3386	3386
5°	3306	3912	4551
10°	2998	5702	7545
15°	2547	7447	9110
20°	2072	8628	9285
25°	1728	9026	9096
30°	1457	9081	9079
35°	1287	8928	9314
40°	1121	8729	9556
45°	1015	8583	9593
50°	930	8452	9435
55°	889	8260	9016
60°	910	7893	8356
65°	945	7338	7449
70°	1005	6395	6292
75°	1109	5210	4910
80°	1201	3608	3310
85°	1049	1911	1694

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9593 cd/sqm



TEST NUMBER: P938075

CATALOG NUMBER: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.8	0.6
10°-20°	313.8	2.9
20°-30°	548.8	5.0
30°-40°	706.5	6.5
40°-50°	789.2	7.2
50°-60°	755.8	6.9
60°-70°	599.0	5.5
70°-80°	352.2	3.2
80°-90°	101.8	0.9
90°-100°	500.9	4.6
100°-110°	1316.9	12.1
110°-120°	1365.4	12.5
120°-130°	1095.3	10.0
130°-140°	859.4	7.9
140°-150°	659.6	6.1
150°-160°	475.0	4.4
160°-170°	290.7	2.7
170°-180°	98.2	0.9
0°-30°	933.4	8.6
0°-40°	1639.9	15.0
0°-60°	3184.9	29.2
0°-90°	4237.9	38.9
90°-120°	3183.2	29.2
90°-150°	5797.5	53.2
90°-180°	6661.0	61.1
0°-180°	10899.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	533	572	644	729	755	49
15°	400	737	1242	1506	1554	111
25°	255	836	1480	1545	1547	118
35°	172	799	1394	1473	1531	108
45°	118	637	1232	1411	1475	91
55°	84	405	1045	1214	1248	77
65°	67	215	776	873	885	66
75°	49	132	426	468	470	52
85°	18	40	106	116	118	19
90°	7	19	52	26	26	7
95°	66	259	863	445	303	74
105°	237	359	1456	2210	2062	252
115°	421	512	1166	2326	2655	416
125°	586	657	1061	1792	2114	520
135°	699	769	1028	1447	1641	541
145°	810	862	1014	1234	1331	508
155°	916	941	1014	1114	1146	421
165°	988	1001	1014	1054	1068	279
175°	1028	1028	1021	1034	1034	98
180°	1028	1028	1028	1028	1028	



TEST NUMBER: P938075
 CATALOG NUMBER: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	547.3	547.3	547.3	547.3	547.3	547.3	547.3	547.3	547.3	547.3	547.3
2.5°	547.3	547.3	550.8	552.6	556.1	557.8	561.4	564.9	575.4	577.2	580.8
5°	533.2	540.3	563.2	572.0	596.6	630.0	644.1	667.0	714.5	728.6	737.4
7.5°	512.1	527.9	584.3	598.3	660.0	748.0	784.9	834.2	909.8	946.8	976.7
10°	478.6	512.1	612.5	645.8	746.2	879.9	948.6	1017.2	1131.6	1182.6	1202.0
12.5°	441.7	496.3	642.4	688.1	832.4	1027.8	1110.4	1186.1	1316.4	1385.0	1395.6
15°	399.5	473.4	670.5	737.4	923.9	1150.9	1242.5	1335.7	1457.1	1506.4	1518.7
17.5°	362.6	455.8	696.9	767.3	994.3	1261.8	1355.1	1432.5	1531.1	1564.5	1573.3
20°	316.7	427.7	714.5	806.0	1068.3	1342.7	1432.5	1492.4	1559.2	1580.4	1583.8
22.5°	283.4	397.7	725.1	820.1	1117.5	1392.0	1467.7	1515.2	1561.0	1568.0	1569.8
25°	255.2	364.3	723.3	836.0	1159.7	1422.0	1480.0	1515.2	1541.7	1545.1	1545.1
27.5°	228.7	327.3	716.3	839.4	1191.4	1429.0	1474.7	1499.4	1511.7	1518.7	1518.7
30°	205.9	292.2	698.7	832.4	1205.5	1422.0	1458.9	1471.2	1483.6	1494.1	1499.4
32.5°	188.3	258.7	672.2	818.3	1207.2	1404.4	1430.7	1437.8	1455.3	1480.0	1488.8
35°	172.4	225.3	642.4	798.9	1196.7	1376.2	1393.8	1400.8	1436.0	1473.0	1485.3
37.5°	156.6	200.6	603.7	765.5	1180.9	1342.7	1355.1	1367.4	1422.0	1465.9	1480.0
40°	140.7	179.5	557.8	728.6	1156.2	1302.3	1312.8	1332.2	1404.4	1455.3	1469.5
42.5°	128.5	161.9	508.6	689.9	1124.6	1256.5	1272.3	1300.5	1383.2	1437.8	1453.7
45°	117.9	144.3	455.8	637.1	1084.1	1209.0	1231.9	1270.6	1358.6	1411.4	1425.5
47.5°	107.4	132.0	401.3	582.5	1040.0	1161.5	1191.4	1235.4	1325.2	1376.2	1388.5
50°	98.6	119.7	346.7	524.5	992.5	1110.4	1145.7	1191.4	1282.9	1330.4	1346.3
52.5°	91.6	109.1	295.6	466.4	938.0	1057.7	1098.1	1145.7	1231.9	1277.7	1288.2
55°	84.4	100.3	251.7	404.8	881.7	1001.3	1045.4	1091.1	1175.5	1214.3	1221.4
57.5°	81.0	93.2	214.7	346.7	821.8	938.0	987.3	1029.5	1108.7	1138.6	1145.7
60°	75.7	88.0	186.6	297.4	756.8	878.1	920.4	962.6	1029.5	1054.1	1059.4
62.5°	70.4	84.4	165.4	249.9	689.9	807.7	850.0	888.7	945.0	962.6	969.7
65°	66.9	81.0	149.6	214.7	621.2	733.8	776.1	809.5	855.3	872.9	876.4
67.5°	63.3	77.4	137.3	184.8	552.6	660.0	691.6	723.3	758.5	776.1	777.9
70°	58.1	73.9	126.7	163.7	482.2	575.4	601.9	635.3	663.4	672.2	677.5
72.5°	54.5	68.6	119.7	147.9	410.1	494.5	519.1	538.5	563.2	572.0	572.0
75°	49.3	61.6	112.6	132.0	336.1	404.8	425.9	445.2	464.6	468.2	462.8
77.5°	44.0	54.5	96.8	110.9	262.2	320.3	337.9	348.5	364.3	367.8	369.6
80°	36.9	47.5	75.7	86.2	190.0	235.9	248.1	256.9	271.0	271.0	274.6
82.5°	28.1	36.9	54.5	61.6	128.5	161.9	172.4	177.8	186.6	186.6	186.6
85°	17.6	22.9	35.2	40.5	77.4	98.6	105.6	107.4	114.4	116.2	116.2
87.5°	8.8	12.3	22.9	24.6	40.5	51.1	51.1	54.5	54.5	52.8	51.1
90°	6.9	12.4	17.9	19.3	30.3	45.0	52.4	46.5	34.9	26.2	26.2
92.5°	27.6	74.5	121.4	133.1	187.1	259.1	295.2	258.7	185.8	131.1	125.8
95°	66.2	152.0	237.8	259.3	460.4	728.7	862.8	769.9	584.1	444.8	429.0
97.5°	114.5	190.1	265.9	284.8	620.2	1067.5	1291.1	1232.4	1115.0	1026.9	996.9
100°	151.8	220.4	289.0	306.2	678.3	1174.6	1422.8	1427.0	1435.6	1442.0	1406.2
102.5°	183.5	247.5	311.6	327.6	705.1	1208.3	1460.0	1534.7	1684.4	1796.5	1765.9
105°	237.3	291.5	345.7	359.3	724.8	1212.2	1455.9	1623.5	1958.8	2210.3	2193.8
107.5°	292.4	342.9	393.6	406.2	728.5	1158.2	1373.1	1607.0	2074.7	2425.5	2429.5
110°	329.6	375.3	420.9	432.4	722.9	1110.4	1304.1	1565.5	2088.5	2480.7	2497.9



TEST NUMBER: P938075

CATALOG NUMBER: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	366.2	409.7	453.2	464.2	723.2	1068.6	1241.3	1508.9	2044.1	2445.5	2471.8
115°	421.4	461.5	501.7	511.8	729.9	1020.8	1166.2	1424.0	1939.6	2326.2	2362.8
117.5°	475.9	512.4	548.8	557.9	743.4	990.7	1114.4	1347.1	1812.4	2161.4	2201.9
120°	507.6	541.9	576.2	584.8	754.4	980.6	1093.7	1306.3	1731.4	2050.3	2089.7
122.5°	538.7	573.3	607.9	616.5	770.3	975.4	1077.9	1269.4	1652.2	1939.3	1978.1
125°	586.2	617.8	649.3	657.2	791.7	971.0	1060.7	1223.3	1548.5	1792.4	1828.2
127.5°	624.8	656.7	688.6	696.5	813.1	968.5	1046.2	1185.8	1465.1	1674.5	1704.7
130°	645.5	679.9	714.1	722.7	828.7	970.0	1040.6	1165.0	1413.5	1600.0	1627.9
132.5°	666.9	701.3	735.5	744.1	841.4	971.0	1035.9	1147.1	1369.7	1536.5	1561.5
135°	698.6	729.8	761.1	768.9	855.1	970.1	1027.6	1120.7	1307.1	1446.9	1468.4
137.5°	731.0	762.0	793.0	800.7	875.8	976.1	1026.2	1104.9	1262.5	1380.7	1398.2
140°	757.9	786.4	814.9	822.0	888.4	977.1	1021.4	1089.4	1225.5	1327.6	1344.1
142.5°	778.6	805.0	831.3	837.9	899.1	980.6	1021.4	1081.1	1200.7	1290.4	1304.6
145°	810.3	833.3	856.3	862.1	912.9	980.6	1014.5	1063.4	1161.1	1234.5	1245.2
147.5°	842.1	864.5	886.8	892.4	933.1	987.4	1014.5	1052.9	1129.9	1187.6	1196.5
150°	862.8	883.0	903.2	908.2	943.7	990.8	1014.5	1047.0	1112.0	1160.7	1167.9
152.5°	884.1	899.5	914.8	918.6	950.6	993.1	1014.5	1042.2	1097.7	1139.3	1144.7
155°	915.9	927.2	938.5	941.4	965.7	998.2	1014.5	1036.6	1080.7	1113.8	1117.5
157.5°	939.3	950.3	961.3	964.1	980.9	1003.3	1014.5	1031.6	1066.0	1091.7	1094.2
160°	955.1	963.7	972.4	974.5	987.8	1005.6	1014.5	1029.2	1058.6	1080.7	1082.1
162.5°	971.0	977.4	983.9	985.5	995.2	1008.1	1014.5	1026.9	1051.7	1070.3	1071.7
165°	988.3	994.1	1000.0	1001.4	1005.7	1011.5	1014.5	1023.3	1041.2	1054.5	1055.9
167.5°	1004.2	1006.9	1009.7	1010.4	1014.0	1018.9	1021.4	1027.2	1038.9	1047.6	1048.2
170°	1014.5	1017.2	1020.0	1020.7	1020.9	1021.2	1021.4	1027.2	1038.9	1047.6	1047.6
172.5°	1020.0	1020.6	1021.2	1021.4	1021.4	1021.4	1021.4	1026.0	1035.1	1042.1	1041.5
175°	1027.6	1027.6	1027.6	1027.6	1025.6	1022.8	1021.4	1024.3	1030.2	1034.5	1034.5
177.5°	1027.6	1027.6	1027.6	1027.6	1026.0	1023.8	1022.7	1025.0	1029.6	1033.1	1032.5
180°	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6



TEST NUMBER: P938075

CATALOG NUMBER: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	547.3	547.3
2.5°	584.3	580.8
5°	751.4	755.0
7.5°	1011.9	1010.2
10°	1258.3	1274.1
12.5°	1437.8	1441.3
15°	1546.9	1553.9
17.5°	1589.2	1590.9
20°	1590.9	1587.4
22.5°	1571.5	1568.0
25°	1548.7	1546.9
27.5°	1527.5	1529.3
30°	1518.7	1524.0
32.5°	1518.7	1527.5
35°	1522.3	1531.1
37.5°	1520.5	1531.1
40°	1513.4	1525.8
42.5°	1494.1	1502.9
45°	1464.2	1474.7
47.5°	1425.5	1432.5
50°	1376.2	1383.2
52.5°	1314.6	1316.4
55°	1240.7	1247.7
57.5°	1161.5	1163.3
60°	1073.5	1078.7
62.5°	980.3	980.3
65°	881.7	885.2
67.5°	779.6	788.4
70°	675.8	677.5
72.5°	573.7	573.7
75°	468.2	469.8
77.5°	367.8	367.8
80°	272.8	274.6
82.5°	188.3	191.8
85°	117.9	117.9
87.5°	54.5	49.3
90°	26.2	26.2
92.5°	105.0	84.1
95°	365.9	302.7
97.5°	876.7	756.6
100°	1263.2	1120.0
102.5°	1643.2	1520.7
105°	2127.9	2062.0
107.5°	2445.4	2461.4
110°	2566.5	2635.1



TEST NUMBER: P938075

CATALOG NUMBER: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2577.2	2682.7
115°	2509.0	2655.1
117.5°	2364.0	2526.2
120°	2247.3	2404.8
122.5°	2133.5	2288.9
125°	1971.4	2114.5
127.5°	1825.5	1946.2
130°	1739.5	1851.0
132.5°	1661.4	1761.3
135°	1554.5	1640.7
137.5°	1468.8	1539.3
140°	1410.0	1475.9
142.5°	1361.2	1418.0
145°	1288.1	1331.0
147.5°	1232.1	1267.6
150°	1196.8	1225.5
152.5°	1166.5	1188.2
155°	1131.8	1146.2
157.5°	1104.3	1114.4
160°	1088.0	1093.7
162.5°	1077.2	1082.7
165°	1061.8	1067.6
167.5°	1050.6	1053.1
170°	1047.6	1047.6
172.5°	1039.4	1037.3
175°	1034.5	1034.5
177.5°	1030.1	1027.6
180°	1027.6	1027.6



TEST NUMBER: P938075
 CATALOG NUMBER: SQ4-FB-125U-100D-940-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.13	4.92	5.17	5.97	7.39	17.29	18.09	18.33	19.14	20.56
	3H	4.83	5.54	5.88	6.60	8.04	19.12	19.84	20.17	20.90	22.33
	4H	5.12	5.80	6.18	6.86	8.31	19.76	20.44	20.82	21.50	22.95
	6H	5.37	6.00	6.44	7.06	8.52	20.18	20.81	21.25	21.87	23.33
	8H	5.44	6.03	6.51	7.11	8.56	20.30	20.90	21.38	21.98	23.43
	12H	5.45	6.02	6.53	7.09	8.57	20.36	20.93	21.44	22.01	23.48
4H	2H	11.33	12.01	12.39	13.07	14.51	17.56	18.24	18.63	19.30	20.74
	3H	12.89	13.46	13.96	14.55	16.00	19.59	20.16	20.67	21.25	22.71
	4H	12.98	13.50	14.06	14.58	16.06	20.35	20.88	21.44	21.96	23.43
	6H	12.99	13.44	14.08	14.54	16.01	20.89	21.33	21.98	22.44	23.91
	8H	12.96	13.38	14.05	14.48	15.97	21.04	21.46	22.13	22.56	24.05
	12H	12.92	13.30	14.03	14.40	15.90	21.13	21.51	22.24	22.62	24.11
8H	4H	14.42	14.84	15.51	15.93	17.42	20.41	20.83	21.50	21.92	23.41
	6H	14.66	15.00	15.77	16.14	17.63	21.03	21.38	22.15	22.52	24.00
	8H	14.67	14.98	15.79	16.10	17.60	21.25	21.55	22.37	22.67	24.18
	12H	14.64	14.91	15.76	16.02	17.56	21.39	21.65	22.51	22.77	24.31
12H	4H	14.56	14.94	15.66	16.04	17.54	20.36	20.74	21.47	21.85	23.34
	6H	14.91	15.22	16.03	16.34	17.84	21.01	21.32	22.13	22.44	23.94
	8H	14.98	15.25	16.10	16.36	17.90	21.24	21.51	22.36	22.62	24.16