

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562551

Luminaire Tested: **SQ4-PC3-025U-075D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562551
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-075D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5027.4 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562551
CATALOG NUMBER: SQ4-PC3-025U-075D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562551

CATALOG NUMBER: SQ4-PC3-025U-075D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75				
1	103	99	95	91	98	94	91	88	85	83	80	77	75	73	70	68	67	63				
2	94	87	80	75	89	82	77	72	75	70	66	68	64	61	62	59	56	53				
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48	45				
4	79	67	59	53	75	64	57	51	59	53	48	54	49	44	49	45	41	38				
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	39	36	33				
6	67	54	46	39	63	52	44	38	48	41	36	44	38	34	40	35	32	29				
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28	26				
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	29	25	23				
9	54	41	33	28	51	39	32	27	36	30	25	33	28	24	31	26	23	21				
10	50	37	30	25	48	36	29	24	33	27	23	31	26	22	29	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8476	8476	8476
5°	8540	8485	8454
10°	8520	8480	8456
15°	8475	8475	8467
20°	8420	8444	8444
25°	8339	8401	8374
30°	8238	8338	8302
35°	8115	8240	8183
40°	7981	8094	8012
45°	7837	7892	7770
50°	7631	7631	7510
55°	7390	7293	7184
60°	7033	6891	6782
65°	6500	6370	6315
70°	5692	5737	5713
75°	4579	5064	5095
80°	3255	4293	4339
85°	1983	3599	3599



TEST NUMBER: P562551

CATALOG NUMBER: SQ4-PC3-025U-075D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.4	2.6
10°-20°	374.3	7.4
20°-30°	566.8	11.3
30°-40°	679.5	13.5
40°-50°	692.9	13.8
50°-60°	604.8	12.0
60°-70°	433.0	8.6
70°-80°	223.0	4.4
80°-90°	57.4	1.1
90°-100°	95.1	1.9
100°-110°	250.1	5.0
110°-120°	259.3	5.2
120°-130°	208.0	4.1
130°-140°	163.2	3.2
140°-150°	125.3	2.5
150°-160°	90.2	1.8
160°-170°	55.2	1.1
170°-180°	18.6	0.4
0°-30°	1071.5	21.3
0°-40°	1751.0	34.8
0°-60°	3048.8	60.6
0°-90°	3762.2	74.8
90°-120°	604.6	12.0
90°-150°	1101.1	21.9
90°-180°	1265.0	25.2
0°-180°	5027.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1378	1378	1378	1378	1378	
5°	1383	1370	1374	1370	1369	131
15°	1331	1320	1331	1331	1330	375
25°	1229	1220	1238	1234	1234	566
35°	1081	1078	1097	1090	1090	676
45°	901	898	907	896	893	693
55°	689	680	680	670	670	614
65°	447	437	438	434	434	442
75°	193	201	213	214	214	208
85°	28	43	51	52	51	38
90°	1	4	10	5	5	2
95°	12	49	164	84	58	14
105°	45	68	276	420	392	48
115°	80	97	222	442	504	79
125°	111	125	201	340	402	99
135°	133	146	195	275	312	103
145°	154	164	193	234	253	96
155°	174	179	193	212	218	80
165°	188	190	193	200	203	53
175°	195	195	194	196	196	19
180°	195	195	195	195	195	

TEST NUMBER: P562551

CATALOG NUMBER: SQ4-PC3-025U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1378.1	1378.1	1378.1	1378.1	1378.1
2.5°	1386.3	1374.3	1378.1	1375.0	1370.0
5°	1383.2	1369.5	1374.3	1370.5	1369.2
7.5°	1373.3	1359.6	1365.9	1363.3	1362.1
10°	1364.1	1350.4	1357.7	1355.1	1353.9
12.5°	1351.9	1339.1	1347.5	1345.0	1344.7
15°	1330.9	1319.7	1330.9	1330.9	1329.6
17.5°	1304.6	1294.4	1306.4	1307.2	1306.4
20°	1286.3	1275.0	1290.1	1288.8	1290.1
22.5°	1263.8	1254.6	1270.7	1267.4	1268.7
25°	1228.8	1220.1	1237.8	1233.9	1233.9
27.5°	1187.5	1181.3	1200.5	1196.4	1196.4
30°	1159.9	1153.7	1174.0	1168.9	1168.9
32.5°	1129.3	1125.1	1144.4	1138.2	1138.2
35°	1080.8	1078.3	1097.4	1089.8	1089.8
37.5°	1030.8	1028.6	1045.9	1036.6	1033.6
40°	994.0	992.8	1008.1	997.9	997.9
42.5°	957.3	956.0	969.3	957.0	957.0
45°	900.9	898.4	907.3	895.7	893.2
47.5°	839.4	836.9	842.5	829.9	828.7
50°	797.5	795.0	797.5	786.0	784.8
52.5°	754.7	750.2	750.6	739.1	738.8
55°	689.1	680.3	680.1	669.9	669.9
57.5°	619.7	608.2	609.2	600.5	599.2
60°	571.7	559.2	560.2	552.5	551.3
62.5°	524.7	510.2	513.2	504.5	504.3
65°	446.6	436.6	437.7	433.9	433.9
67.5°	371.6	362.4	369.0	366.0	365.7
70°	316.5	310.2	319.0	319.0	317.7
72.5°	265.4	265.2	276.1	276.2	276.9
75°	192.7	201.4	213.1	214.4	214.4
77.5°	128.6	144.1	157.0	157.5	157.2
80°	91.9	109.3	121.2	123.7	122.5
82.5°	62.3	80.7	90.6	93.1	91.9
85°	28.1	43.0	51.0	52.3	51.0
87.5°	8.4	17.9	22.4	21.4	19.4
90°	1.3	3.7	10.0	5.0	5.0
92.5°	5.3	25.3	56.1	24.8	16.0
95°	12.5	49.2	163.9	84.5	57.6
97.5°	21.8	54.1	245.2	195.0	143.6
100°	28.8	58.1	270.3	273.9	212.7
102.5°	34.8	62.2	277.3	341.1	288.8
105°	45.0	68.3	276.5	419.8	391.6
107.5°	55.6	77.1	260.8	460.6	467.5
110°	62.6	82.1	247.7	471.1	500.5



TEST NUMBER: P562551

CATALOG NUMBER: SQ4-PC3-025U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	69.6	88.2	235.7	464.5	509.5
115°	80.1	97.2	221.5	441.8	504.2
117.5°	90.3	106.0	211.7	410.5	479.7
120°	96.3	111.0	207.7	389.4	456.7
122.5°	102.3	117.0	204.7	368.4	434.7
125°	111.4	124.8	201.4	340.5	401.6
127.5°	118.6	132.3	198.7	318.0	369.6
130°	122.6	137.3	197.7	303.9	351.6
132.5°	126.6	141.3	196.7	291.8	334.6
135°	132.6	146.1	195.2	274.8	311.6
137.5°	138.9	152.1	194.9	262.2	292.3
140°	143.9	156.1	193.9	252.1	280.3
142.5°	147.9	159.1	193.9	245.0	269.3
145°	153.9	163.7	192.7	234.4	252.7
147.5°	159.9	169.4	192.7	225.6	240.7
150°	163.9	172.5	192.7	220.5	232.7
152.5°	167.9	174.5	192.7	216.4	225.7
155°	173.9	178.8	192.7	211.6	217.7
157.5°	178.4	183.1	192.7	207.3	211.7
160°	181.4	185.1	192.7	205.3	207.7
162.5°	184.4	187.1	192.7	203.3	205.7
165°	187.7	190.1	192.7	200.2	202.7
167.5°	190.7	191.9	193.9	199.0	199.9
170°	192.7	193.9	193.9	198.9	198.9
172.5°	193.7	193.9	193.9	197.9	196.9
175°	195.2	195.2	193.9	196.4	196.4
177.5°	195.2	195.2	194.2	196.2	195.2
180°	195.2	195.2	195.2	195.2	195.2

(END OF REPORT)