

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562671

Luminaire Tested: **SQ4-PC3-050U-100D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562671  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-050U-100D-940-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7582.0 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 73.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562671  
CATALOG NUMBER: SQ4-PC3-050U-100D-940-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P562671

CATALOG NUMBER: SQ4-PC3-050U-100D-940-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	90	95	91	88	85	81	78	76	72	70	68	63	61	60	56
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	36	29	24	46	35	28	23	32	26	22	28	23	20	26	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11263	11263	11263
5°	11348	11274	11233
10°	11320	11267	11235
15°	11261	11261	11250
20°	11187	11220	11220
25°	11081	11161	11127
30°	10946	11079	11031
35°	10783	10948	10873
40°	10605	10754	10646
45°	10412	10486	10323
50°	10140	10140	9978
55°	9819	9691	9545
60°	9344	9156	9011
65°	8636	8465	8390
70°	7562	7623	7593
75°	6084	6728	6768
80°	4325	5706	5767
85°	2632	4785	4785



TEST NUMBER: P562671

CATALOG NUMBER: SQ4-PC3-050U-100D-940-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	173.3	2.3
10°-20°	497.3	6.6
20°-30°	753.1	9.9
30°-40°	902.9	11.9
40°-50°	920.6	12.1
50°-60°	803.7	10.6
60°-70°	575.4	7.6
70°-80°	296.3	3.9
80°-90°	76.5	1.0
90°-100°	189.9	2.5
100°-110°	515.9	6.8
110°-120°	530.4	7.0
120°-130°	424.1	5.6
130°-140°	333.2	4.4
140°-150°	255.5	3.4
150°-160°	183.7	2.4
160°-170°	112.4	1.5
170°-180°	37.9	0.5
0°-30°	1423.7	18.8
0°-40°	2326.6	30.7
0°-60°	4050.9	53.4
0°-90°	4999.0	65.9
90°-120°	1236.2	16.3
90°-150°	2249.0	29.7
90°-180°	2583.0	34.1
0°-180°	7582.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1831	1831	1831	1831	1831	
5°	1838	1820	1826	1821	1819	174
15°	1768	1754	1768	1768	1767	499
25°	1633	1621	1645	1640	1640	751
35°	1436	1433	1458	1448	1448	898
45°	1197	1194	1206	1190	1187	921
55°	916	904	904	890	890	816
65°	593	580	582	576	576	587
75°	256	268	283	285	285	277
85°	37	57	68	70	68	51
90°	1	5	9	11	11	3
95°	28	104	331	144	97	30
105°	92	143	567	864	813	97
115°	163	198	454	903	1029	161
125°	224	255	411	692	817	200
135°	270	300	399	564	636	209
145°	312	334	394	479	515	196
155°	352	365	392	430	443	162
165°	382	387	393	410	411	108
175°	396	397	394	399	398	38
180°	396	396	396	396	396	

TEST NUMBER: P562671

CATALOG NUMBER: SQ4-PC3-050U-100D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1831.1	1831.1	1831.1	1831.1	1831.1
2.5°	1842.0	1826.1	1831.1	1826.9	1820.3
5°	1837.9	1819.7	1826.0	1820.9	1819.3
7.5°	1824.7	1806.5	1814.9	1811.4	1809.8
10°	1812.5	1794.2	1804.0	1800.6	1798.9
12.5°	1796.2	1779.3	1790.4	1787.0	1786.7
15°	1768.4	1753.5	1768.4	1768.4	1766.7
17.5°	1733.5	1719.9	1735.8	1736.8	1735.8
20°	1709.1	1694.1	1714.1	1712.5	1714.1
22.5°	1679.2	1667.0	1688.4	1684.0	1685.7
25°	1632.8	1621.2	1644.6	1639.5	1639.5
27.5°	1577.8	1569.5	1595.1	1589.7	1589.7
30°	1541.2	1532.9	1559.9	1553.1	1553.1
32.5°	1500.5	1494.9	1520.5	1512.4	1512.4
35°	1436.1	1432.8	1458.1	1448.0	1448.0
37.5°	1369.6	1366.6	1389.6	1377.3	1373.4
40°	1320.8	1319.1	1339.4	1325.9	1325.9
42.5°	1272.0	1270.3	1287.9	1271.6	1271.6
45°	1197.0	1193.7	1205.5	1190.2	1186.8
47.5°	1115.3	1112.0	1119.4	1102.7	1101.1
50°	1059.7	1056.4	1059.7	1044.4	1042.7
52.5°	1002.7	996.7	997.3	982.0	981.7
55°	915.6	904.0	903.7	890.1	890.1
57.5°	823.3	808.1	809.4	797.9	796.2
60°	759.6	743.0	744.3	734.1	732.5
62.5°	697.2	678.0	681.9	670.4	670.1
65°	593.4	580.2	581.6	576.5	576.5
67.5°	493.7	481.5	490.3	486.3	485.9
70°	420.5	412.2	423.9	423.8	422.2
72.5°	352.7	352.3	366.9	366.9	367.9
75°	256.0	267.6	283.1	284.8	284.8
77.5°	170.9	191.5	208.5	209.2	208.9
80°	122.1	145.3	161.1	164.4	162.8
82.5°	82.7	107.3	120.4	123.7	122.1
85°	37.3	57.2	67.8	69.5	67.8
87.5°	11.1	23.8	28.9	29.4	26.7
90°	1.3	5.0	8.9	11.4	11.4
92.5°	11.4	52.0	90.3	38.8	32.8
95°	28.0	103.9	330.7	143.9	96.7
97.5°	46.3	114.7	507.0	394.5	277.0
100°	58.5	121.9	561.0	568.6	459.2
102.5°	70.7	129.2	575.2	703.3	606.8
105°	91.6	142.6	567.3	863.8	812.8
107.5°	113.2	158.2	534.5	946.7	960.9
110°	128.5	169.5	510.1	963.0	1024.0

TEST NUMBER: P562671

CATALOG NUMBER: SQ4-PC3-050U-100D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	180.8	485.7	949.5	1041.3
115°	162.8	197.6	454.1	903.4	1029.1
117.5°	182.7	216.0	434.0	838.2	979.7
120°	195.9	228.2	424.9	794.4	934.9
122.5°	207.1	239.4	418.7	750.5	886.1
125°	223.9	255.0	410.9	692.3	816.6
127.5°	238.9	269.7	406.5	648.1	754.8
130°	248.0	277.9	404.5	620.4	716.1
132.5°	257.2	287.1	402.5	596.7	681.5
135°	269.7	299.5	399.4	563.9	636.0
137.5°	283.2	310.3	397.9	534.9	595.6
140°	291.3	317.4	396.9	516.4	571.1
142.5°	299.4	323.6	395.9	502.0	547.7
145°	311.6	334.0	394.3	479.1	515.2
147.5°	325.4	344.5	393.1	461.1	489.5
150°	334.5	350.7	393.1	450.8	473.2
152.5°	341.7	355.8	392.0	441.6	460.0
155°	352.3	364.8	391.8	430.2	442.7
157.5°	362.8	372.5	391.8	422.5	432.0
160°	368.9	377.6	391.8	417.4	424.9
162.5°	375.0	381.7	392.8	413.3	418.7
165°	381.6	386.6	393.1	409.6	410.9
167.5°	388.5	391.0	394.3	405.3	406.3
170°	390.5	393.0	394.3	403.2	403.2
172.5°	392.5	394.0	394.3	401.2	401.2
175°	395.6	396.8	394.3	399.4	398.1
177.5°	396.6	396.6	393.6	397.6	395.6
180°	395.6	395.6	395.6	395.6	395.6

(END OF REPORT)