

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562815

Luminaire Tested: **SQ4-PC3-0U-050D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562815
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-050D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2551.9 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562815
CATALOG NUMBER: SQ4-PC3-0U-050D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562815

CATALOG NUMBER: SQ4-PC3-0U-050D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5751	5751	5751
5°	5795	5757	5736
10°	5780	5754	5737
15°	5750	5750	5744
20°	5712	5729	5729
25°	5658	5699	5682
30°	5590	5657	5633
35°	5506	5591	5552
40°	5415	5492	5436
45°	5317	5355	5271
50°	5178	5178	5095
55°	5013	4949	4874
60°	4772	4676	4601
65°	4410	4323	4285
70°	3861	3892	3877
75°	3106	3436	3458
80°	2207	2912	2943
85°	1341	2442	2442



TEST NUMBER: P562815

CATALOG NUMBER: SQ4-PC3-0U-050D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.5	3.5
10°-20°	253.9	10.0
20°-30°	384.6	15.1
30°-40°	461.0	18.1
40°-50°	470.1	18.4
50°-60°	410.4	16.1
60°-70°	293.8	11.5
70°-80°	151.3	5.9
80°-90°	38.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	727.0	28.5
0°-40°	1188.1	46.6
0°-60°	2068.5	81.1
0°-90°	2551.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2551.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	935	935	935	935	935	
5°	938	929	932	930	929	89
15°	903	895	903	903	902	255
25°	834	828	840	837	837	384
35°	733	732	745	739	739	459
45°	611	610	616	608	606	470
55°	468	462	462	454	454	417
65°	303	296	297	294	294	300
75°	131	137	145	146	146	141
85°	19	29	35	36	35	27
90°	0	0	0	0	0	



TEST NUMBER: P562815

CATALOG NUMBER: SQ4-PC3-0U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	935.0	935.0	935.0	935.0	935.0
2.5°	940.6	932.5	935.0	932.9	929.5
5°	938.5	929.2	932.4	929.8	929.0
7.5°	931.7	922.4	926.7	925.0	924.1
10°	925.5	916.2	921.2	919.4	918.6
12.5°	917.2	908.6	914.3	912.5	912.4
15°	903.0	895.4	903.0	903.0	902.1
17.5°	885.2	878.2	886.4	886.9	886.4
20°	872.7	865.1	875.3	874.5	875.3
22.5°	857.5	851.2	862.1	859.9	860.8
25°	833.7	827.8	839.8	837.2	837.2
27.5°	805.7	801.5	814.5	811.8	811.8
30°	787.0	782.8	796.5	793.1	793.1
32.5°	766.2	763.3	776.4	772.3	772.3
35°	733.3	731.6	744.6	739.4	739.4
37.5°	699.4	697.9	709.6	703.3	701.3
40°	674.4	673.6	684.0	677.0	677.0
42.5°	649.5	648.7	657.6	649.3	649.3
45°	611.2	609.5	615.6	607.7	606.0
47.5°	569.5	567.8	571.6	563.1	562.2
50°	541.1	539.4	541.1	533.3	532.5
52.5°	512.0	509.0	509.2	501.5	501.3
55°	467.5	461.6	461.5	454.5	454.5
57.5°	420.4	412.6	413.3	407.4	406.6
60°	387.9	379.4	380.1	374.9	374.0
62.5°	356.0	346.2	348.2	342.3	342.2
65°	303.0	296.2	297.0	294.4	294.4
67.5°	252.1	245.8	250.4	248.3	248.1
70°	214.7	210.5	216.4	216.4	215.6
72.5°	180.1	179.9	187.4	187.4	187.9
75°	130.7	136.7	144.6	145.5	145.5
77.5°	87.3	97.8	106.5	106.8	106.7
80°	62.3	74.2	82.2	84.0	83.1
82.5°	42.2	54.8	61.5	63.2	62.3
85°	19.0	29.2	34.6	35.5	34.6
87.5°	5.5	11.6	13.9	13.8	12.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)