

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P519760

Luminaire Tested: **SQ4-125U-0D-940-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519760  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-125U-0D-940-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4321.8 lumens  
Efficiency: N/A  
Efficacy: 136.3 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 31.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519760  
CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P519760

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	5060	54348	19235
100°	5212	47712	41416
105°	5565	33259	46694
110°	5775	23121	44494
115°	6014	16961	37069
120°	6106	13361	28908
125°	6050	11221	22320
130°	5974	9842	17395
135°	5909	8846	14054
140°	5875	8114	11668
145°	5897	7541	9836
150°	5979	7087	8568
155°	6051	6754	7666
160°	6113	6523	7058
165°	6158	6362	6647
170°	6200	6248	6400
175°	6208	6176	6248



TEST NUMBER: P519760

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	313.2	7.2
100°-110°	843.6	19.5
110°-120°	885.4	20.5
120°-130°	718.5	16.6
130°-140°	563.5	13.0
140°-150°	432.6	10.0
150°-160°	311.0	7.2
160°-170°	190.0	4.4
170°-180°	64.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2042.2	47.3
90°-150°	3756.7	86.9
90°-180°	4322.0	100.0
0°-180°	4321.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	5	10	11	11	
95°	48	170	513	262	182	53
105°	156	243	933	1396	1310	164
115°	276	337	777	1501	1698	271
125°	376	432	698	1179	1388	336
135°	453	505	678	951	1077	350
145°	524	564	670	813	873	328
155°	594	616	664	730	753	274
165°	645	652	666	693	696	182
175°	670	670	667	676	675	64
180°	670	670	670	670	670	



TEST NUMBER: P519760

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	1.7	5.0	10.2	11.1	11.1
92.5°	20.8	73.5	145.3	70.0	48.6
95°	47.8	170.3	513.4	262.5	181.7
97.5°	76.2	195.0	805.2	672.7	507.3
100°	98.1	204.8	898.0	939.6	779.5
102.5°	119.2	218.6	928.7	1139.5	1008.0
105°	156.1	242.8	933.0	1395.8	1309.9
107.5°	190.9	268.2	893.3	1527.6	1549.8
110°	214.1	287.4	857.1	1568.5	1649.4
112.5°	238.6	306.7	822.3	1559.4	1692.4
115°	275.5	337.2	776.9	1501.2	1698.0
117.5°	309.1	366.9	741.8	1408.2	1627.4
120°	330.9	386.8	724.1	1341.5	1566.6
122.5°	350.0	405.2	711.1	1273.3	1497.7
125°	376.1	432.0	697.6	1179.1	1387.6
127.5°	401.2	456.2	689.1	1096.0	1282.1
130°	416.2	471.2	685.7	1048.4	1211.9
132.5°	431.2	485.6	682.3	1006.5	1156.6
135°	452.9	505.4	678.0	951.2	1077.1
137.5°	473.5	523.9	675.8	904.3	1007.7
140°	487.8	536.2	673.7	875.4	968.8
142.5°	502.8	547.9	672.4	848.5	927.2
145°	523.6	564.5	669.5	813.3	873.3
147.5°	546.2	581.7	666.6	783.6	830.8
150°	561.2	592.0	665.2	765.0	804.2
152.5°	574.8	601.7	664.5	749.8	781.7
155°	594.4	616.1	663.5	729.7	753.0
157.5°	611.6	628.5	663.7	715.5	731.2
160°	622.6	636.7	664.4	707.3	718.9
162.5°	632.1	643.6	665.0	700.4	708.7
165°	644.7	652.2	666.1	692.6	695.9
167.5°	655.0	659.3	666.9	686.6	687.9
170°	661.8	663.5	666.9	683.1	683.1
172.5°	665.9	666.2	667.6	679.7	679.7
175°	670.3	669.5	666.9	676.3	674.6
177.5°	672.2	670.9	667.4	672.9	671.5
180°	669.5	669.5	669.5	669.5	669.5

(END OF REPORT)