

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563103

Luminaire Tested: **SQ4-PC3-150U-050D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563103
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-050D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10365.8 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563103
CATALOG NUMBER: SQ4-PC3-150U-050D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563103

CATALOG NUMBER: SQ4-PC3-150U-050D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5751	5751	5751
5°	5795	5757	5736
10°	5780	5754	5737
15°	5750	5750	5744
20°	5712	5729	5729
25°	5658	5699	5682
30°	5590	5657	5633
35°	5506	5591	5552
40°	5415	5492	5436
45°	5317	5355	5271
50°	5178	5178	5095
55°	5013	4949	4874
60°	4772	4676	4601
65°	4410	4323	4285
70°	3861	3892	3877
75°	3106	3436	3458
80°	2207	2912	2943
85°	1341	2442	2442



TEST NUMBER: P563103

CATALOG NUMBER: SQ4-PC3-150U-050D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.5	0.9
10°-20°	253.9	2.4
20°-30°	384.6	3.7
30°-40°	461.0	4.4
40°-50°	470.1	4.5
50°-60°	410.4	4.0
60°-70°	293.8	2.8
70°-80°	151.3	1.5
80°-90°	40.8	0.4
90°-100°	563.1	5.4
100°-110°	1522.4	14.7
110°-120°	1600.6	15.4
120°-130°	1300.1	12.5
130°-140°	1019.8	9.8
140°-150°	782.7	7.6
150°-160°	562.9	5.4
160°-170°	343.9	3.3
170°-180°	115.9	1.1
0°-30°	727.0	7.0
0°-40°	1188.1	11.5
0°-60°	2068.5	20.0
0°-90°	2554.4	24.6
90°-120°	3686.0	35.6
90°-150°	6788.7	65.5
90°-180°	7811.0	75.4
0°-180°	10365.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	935	935	935	935	935	
5°	938	929	932	930	929	89
15°	903	895	903	903	902	255
25°	834	828	840	837	837	384
35°	733	732	745	739	739	459
45°	611	610	616	608	606	470
55°	468	462	462	454	454	417
65°	303	296	297	294	294	300
75°	131	137	145	146	146	141
85°	19	29	35	36	35	26
90°	3	8	17	18	17	7
95°	87	307	936	485	288	91
105°	283	437	1689	2491	2389	298
115°	498	609	1401	2712	3061	492
125°	682	782	1262	2130	2503	608
135°	818	915	1228	1720	1947	632
145°	951	1022	1212	1472	1585	595
155°	1073	1115	1201	1321	1364	495
165°	1168	1180	1206	1253	1260	329
175°	1213	1212	1208	1223	1221	115
180°	1212	1212	1212	1212	1212	



TEST NUMBER: P563103

CATALOG NUMBER: SQ4-PC3-150U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	935.0	935.0	935.0	935.0	935.0
2.5°	940.6	932.5	935.0	932.9	929.5
5°	938.5	929.2	932.4	929.8	929.0
7.5°	931.7	922.4	926.7	925.0	924.1
10°	925.5	916.2	921.2	919.4	918.6
12.5°	917.2	908.6	914.3	912.5	912.4
15°	903.0	895.4	903.0	903.0	902.1
17.5°	885.2	878.2	886.4	886.9	886.4
20°	872.7	865.1	875.3	874.5	875.3
22.5°	857.5	851.2	862.1	859.9	860.8
25°	833.7	827.8	839.8	837.2	837.2
27.5°	805.7	801.5	814.5	811.8	811.8
30°	787.0	782.8	796.5	793.1	793.1
32.5°	766.2	763.3	776.4	772.3	772.3
35°	733.3	731.6	744.6	739.4	739.4
37.5°	699.4	697.9	709.6	703.3	701.3
40°	674.4	673.6	684.0	677.0	677.0
42.5°	649.5	648.7	657.6	649.3	649.3
45°	611.2	609.5	615.6	607.7	606.0
47.5°	569.5	567.8	571.6	563.1	562.2
50°	541.1	539.4	541.1	533.3	532.5
52.5°	512.0	509.0	509.2	501.5	501.3
55°	467.5	461.6	461.5	454.5	454.5
57.5°	420.4	412.6	413.3	407.4	406.6
60°	387.9	379.4	380.1	374.9	374.0
62.5°	356.0	346.2	348.2	342.3	342.2
65°	303.0	296.2	297.0	294.4	294.4
67.5°	252.1	245.8	250.4	248.3	248.1
70°	214.7	210.5	216.4	216.4	215.6
72.5°	180.1	179.9	187.4	187.4	187.9
75°	130.7	136.7	144.6	145.5	145.5
77.5°	87.3	97.8	106.5	106.8	106.7
80°	62.3	74.2	82.2	84.0	83.1
82.5°	42.2	54.8	61.5	63.2	62.3
85°	19.0	29.2	34.6	35.5	34.6
87.5°	6.1	13.2	17.2	17.5	15.9
90°	2.6	7.7	17.0	18.2	17.0
92.5°	37.0	135.0	266.3	115.6	83.7
95°	87.4	306.7	936.4	484.6	288.2
97.5°	140.3	351.8	1459.6	1207.9	887.1
100°	180.0	370.0	1622.4	1692.0	1368.1
102.5°	216.5	395.3	1679.8	2059.0	1816.7
105°	283.0	437.3	1688.9	2491.2	2389.2
107.5°	344.6	485.3	1615.1	2760.9	2794.8
110°	392.6	520.1	1549.3	2833.3	2977.4



TEST NUMBER: P563103

CATALOG NUMBER: SQ4-PC3-150U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.3	554.7	1488.8	2818.8	3060.9
115°	498.2	609.1	1400.7	2711.5	3060.9
117.5°	559.7	663.8	1342.5	2547.4	2943.5
120°	597.3	699.3	1308.1	2429.7	2833.9
122.5°	632.8	732.8	1287.2	2303.5	2710.8
125°	682.1	781.5	1262.4	2130.3	2502.7
127.5°	727.5	825.1	1247.8	1989.0	2316.4
130°	752.5	853.2	1241.6	1901.7	2197.5
132.5°	778.6	878.3	1235.3	1822.9	2095.3
135°	817.7	914.6	1228.5	1720.1	1947.1
137.5°	857.1	948.6	1222.8	1636.7	1821.6
140°	884.2	969.7	1220.7	1583.1	1747.6
142.5°	910.3	990.6	1216.5	1534.6	1678.7
145°	950.7	1022.1	1211.6	1472.3	1584.6
147.5°	987.5	1050.8	1205.8	1415.9	1502.1
150°	1014.6	1070.7	1203.7	1385.3	1454.1
152.5°	1039.7	1088.6	1202.7	1356.8	1413.4
155°	1073.3	1115.4	1201.1	1320.8	1364.1
157.5°	1108.3	1137.6	1201.4	1295.7	1324.2
160°	1128.1	1152.3	1202.4	1279.8	1300.2
162.5°	1143.7	1163.9	1203.5	1267.2	1282.5
165°	1168.5	1180.0	1206.3	1253.4	1259.8
167.5°	1185.5	1193.4	1206.6	1241.6	1244.7
170°	1195.9	1199.7	1207.6	1236.3	1236.3
172.5°	1204.3	1205.0	1207.6	1230.1	1229.0
175°	1212.9	1211.6	1207.6	1223.2	1220.7
177.5°	1215.7	1212.7	1207.4	1217.8	1214.7
180°	1211.6	1211.6	1211.6	1211.6	1211.6

(END OF REPORT)