

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563343

Luminaire Tested: **SQ4-PP3-050U-100D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563343  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-050U-100D-940-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7534.7 lumens  
Efficiency: N/A  
Efficacy: 102.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 73.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563343  
CATALOG NUMBER: SQ4-PP3-050U-100D-940-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563343

CATALOG NUMBER: SQ4-PP3-050U-100D-940-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56
2	93	85	79	74	87	80	75	70	72	67	64	63	60	57	56	53	51	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	52	73	63	56	50	56	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33	30
6	66	54	45	39	62	51	43	38	46	39	35	41	36	32	36	32	29	26
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	27	50	38	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11896	11896	11896
5°	11984	11910	11868
10°	11964	11879	11826
15°	11884	11819	11755
20°	11806	11739	11650
25°	11665	11585	11469
30°	11449	11389	11244
35°	11150	11073	10933
40°	10793	10725	10603
45°	10498	10424	10322
50°	10121	10057	9959
55°	9598	9470	9398
60°	8737	8487	8445
65°	7698	7376	7351
70°	6645	6372	6372
75°	5720	5639	5559
80°	5044	5104	4984
85°	3945	4305	4305



TEST NUMBER: P563343

CATALOG NUMBER: SQ4-PP3-050U-100D-940-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.9	2.4
10°-20°	522.2	6.9
20°-30°	782.2	10.4
30°-40°	917.5	12.2
40°-50°	920.3	12.2
50°-60°	785.1	10.4
60°-70°	512.0	6.8
70°-80°	256.9	3.4
80°-90°	72.6	1.0
90°-100°	189.9	2.5
100°-110°	515.9	6.8
110°-120°	530.4	7.0
120°-130°	424.1	5.6
130°-140°	333.2	4.4
140°-150°	255.5	3.4
150°-160°	183.7	2.4
160°-170°	112.4	1.5
170°-180°	37.9	0.5
0°-30°	1487.3	19.7
0°-40°	2404.8	31.9
0°-60°	4110.2	54.6
0°-90°	4951.7	65.7
90°-120°	1236.2	16.4
90°-150°	2249.0	29.8
90°-180°	2583.0	34.3
0°-180°	7534.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1934	1934	1934	1934	1934	
5°	1941	1923	1929	1922	1922	184
15°	1866	1848	1856	1849	1846	527
25°	1719	1699	1707	1692	1690	790
35°	1485	1470	1475	1458	1456	928
45°	1207	1199	1198	1187	1187	929
55°	895	892	883	878	876	795
65°	529	519	507	504	505	528
75°	241	241	237	236	234	261
85°	56	61	61	61	61	66
90°	1	5	9	11	11	4
95°	28	104	331	144	97	30
105°	92	143	567	864	813	97
115°	163	198	454	903	1029	161
125°	224	255	411	692	817	200
135°	270	300	399	564	636	209
145°	312	334	394	479	515	196
155°	352	365	392	430	443	162
165°	382	387	393	410	411	108
175°	396	397	394	399	398	38
180°	396	396	396	396	396	

TEST NUMBER: P563343

CATALOG NUMBER: SQ4-PP3-050U-100D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1934.1	1934.1	1934.1	1934.1	1934.1
2.5°	1946.3	1930.4	1934.1	1931.2	1923.3
5°	1940.9	1922.7	1929.0	1922.2	1922.2
7.5°	1927.7	1907.8	1914.1	1907.3	1907.0
10°	1915.5	1895.6	1901.9	1895.1	1893.4
12.5°	1897.8	1877.9	1885.6	1877.5	1877.1
15°	1866.3	1848.1	1856.1	1849.3	1846.0
17.5°	1830.7	1810.8	1820.5	1811.0	1809.7
20°	1803.6	1783.7	1793.4	1779.8	1779.8
22.5°	1771.0	1751.1	1762.2	1744.6	1744.6
25°	1718.8	1698.9	1707.0	1691.7	1690.0
27.5°	1656.8	1637.2	1645.6	1628.3	1628.0
30°	1612.0	1593.8	1603.6	1584.9	1583.2
32.5°	1563.2	1546.3	1553.4	1534.7	1533.0
35°	1484.9	1470.0	1474.7	1457.7	1456.1
37.5°	1402.5	1387.3	1392.7	1378.1	1377.4
40°	1344.2	1334.3	1335.7	1323.8	1320.5
42.5°	1290.0	1278.7	1280.1	1268.3	1267.6
45°	1206.9	1198.6	1198.4	1186.6	1186.6
47.5°	1118.8	1112.5	1110.6	1100.8	1100.5
50°	1057.7	1052.8	1051.0	1042.4	1040.8
52.5°	994.0	991.7	985.9	978.7	978.4
55°	895.0	891.7	883.1	878.0	876.4
57.5°	787.5	780.9	771.3	763.8	765.2
60°	710.2	703.6	689.9	686.5	686.5
62.5°	635.7	627.7	614.0	609.3	611.9
65°	528.9	518.9	506.8	503.5	505.1
67.5°	431.9	423.0	409.9	409.8	408.5
70°	369.5	364.6	354.3	354.3	354.3
72.5°	313.9	311.6	304.1	304.1	302.7
75°	240.7	240.7	237.3	235.6	233.9
77.5°	180.4	181.0	179.3	177.6	174.6
80°	142.4	145.7	144.1	142.4	140.7
82.5°	107.1	110.4	110.2	107.1	106.8
85°	55.9	60.9	61.0	61.0	61.0
87.5°	15.2	21.2	23.5	24.0	25.3
90°	1.3	5.0	8.9	11.4	11.4
92.5°	11.4	52.0	90.3	38.8	32.8
95°	28.0	103.9	330.7	143.9	96.7
97.5°	46.3	114.7	507.0	394.5	277.0
100°	58.5	121.9	561.0	568.6	459.2
102.5°	70.7	129.2	575.2	703.3	606.8
105°	91.6	142.6	567.3	863.8	812.8
107.5°	113.2	158.2	534.5	946.7	960.9
110°	128.5	169.5	510.1	963.0	1024.0

TEST NUMBER: P563343

CATALOG NUMBER: SQ4-PP3-050U-100D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	180.8	485.7	949.5	1041.3
115°	162.8	197.6	454.1	903.4	1029.1
117.5°	182.7	216.0	434.0	838.2	979.7
120°	195.9	228.2	424.9	794.4	934.9
122.5°	207.1	239.4	418.7	750.5	886.1
125°	223.9	255.0	410.9	692.3	816.6
127.5°	238.9	269.7	406.5	648.1	754.8
130°	248.0	277.9	404.5	620.4	716.1
132.5°	257.2	287.1	402.5	596.7	681.5
135°	269.7	299.5	399.4	563.9	636.0
137.5°	283.2	310.3	397.9	534.9	595.6
140°	291.3	317.4	396.9	516.4	571.1
142.5°	299.4	323.6	395.9	502.0	547.7
145°	311.6	334.0	394.3	479.1	515.2
147.5°	325.4	344.5	393.1	461.1	489.5
150°	334.5	350.7	393.1	450.8	473.2
152.5°	341.7	355.8	392.0	441.6	460.0
155°	352.3	364.8	391.8	430.2	442.7
157.5°	362.8	372.5	391.8	422.5	432.0
160°	368.9	377.6	391.8	417.4	424.9
162.5°	375.0	381.7	392.8	413.3	418.7
165°	381.6	386.6	393.1	409.6	410.9
167.5°	388.5	391.0	394.3	405.3	406.3
170°	390.5	393.0	394.3	403.2	403.2
172.5°	392.5	394.0	394.3	401.2	401.2
175°	395.6	396.8	394.3	399.4	398.1
177.5°	396.6	396.6	393.6	397.6	395.6
180°	395.6	395.6	395.6	395.6	395.6

(END OF REPORT)