

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563367

Luminaire Tested: **SQ4-PP3-050U-125D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563367
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8901.7 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 87.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563367
CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563367

CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60
2	94	86	80	75	89	82	76	72	74	69	66	66	63	60	59	57	55	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	43
4	79	68	59	53	74	64	57	51	58	52	48	53	48	44	47	44	40	37
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	29
7	62	49	41	35	58	47	39	34	43	37	32	39	34	30	35	31	28	25
8	57	45	37	31	54	43	35	30	39	33	29	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	25	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15181	15181	15181
5°	15292	15199	15146
10°	15267	15159	15091
15°	15166	15083	15001
20°	15065	14980	14867
25°	14887	14783	14637
30°	14611	14534	14350
35°	14228	14131	13953
40°	13773	13687	13530
45°	13398	13304	13171
50°	12916	12834	12709
55°	12248	12085	11993
60°	11150	10830	10777
65°	9823	9414	9382
70°	8481	8130	8130
75°	7301	7196	7094
80°	6436	6514	6358
85°	5039	5498	5498



TEST NUMBER: P563367

CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.4	2.6
10°-20°	666.4	7.5
20°-30°	998.2	11.2
30°-40°	1170.8	13.2
40°-50°	1174.5	13.2
50°-60°	1001.9	11.3
60°-70°	653.4	7.3
70°-80°	327.8	3.7
80°-90°	92.2	1.0
90°-100°	189.9	2.1
100°-110°	515.9	5.8
110°-120°	530.4	6.0
120°-130°	424.1	4.8
130°-140°	333.2	3.7
140°-150°	255.5	2.9
150°-160°	183.7	2.1
160°-170°	112.4	1.3
170°-180°	37.9	0.4
0°-30°	1898.0	21.3
0°-40°	3068.8	34.5
0°-60°	5245.2	58.9
0°-90°	6318.7	71.0
90°-120°	1236.2	13.9
90°-150°	2249.0	25.3
90°-180°	2583.0	29.0
0°-180°	8901.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2468	2468	2468	2468	2468	
5°	2477	2454	2462	2453	2453	235
15°	2382	2358	2369	2360	2356	672
25°	2194	2168	2178	2159	2157	1009
35°	1895	1876	1882	1860	1858	1184
45°	1540	1530	1529	1514	1514	1186
55°	1142	1138	1127	1120	1118	1015
65°	675	662	647	642	645	674
75°	307	307	303	301	298	333
85°	71	78	78	78	78	84
90°	1	5	9	11	11	5
95°	28	104	331	144	97	30
105°	92	143	567	864	813	97
115°	163	198	454	903	1029	161
125°	224	255	411	692	817	200
135°	270	300	399	564	636	209
145°	312	334	394	479	515	196
155°	352	365	392	430	443	162
165°	382	387	393	410	411	108
175°	396	397	394	399	398	38
180°	396	396	396	396	396	

TEST NUMBER: P563367

CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2468.2	2468.2	2468.2	2468.2	2468.2
2.5°	2483.7	2463.4	2468.2	2464.5	2454.3
5°	2476.8	2453.6	2461.7	2453.0	2453.0
7.5°	2460.0	2434.6	2442.6	2434.0	2433.6
10°	2444.4	2419.0	2427.1	2418.4	2416.3
12.5°	2421.9	2396.5	2406.3	2395.9	2395.5
15°	2381.6	2358.4	2368.7	2359.9	2355.7
17.5°	2336.2	2310.8	2323.2	2311.1	2309.4
20°	2301.6	2276.2	2288.6	2271.3	2271.3
22.5°	2260.1	2234.7	2248.8	2226.3	2226.3
25°	2193.5	2168.1	2178.3	2158.8	2156.7
27.5°	2114.3	2089.3	2100.0	2077.9	2077.5
30°	2057.2	2033.9	2046.4	2022.5	2020.4
32.5°	1994.9	1973.3	1982.3	1958.5	1956.4
35°	1894.9	1875.9	1882.0	1860.3	1858.2
37.5°	1789.8	1770.3	1777.3	1758.6	1757.8
40°	1715.4	1702.7	1704.6	1689.3	1685.1
42.5°	1646.2	1631.8	1633.6	1618.5	1617.6
45°	1540.2	1529.6	1529.4	1514.2	1514.2
47.5°	1427.7	1419.7	1417.3	1404.8	1404.3
50°	1349.8	1343.5	1341.2	1330.3	1328.2
52.5°	1268.5	1265.5	1258.1	1249.0	1248.6
55°	1142.2	1137.9	1127.0	1120.5	1118.4
57.5°	1005.0	996.5	984.2	974.8	976.5
60°	906.4	897.9	880.4	876.1	876.1
62.5°	811.2	801.0	783.5	777.5	780.9
65°	674.9	662.2	646.8	642.5	644.6
67.5°	551.2	539.8	523.1	523.0	521.3
70°	471.6	465.2	452.1	452.1	452.1
72.5°	400.6	397.7	388.1	388.0	386.3
75°	307.2	307.2	302.8	300.6	298.5
77.5°	230.2	231.0	228.9	226.6	222.8
80°	181.7	185.9	183.9	181.7	179.5
82.5°	136.7	140.9	140.6	136.7	136.3
85°	71.4	77.7	77.9	77.9	77.9
87.5°	19.3	26.8	29.5	30.0	31.7
90°	1.3	5.0	8.9	11.4	11.4
92.5°	11.4	52.0	90.3	38.8	32.8
95°	28.0	103.9	330.7	143.9	96.7
97.5°	46.3	114.7	507.0	394.5	277.0
100°	58.5	121.9	561.0	568.6	459.2
102.5°	70.7	129.2	575.2	703.3	606.8
105°	91.6	142.6	567.3	863.8	812.8
107.5°	113.2	158.2	534.5	946.7	960.9
110°	128.5	169.5	510.1	963.0	1024.0



TEST NUMBER: P563367

CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	180.8	485.7	949.5	1041.3
115°	162.8	197.6	454.1	903.4	1029.1
117.5°	182.7	216.0	434.0	838.2	979.7
120°	195.9	228.2	424.9	794.4	934.9
122.5°	207.1	239.4	418.7	750.5	886.1
125°	223.9	255.0	410.9	692.3	816.6
127.5°	238.9	269.7	406.5	648.1	754.8
130°	248.0	277.9	404.5	620.4	716.1
132.5°	257.2	287.1	402.5	596.7	681.5
135°	269.7	299.5	399.4	563.9	636.0
137.5°	283.2	310.3	397.9	534.9	595.6
140°	291.3	317.4	396.9	516.4	571.1
142.5°	299.4	323.6	395.9	502.0	547.7
145°	311.6	334.0	394.3	479.1	515.2
147.5°	325.4	344.5	393.1	461.1	489.5
150°	334.5	350.7	393.1	450.8	473.2
152.5°	341.7	355.8	392.0	441.6	460.0
155°	352.3	364.8	391.8	430.2	442.7
157.5°	362.8	372.5	391.8	422.5	432.0
160°	368.9	377.6	391.8	417.4	424.9
162.5°	375.0	381.7	392.8	413.3	418.7
165°	381.6	386.6	393.1	409.6	410.9
167.5°	388.5	391.0	394.3	405.3	406.3
170°	390.5	393.0	394.3	403.2	403.2
172.5°	392.5	394.0	394.3	401.2	401.2
175°	395.6	396.8	394.3	399.4	398.1
177.5°	396.6	396.6	393.6	397.6	395.6
180°	395.6	395.6	395.6	395.6	395.6

(END OF REPORT)