

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563415

Luminaire Tested: **SQ4-PP3-075U-075D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563415
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7609.2 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563415
CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563415

CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8953	8953	8953
5°	9019	8964	8932
10°	9004	8940	8900
15°	8944	8895	8847
20°	8885	8835	8768
25°	8779	8719	8632
30°	8617	8572	8463
35°	8392	8334	8229
40°	8123	8072	7980
45°	7901	7846	7768
50°	7618	7569	7495
55°	7223	7128	7073
60°	6575	6387	6356
65°	5793	5551	5533
70°	5001	4794	4794
75°	4306	4244	4185
80°	3797	3840	3751
85°	2971	3239	3239



TEST NUMBER: P563415

CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	1.8
10°-20°	393.0	5.2
20°-30°	588.7	7.7
30°-40°	690.5	9.1
40°-50°	692.7	9.1
50°-60°	590.9	7.8
60°-70°	385.4	5.1
70°-80°	193.3	2.5
80°-90°	55.0	0.7
90°-100°	281.1	3.7
100°-110°	773.3	10.2
110°-120°	798.1	10.5
120°-130°	639.5	8.4
130°-140°	502.3	6.6
140°-150°	384.9	5.1
150°-160°	276.7	3.6
160°-170°	169.2	2.2
170°-180°	57.0	0.7
0°-30°	1119.3	14.7
0°-40°	1809.9	23.8
0°-60°	3093.4	40.7
0°-90°	3727.1	49.0
90°-120°	1852.5	24.3
90°-150°	3379.1	44.4
90°-180°	3882.0	51.0
0°-180°	7609.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1456	1456	1456	1456	1456	
5°	1461	1447	1452	1447	1447	139
15°	1405	1391	1397	1392	1389	396
25°	1294	1279	1285	1273	1272	595
35°	1118	1106	1110	1097	1096	698
45°	908	902	902	893	893	699
55°	674	671	665	661	660	599
65°	398	391	381	379	380	397
75°	181	181	179	177	176	197
85°	42	46	46	46	46	49
90°	1	5	9	11	11	4
95°	42	153	497	212	136	44
105°	138	213	852	1298	1211	146
115°	245	298	683	1361	1544	241
125°	337	384	620	1049	1229	301
135°	407	452	602	848	960	314
145°	470	503	593	723	778	295
155°	532	550	590	650	668	245
165°	576	583	592	616	620	162
175°	596	597	593	601	600	57
180°	596	596	596	596	596	

TEST NUMBER: P563415

CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1455.6	1455.6	1455.6	1455.6	1455.6
2.5°	1464.8	1452.8	1455.6	1453.5	1447.5
5°	1460.7	1447.0	1451.8	1446.7	1446.7
7.5°	1450.8	1435.8	1440.6	1435.5	1435.2
10°	1441.6	1426.6	1431.4	1426.3	1425.0
12.5°	1428.3	1413.4	1419.1	1413.0	1412.8
15°	1404.6	1390.9	1396.9	1391.8	1389.3
17.5°	1377.8	1362.8	1370.2	1363.0	1362.0
20°	1357.4	1342.4	1349.7	1339.5	1339.5
22.5°	1332.9	1317.9	1326.3	1313.0	1313.0
25°	1293.6	1278.6	1284.7	1273.2	1271.9
27.5°	1246.9	1232.2	1238.5	1225.5	1225.2
30°	1213.2	1199.5	1206.9	1192.8	1191.6
32.5°	1176.5	1163.8	1169.1	1155.0	1153.8
35°	1117.6	1106.3	1109.9	1097.1	1095.9
37.5°	1055.6	1044.1	1048.2	1037.2	1036.7
40°	1011.7	1004.2	1005.3	996.3	993.8
42.5°	970.8	962.4	963.4	954.5	954.0
45°	908.3	902.1	902.0	893.0	893.0
47.5°	842.0	837.3	835.9	828.5	828.2
50°	796.1	792.3	791.0	784.6	783.3
52.5°	748.1	746.4	742.0	736.6	736.4
55°	673.6	671.1	664.7	660.8	659.6
57.5°	592.7	587.7	580.5	574.9	575.9
60°	534.5	529.6	519.2	516.7	516.7
62.5°	478.4	472.4	462.1	458.6	460.5
65°	398.0	390.6	381.4	378.9	380.2
67.5°	325.1	318.3	308.5	308.5	307.5
70°	278.1	274.4	266.6	266.6	266.6
72.5°	236.3	234.5	228.9	228.8	227.8
75°	181.2	181.2	178.6	177.3	176.1
77.5°	135.7	136.2	135.0	133.6	131.4
80°	107.2	109.7	108.4	107.1	105.9
82.5°	80.6	83.1	82.9	80.6	80.4
85°	42.1	45.8	45.9	45.9	45.9
87.5°	11.5	16.2	18.1	18.6	19.6
90°	1.3	5.0	8.9	11.4	11.4
92.5°	17.5	74.8	129.6	49.8	40.8
95°	41.8	153.4	497.0	212.5	135.7
97.5°	68.2	170.1	758.5	584.4	412.3
100°	87.5	180.5	840.6	848.5	692.3
102.5°	105.7	192.8	861.9	1052.6	909.3
105°	138.2	212.6	852.0	1297.6	1210.8
107.5°	169.1	237.1	803.6	1417.6	1443.4
110°	191.5	253.4	767.1	1447.4	1536.7



TEST NUMBER: P563415

CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.7	271.7	730.6	1428.2	1564.1
115°	244.7	298.0	683.4	1360.8	1544.3
117.5°	276.1	325.2	653.5	1266.3	1473.8
120°	295.4	342.5	640.3	1195.4	1409.9
122.5°	312.7	359.8	631.2	1133.3	1336.9
125°	337.3	384.4	620.0	1048.8	1228.6
127.5°	360.6	405.5	612.6	978.3	1136.0
130°	372.8	418.6	608.6	936.4	1080.2
132.5°	387.0	432.8	605.5	899.6	1029.5
135°	407.0	451.6	602.2	848.2	959.8
137.5°	425.8	467.2	599.5	806.7	898.7
140°	440.0	478.4	598.4	779.1	862.2
142.5°	452.1	487.6	596.4	754.5	825.6
145°	470.4	502.6	593.4	722.7	778.5
147.5°	489.9	517.7	591.9	694.5	739.2
150°	502.1	526.9	590.8	679.1	713.8
152.5°	513.2	536.1	589.8	665.8	694.5
155°	532.5	549.9	589.6	649.6	668.2
157.5°	546.5	560.6	589.6	636.3	649.2
160°	556.6	567.8	589.6	629.1	639.0
162.5°	564.7	573.9	590.6	623.0	630.9
165°	575.6	583.1	592.1	616.3	620.0
167.5°	583.2	588.9	593.4	610.6	611.6
170°	588.3	592.0	593.4	608.6	608.6
172.5°	592.4	594.1	593.4	605.5	604.5
175°	595.9	597.1	593.4	601.0	599.7
177.5°	596.9	596.9	592.9	598.9	596.9
180°	595.9	595.9	595.9	595.9	595.9

(END OF REPORT)